

AXIS P1375 Network Camera

Stable, 2 MP surveillance under any circumstances

AXIS P1375 Network Camera offers excellent video even in vibrating conditions and features scene profiles for automatically adjusted settings to suit specific scenes. Enhanced security features such as signed firmware and secure boot ensure the integrity and authenticity of the camera's firmware. Furthermore, features such as tampering alarm and video streaming indicator ensure full control of the video. With Lightfinder and Forensic WDR, the camera provides details even in challenging light conditions and thanks to Zipstream, storage and bandwidth are significantly reduced. The camera's CS mount enables flexibility to change to bigger or more intelligent lenses, such as i-CS lenses.

- > HDTV 1080p at up to 60 fps
- > Electronic image stabilization
- > Signed firmware and secure boot
- > Lightfinder 2.0 and Forensic WDR
- > Zipstream with H.264 and H.265







AXIS P1375 Network Camera

Camera		Analytics	Included
Image sensor	1/2.8" progressive scan RGB CMOS	Allalytics	AXIS Video Motion Detection, active tampering alarm, audio
Lens	Lens CS 2.8–8 mm F1.2 P-Iris 5 MP Horizontal field of view: 121°–33° Vertical field of view: 63°–19°		detection Supported AXIS Live Privacy Shield, AXIS Perimeter Defender, AXIS Guard Suite including AXIS Motion Guard,
Day and night	Automatically removable infrared-cut filter		AXIS Fence Guard, and AXIS Loitering Guard
Minimum	HDTV 1080p 25/30 fps with Forensic WDR and Lightfinder:		Support for AXIS Camera Application Platform enabling installation of third-party applications, see axis.com/acap
illumination	Color: 0.05 lux, at 50 IRE F1.2 B/W: 0.01 lux, at 50 IRE F1.2 HDTV 1080p 50/60 fps with Lightfinder: Color: 0.10 lux, at 50 IRE F1.2 B/W: 0.02 lux, at 50 IRE F1.2	Event triggers Event actions	Analytics, shock detection, edge storage events, supervised external input, audio level, time scheduled Hardware: network, ring power overcurrent protection Record video: SD card and network share
Shutter time	WDR: 1/34500 s to 2 s No WDR: 1/66500 s to 2 s		Upload of images or video clips: FTP, SFTP, HTTP, HTTPS, network share and email
Video			Pre- and post-alarm video or image buffering for recording or upload
Video compression	H.264 (MPEG-4 Part 10/AVC) Baseline, Main and High Profiles H.265 (MPEG-H Part 2/HEVC) Motion JPEG		Notification: email, HTTP, HTTPS, TCP and SNMP trap PTZ: PTZ preset, start/stop guard tour Overlay text, external output activation, play audio clip, WDR mode, day/night mode
Resolution	1920x1080 (HDTV) to 160x90	Data streaming	Event data
Frame rate	WDR: 25/30 fps (50/60 Hz) No WDR: 50/60 fps (50/60 Hz)	Built-in	Focus assistant, pixel counter, remote back focus, autorotation
Video streaming	Multiple, individually configurable streams in H.264, H.265, and	installation aids	Todas assistant, pixer counter, remote ouck rocas, autorotation
video streaming	Motion JPEG	General	
	Axis Zipstream technology in H.264 and H.265 Controllable frame rate and bandwidth VBR/ABR/MBR H.264/H.265 Video streaming indicator	Casing	Metal (zinc) Color lid: White NCS S 1002-B Color chassis: Black NCS S 9002-N
Multi-view streaming	Up to 8 individually cropped out view areas	Mounting	¼"–20 tripod screw thread Camera stand included
Image settings	Saturation, contrast, brightness, sharpness, Forensic WDR: Up to	Sustainability	PVC free
image sectings	120 dB depending on scene, white balance, day/night threshold, exposure mode, exposure zones, local contrast, tone mapping, compression, orientation: auto, 0°, 90°, 180°, 270° including Corridor Format, mirroring of images, dynamic text and image overlay, privacy masks, defogging, electronic image stabilization,	Memory	1 GB RAM, 512 MB Flash
		Power	12–28 V DC, max 9.6 W, typical 4.9 W Power over Ethernet (PoE) IEEE 802.3af/802.3at Type 1 Class 3, max 9.6 W, typical 5.1 W RJ45 10BASE-T/100BASE-TX/1000BASE-T
Pan/Tilt/Zoom	barrel distortion correction, scene profiles: forensic, vivid, traffic overview Digital PTZ		I/O: 6-pin 2.5 mm terminal block, for 2 supervised alarm inputs and 2 outputs RS485/RS422, 2 pcs, 2 pos, full duplex, terminal block
	Uploadable PTZ driver (Pelco D pre-installed)		DC input, terminal block, 3.5 mm mic/line in, 3.5 mm line out
Audio	T. C.H. I. I.		i-CS connector (compatible with P-Iris and DC-iris) Security lock slot
Audio streaming	Two-way, full duplex		AXIS T92G20 connector
Audio compression Audio	AAC LC 8/16/32/48 kHz, G.711 PCM 8 kHz, G.726 ADPCM 8 kHz, Opus 8/16/48 kHz, LPCM 48 kHz Configurable bit rate External microphone input, line input, digital input with ring	Storage	Support for microSD/microSDHC/microSDXC card Support for SD card encryption Support for recording to network-attached storage (NAS) For SD card and NAS recommendations see axis.com
input/output	power, line output, built-in microphone (can be disabled)	Operating	-10 °C to 55 °C (14 °F to 131 °F)
Network		conditions	Humidity 10-85% RH (non-condensing)
Security	Password protection, IP address filtering, HTTPS ^a encryption, IEEE 802.1X (EAP-TLS) ^a network access control, digest authentication, user access log, centralized certificate	Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F) Humidity 5-95% RH (non-condensing)
	management, brute force delay protection, signed firmware, secure boot	Approvals	EMC EN 55032 Class A, EN 61000-3-2, EN 61000-3-3, EN 55024, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class A,
Supported protocols	IPv4, IPv6 USGv6, HTTP, HTTPS ^a , SSL/TLS ^a , QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, Bonjour, UPnP™, SNMP v1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SRTP, SFTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP, ARP, SOCKS, SSH, LLDP		ICES-003 Class A, VCCI Class A, RCM AS/NZS CISPR 32 Class A, KCC KN32 Class A, KN35 Safety IEC/EN/UL 60950-1, IS 13252
System integration			Network NIST SP500–267
Application Programming	Open API for software integration, including VAPIX® and AXIS Camera Application Platform, specifications at axis.com	Dimensions	214 x 80 x 57 mm (8 7/16 x 3 1/8 x 2 1/4 in)
Interface	AXIS Guardian with One-Click Connection	Weight	750 g (1.7 lb)
	ONVIF® Profile G, ONVIF® Profile S, and ONVIF® Profile T, specification at onvif.org	Included accessories	Connector kit, Installation Guide, Windows® decoder 1-user license, stand, Resistorx® L-key TR20, Torx® L-key T6
Onscreen controls	Electronic image stabilization Day/night shift Defogging Wide dynamic range	Optional lenses	Lens CS 2.8-10 mm F1.2 P-Iris 2 MP Theia Varifocal Ultra Wide Lens 1.8-3.0 mm Lens Computar i-CS 2.8-8.5 mm Tamron 5 MP Lens P-Iris 8-50 mm F1.6

www.cxis.com T10129632/EN/M5.2/2001

	Lens i-CS 9-50 mm F1.5 8 MP	
Optional accessories	Axis mounts, Axis lenses, Axis midspans, Axis microphones AXIS T92G20 Outdoor Housing AXIS T8355 Digital Microphone For more accessories, see axis.com	
Video management software	AXIS Companion, AXIS Camera Station, video management software from Axis' Application Development Partners available at axis.com/vms	
Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese, Polish	

Warranty Axis 3-year warranty and AXIS Extended Warranty option, see axis.com/warranty

 a. This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (http://www.openssl.org/), and cryptographic software written by Eric Young (eay@cryptsoft.com).

Environmental responsibility:

axis.com/environmental-responsibility

