



## Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 12

SDS No. : 150233  
V005.0

LOCTITE® 242® THREADLOCKER

Revision: 22.03.2017

printing date: 30.05.2019

Replaces version from: 18.12.2015

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

LOCTITE® 242® THREADLOCKER

#### Contains:

Cumene hydroperoxide

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Adhesive

#### 1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000

Fax-no.: +44 1442 278071

ua-productsafety.uk@henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

Serious eye irritation

Category 2

H319 Causes serious eye irritation.

Specific target organ toxicity - single exposure

Category 3

H335 May cause respiratory irritation.

Target organ: respiratory tract irritation

**Chronic hazards to the aquatic environment**

**Category 3**

**H412 Harmful to aquatic life with long lasting effects.**

#### 2.2. Label elements

##### Label elements (CLP):

Hazard pictogram:



|                                 |  |
|---------------------------------|--|
| <b>Signal word:</b>             | Warning  |
| <b>Hazard statement:</b>        | H319 Causes serious eye irritation.<br>H335 May cause respiratory irritation.<br>H412 Harmful to aquatic life with long lasting effects. |
| <b>Precautionary statement:</b> | P261 Avoid breathing vapours.  |
| <b>Prevention</b>               | P273 Avoid release to the environment.   |
| <b>Precautionary statement:</b> | P337+P313 If eye irritation persists: Get medical advice/attention.  |
| <b>Response</b>                 |  |

### 2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

## SECTION 3: Composition/information on ingredients

### 3.2. Mixtures

#### General chemical description:

Anaerobic Sealant

**Declaration of the ingredients according to CLP (EC) No 1272/2008:**

| <b>Hazardous components<br/>CAS-No.</b> | <b>EC Number<br/>REACH-Reg No.</b> | <b>content</b> | <b>Classification</b>  |
|---|------------------------------------|----------------|--|
| Cumene hydroperoxide<br>80-15-9         | 201-254-7                          | 1- < 3 %       | Acute Tox. 4; Dermal<br>H312<br>STOT RE 2<br>H373<br>Acute Tox. 4; Oral<br>H302<br>Org. Perox. E<br>H242<br>Acute Tox. 3; Inhalation<br>H331<br>Aquatic Chronic 2<br>H411<br>Skin Corr. 1B<br>H314   |
| N,N-Diethyl-p-toluidine<br>613-48-9     | 210-345-0                          | 0,1- < 1 %     | Acute Tox. 3; Oral<br>H301<br>Acute Tox. 3; Dermal<br>H311<br>Acute Tox. 3; Inhalation<br>H331<br>STOT RE 2<br>H373<br>Aquatic Chronic 3<br>H412   |
| 1,4-Naphthalenedione<br>130-15-4        | 204-977-6                          | 0,01- < 0,1 %  | Acute Tox. 3; Oral<br>H301<br>Skin Irrit. 2; Dermal<br>H315<br>Skin Sens. 1; Dermal<br>H317<br>Eye Irrit. 2<br>H319<br>Acute Tox. 1; Inhalation<br>H330<br>STOT SE 3; Inhalation<br>H335<br>Aquatic Acute 1<br>H400<br>Aquatic Chronic 1<br>H410<br>M factor (Acute Aquat Tox): 10 M factor<br>(Chron Aquat Tox): 10 |

**For full text of the H - statements and other abbreviations see section 16 "Other information".**  
**Substances without classification may have community workplace exposure limits available.**

**SECTION 4: First aid measures****4.1. Description of first aid measures****Inhalation:**

Should not be a problem as product is of low volatility. However, if feeling unwell remove patient to fresh air.

**Skin contact:**

Rinse with running water and soap.

Obtain medical attention if irritation persists.

**Eye contact:**

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

**Ingestion:**

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

#### **4.2. Most important symptoms and effects, both acute and delayed**

EYE: Irritation, conjunctivitis.

RESPIRATORY: Irritation, coughing, shortness of breath, chest tightness.

Prolonged or repeated contact may cause skin irritation.

#### **4.3. Indication of any immediate medical attention and special treatment needed**

See section: Description of first aid measures

### **SECTION 5: Firefighting measures**

#### **5.1. Extinguishing media**

##### **Suitable extinguishing media:**

carbon dioxide, foam, powder, water spray jet, fine water spray

##### **Extinguishing media which must not be used for safety reasons:**

High pressure waterjet

#### **5.2. Special hazards arising from the substance or mixture**

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO<sub>2</sub>) and nitrogen oxides (NO<sub>x</sub>) can be released.  
Oxides of carbon, oxides of nitrogen, irritating organic vapors.

#### **5.3. Advice for firefighters**

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

##### **Additional information:**

In case of fire, keep containers cool with water spray.

### **SECTION 6: Accidental release measures**

#### **6.1. Personal precautions, protective equipment and emergency procedures**

Ensure adequate ventilation.  
Avoid contact with skin and eyes.  
Wear protective equipment.

#### **6.2. Environmental precautions**

Do not empty into drains / surface water / ground water.

#### **6.3. Methods and material for containment and cleaning up**

For small spills wipe up with paper towel and place in container for disposal.  
For large spills absorb onto inert absorbent material and place in sealed container for disposal.

#### **6.4. Reference to other sections**

See advice in section 8

### **SECTION 7: Handling and storage**

#### **7.1. Precautions for safe handling**

Use only in well-ventilated areas.  
Avoid skin and eye contact.  
See advice in section 8

##### **Hygiene measures:**

Good industrial hygiene practices should be observed.  
Wash hands before work breaks and after finishing work.  
Do not eat, drink or smoke while working.

#### **7.2. Conditions for safe storage, including any incompatibilities**

Refer to Technical Data Sheet

**7.3. Specific end use(s)**  
Adhesive**SECTION 8: Exposure controls/personal protection****8.1. Control parameters****Occupational Exposure Limits**Valid for  
Great Britain

| Ingredient [Regulated substance]   | ppm | mg/m <sup>3</sup> | Value type                   | Short term exposure limit category / Remarks | Regulatory list |
|--|-----|-------------------|------------------------------|--|-----------------|
| Silicon dioxide<br>112945-52-5<br>[SILICA, AMORPHOUS, INHALABLE DUST]            |     | 6                 | Time Weighted Average (TWA): |  | EH40 WEL        |
| Silicon dioxide<br>112945-52-5<br>[SILICA, AMORPHOUS, RESPIRABLE DUST]           |     | 2,4               | Time Weighted Average (TWA): |  | EH40 WEL        |
| Propane-1,2-diol<br>57-55-6<br>[PROPANE-1,2-DIOL, PARTICULATES]                  |     | 10                | Time Weighted Average (TWA): |  | EH40 WEL        |
| Propane-1,2-diol<br>57-55-6<br>[PROPANE-1,2-DIOL, TOTAL VAPOUR AND PARTICULATES] | 150 | 474               | Time Weighted Average (TWA): |  | EH40 WEL        |

**Occupational Exposure Limits**Valid for  
Ireland

| Ingredient [Regulated substance]   | ppm | mg/m <sup>3</sup> | Value type                   | Short term exposure limit category / Remarks | Regulatory list |
|--|-----|-------------------|------------------------------|--|-----------------|
| Silicon dioxide<br>112945-52-5<br>[SILICA, AMORPHOUS, TOTAL INHALABLE DUST]        |     | 6                 | Time Weighted Average (TWA): |  | IR_OEL          |
| Silicon dioxide<br>112945-52-5<br>[SILICA, AMORPHOUS, RESPIRABLE DUST]             |     | 2,4               | Time Weighted Average (TWA): |  | IR_OEL          |
| Propane-1,2-diol<br>57-55-6<br>[PROPANE-1,2-DIOL, PARTICULATES]                    |     | 10                | Time Weighted Average (TWA): |  | IR_OEL          |
| Propane-1,2-diol<br>57-55-6<br>[PROPANE-1,2-DIOL, TOTAL (VAPOUR AND PARTICULATES)] | 150 | 470               | Time Weighted Average (TWA): |  | IR_OEL          |

**Predicted No-Effect Concentration (PNEC):**

| Name on list   | Environmental<br>Compartment       | Exposure<br>period | Value           |     |                 |        | Remarks |
|--|------------------------------------|--------------------|-----------------|-----|-----------------|--------|---------|
|  |                                    |                    | mg/l            | ppm | mg/kg           | others |         |
| .alpha.,.alpha.-Dimethylbenzyl<br>hydroperoxide<br>80-15-9 | aqua<br>(freshwater)               |                    | 0,0031<br>mg/l  |     |                 |        |         |
| .alpha.,.alpha.-Dimethylbenzyl<br>hydroperoxide<br>80-15-9 | aqua (marine<br>water)             |                    | 0,00031<br>mg/l |     |                 |        |         |
| .alpha.,.alpha.-Dimethylbenzyl<br>hydroperoxide<br>80-15-9 | aqua<br>(intermittent<br>releases) |                    | 0,031 mg/l      |     |                 |        |         |
| .alpha.,.alpha.-Dimethylbenzyl<br>hydroperoxide<br>80-15-9 | Sewage<br>treatment plant          |                    | 0,35 mg/l       |     |                 |        |         |
| .alpha.,.alpha.-Dimethylbenzyl<br>hydroperoxide<br>80-15-9 | sediment<br>(freshwater)           |                    |                 |     | 0,023<br>mg/kg  |        |         |
| .alpha.,.alpha.-Dimethylbenzyl<br>hydroperoxide<br>80-15-9 | sediment<br>(marine water)         |                    |                 |     | 0,0023<br>mg/kg |        |         |
| .alpha.,.alpha.-Dimethylbenzyl<br>hydroperoxide<br>80-15-9 | soil                               |                    |                 |     | 0,0029<br>mg/kg |        |         |

**Derived No-Effect Level (DNEL):**

| Name on list   | Application<br>Area | Route of<br>Exposure | Health Effect                               | Exposure<br>Time | Value               | Remarks |
|--|---------------------|----------------------|---|------------------|---------------------|---------|
| .alpha.,.alpha.-Dimethylbenzyl<br>hydroperoxide<br>80-15-9 | Workers             | inhalation           | Long term<br>exposure -<br>systemic effects |                  | 6 mg/m <sup>3</sup> |         |

**Biological Exposure Indices:**

None

**8.2. Exposure controls:**

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387)

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to &gt; 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; &gt;= 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to &gt; 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; &gt;= 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

**Eye protection:**

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.  
Protective eye equipment should conform to EN166.

**Skin protection:**

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

**Advices to personal protection equipment:**

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions.  
Personal protective equipment should conform to the relevant EN standard.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

|  |   |
|--|---|
| Appearance                                     | liquid<br>liquid<br>blue                      |
| Odor   | mild  |
| Odour threshold                                | No data available / Not applicable            |
| pH   | Not available.                                |
| pH   | Not applicable                                |
| Initial boiling point                          | > 149,0 °C (> 300,2 °F)                       |
| Flash point                                    | > 93,3 °C (> 199,94 °F); Tagliabue closed cup |
| Decomposition temperature                      | No data available / Not applicable            |
| Vapour pressure<br>(27 °C (80,6 °F))           | < 6,67 mbar                                   |
| Density<br>( $\rho$ )                          | 1,1 g/cm <sup>3</sup>                         |
| Bulk density                                   | No data available / Not applicable            |
| Viscosity                                      | No data available / Not applicable            |
| Viscosity (kinematic)                          | No data available / Not applicable            |
| Explosive properties                           | No data available / Not applicable            |
| Solubility (qualitative)<br>(Solvent: Water)   | Slight  |
| Solubility (qualitative)<br>(Solvent: Acetone) | Not available.                                |
| Solidification temperature                     | No data available / Not applicable            |
| Melting point                                  | No data available / Not applicable            |
| Flammability                                   | No data available / Not applicable            |
| Auto-ignition temperature                      | No data available / Not applicable            |
| Explosive limits                               | No data available / Not applicable            |
| Partition coefficient: n-octanol/water         | No data available / Not applicable            |
| Evaporation rate                               | No data available / Not applicable            |
| Vapor density                                  | No data available / Not applicable            |
| Oxidising properties                           | No data available / Not applicable            |

**9.2. Other information**

No data available / Not applicable

**SECTION 10: Stability and reactivity****10.1. Reactivity**

None if used properly.

**10.2. Chemical stability**

Stable under recommended storage conditions.

**10.3. Possibility of hazardous reactions**

See section reactivity

**10.4. Conditions to avoid**

Stable under normal conditions of storage and use.

**10.5. Incompatible materials**

See section reactivity.

**10.6. Hazardous decomposition products**

None if used for intended purpose.

**SECTION 11: Toxicological information****11.1. Information on toxicological effects****General toxicological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation (EC) No 1272/2008. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

**STOT-single exposure:**

May cause respiratory irritation.

**Oral toxicity:**

This material is considered to have low toxicity if swallowed.

May cause irritation to the digestive tract.

**Inhalative toxicity:**

May cause irritation to respiratory system.

**Skin irritation:**

Prolonged or repeated contact may cause skin irritation.

**Eye irritation:**

Causes serious eye irritation.

**Acute oral toxicity:**

| Hazardous components<br>CAS-No.  | Value<br>type | Value     | Route of<br>application | Exposure<br>time | Species | Method        |
|----------------------------------|---------------|-----------|-------------------------|------------------|---------|---------------|
| Cumene hydroperoxide<br>80-15-9  | LD50          | 550 mg/kg | oral                    |                  | rat     | not specified |
| 1,4-Naphthalenedione<br>130-15-4 | LD50          | 190 mg/kg | oral                    |                  | rat     | not specified |

**Acute dermal toxicity:**

| Hazardous components<br>CAS-No. | Value<br>type | Value                  | Route of<br>application | Exposure<br>time | Species | Method        |
|---------------------------------|---------------|------------------------|-------------------------|------------------|---------|---------------|
| Cumene hydroperoxide<br>80-15-9 | LD50          | 1.200 - 1.520<br>mg/kg | dermal                  |                  |         | not specified |

**Skin corrosion/irritation:**

| Hazardous components<br>CAS-No. | Result    | Exposure<br>time | Species | Method      |
|---------------------------------|-----------|------------------|---------|-------------|
| Cumene hydroperoxide<br>80-15-9 | corrosive |                  | rabbit  | Draize Test |



**Germ cell mutagenicity:**

| Hazardous components CAS-No. | Result   | Type of study / Route of administration           | Metabolic activation / Exposure time | Species | Method  |
|------------------------------|----------|---|--------------------------------------|---------|---|
| Cumene hydroperoxide 80-15-9 | positive | bacterial reverse mutation assay (e.g. Ames test) | without                              |         | OECD Guideline 471 (Bacterial Reverse Mutation Assay) |
| Cumene hydroperoxide 80-15-9 | negative | dermal  |                                      | mouse   | not specified   |

**Repeated dose toxicity**

| Hazardous components CAS-No. | Result | Route of application | Exposure time / Frequency of treatment | Species | Method        |
|------------------------------|--------|----------------------|--|---------|---------------|
| Cumene hydroperoxide 80-15-9 |        | inhalation: aerosol  | 6 h/d5 d/w                             | rat     | not specified |

**SECTION 12: Ecological information****General ecological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation (EC) No 1272/2008. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

**12.1. Toxicity**

| Hazardous components CAS-No.  | Value type | Value      | Acute Toxicity Study | Exposure time | Species                        | Method  |
|-------------------------------|------------|------------|----------------------|---------------|--------------------------------|---|
| Cumene hydroperoxide 80-15-9  | LC50       | 3,9 mg/l   | Fish                 | 96 h          | Oncorhynchus mykiss            | OECD Guideline 203 (Fish, Acute Toxicity Test)                  |
| Cumene hydroperoxide 80-15-9  | EC50       | 18 mg/l    | Daphnia              | 48 h          | Daphnia magna                  | OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)      |
| Cumene hydroperoxide 80-15-9  | ErC50      | 3,1 mg/l   | Algae                | 72 h          | Pseudokirchnerella subcapitata | OECD Guideline 201 (Alga, Growth Inhibition Test) not specified |
| Cumene hydroperoxide 80-15-9  | EC10       | 70 mg/l    | Bacteria             | 30 min        |                                |   |
| 1,4-Naphthalenedione 130-15-4 | EC50       | 0,011 mg/l | Algae                | 72 h          | Dunaliella bioculata           | OECD Guideline 201 (Alga, Growth Inhibition Test)               |

**12.2. Persistence and degradability****Persistence and Biodegradability:**

The product is not biodegradable.

| Hazardous components CAS-No.  | Result | Route of application | Degradability | Method  |
|-------------------------------|--------|----------------------|---------------|---|
| Cumene hydroperoxide 80-15-9  |        | no data              | 0 %           | OECD Guideline 301 B (Ready Biodegradability: CO2 Evolution Test) |
| 1,4-Naphthalenedione 130-15-4 |        | no data              | 0 - 60 %      | OECD 301 A - F  |

**12.3. Bioaccumulative potential / 12.4. Mobility in soil****Mobility:**

Cured adhesives are immobile.

**Bioaccumulative potential:**

No data available for the product.

| Hazardous components<br>CAS-No.  | LogPow | Bioconcentration<br>factor (BCF) | Exposure<br>time | Species     | Temperature | Method  |
|----------------------------------|--------|----------------------------------|------------------|-------------|-------------|---|
| Cumene hydroperoxide<br>80-15-9  |        | 9,1                              |                  | calculation |             | OECD Guideline 305<br>(Bioconcentration: Flow-<br>through Fish Test)<br>not specified |
| Cumene hydroperoxide<br>80-15-9  | 2,16   |                                  |                  |             |             |   |
| 1,4-Naphthalenedione<br>130-15-4 | 1,71   |                                  |                  |             |             | not specified   |

#### 12.5. Results of PBT and vPvB assessment

| Hazardous components<br>CAS-No. | PBT/vPvB  |
|---------------------------------|---|
| Cumene hydroperoxide<br>80-15-9 | Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria. |

#### 12.6. Other adverse effects

No data available.

### SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

Product disposal:

Collection and delivery to recycling enterprise or other registered elimination institution.

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

## SECTION 14: Transport information

**14.1. UN number**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.2. UN proper shipping name**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.3. Transport hazard class(es)**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.4. Packing group**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.5. Environmental hazards**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.6. Special precautions for user**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

**14.7. Transport in bulk according to Annex II of Marpol and the IBC Code**

not applicable

## SECTION 15: Regulatory information

**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content < 3 %  
(2010/75/EC)

**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.

## SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H242 Heating may cause a fire.  
H301 Toxic if swallowed.  
H302 Harmful if swallowed.  
H311 Toxic in contact with skin.  
H312 Harmful in contact with skin.  
H314 Causes severe skin burns and eye damage.  
H315 Causes skin irritation.  
H317 May cause an allergic skin reaction.  
H319 Causes serious eye irritation.  
H330 Fatal if inhaled.  
H331 Toxic if inhaled.  
H335 May cause respiratory irritation.  
H373 May cause damage to organs through prolonged or repeated exposure.  
H400 Very toxic to aquatic life.  
H410 Very toxic to aquatic life with long lasting effects.  
H411 Toxic to aquatic life with long lasting effects.  
H412 Harmful to aquatic life with long lasting effects.

### Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**