



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.triplite.com

- Tripp Lite P568-Series HDMI cabling recommended for maximum distance and best performance and required for distances over 75 ft.
- Most installations are self powered. On the rare occasion where additional power is needed, power can be added via a USB Micro-B port on the extender. Connect a USB Micro-B cable between the port and a USB wall charger, monitor or computer. Cable and charger not included.

## HDMI Signal Booster – F/F, 1920 x 1200 (1080p) @ 60 Hz, Up to 125 ft., TAA

MODEL NUMBER: **B122-000-60**



In-line HDMI signal extender boosts a high-quality HDMI audio/video transmission up to 125 ft. from the source device.

### Features

**HDMI Booster Extends High-Definition 1080p Video and Digital Audio Signals up to 125 ft.** Don't let HDMI's 16-foot distance limitation limit your audio/video application. This in-line HDMI signal extender boosts your 1080p transmission up to 125 feet from the source device without a drop in signal quality. This gives you the flexibility to hide your Blu-ray player or media server away in a secure, remote location for controlled access, while delivering video to an HDMI display somewhere else. The B122-000-60 is recommended for digital signs or video presentations in schools, conference rooms, retail displays, trade show booths and anywhere else you need to display high-definition video.

**Meets HDMI Industry Standards to Deliver High-Definition Results** This HDMI signal booster supports computer video resolutions up to 1920 x 1200 and HD resolutions up to 1080p at 60 Hz, as well as 36-bit Deep Color (12 bits per channel). It also supports DTS-HD, Dolby TrueHD and 7.1-channel surround sound to ensure your speakers deliver rich, clear audio to match the video quality.

**Greater Distance Gives You More Freedom in Placing Your Source and Display Devices** This low-profile HDMI booster is designed for use with Tripp Lite P568-Series HDMI cables (sold separately). Connect the longer cable (up to 125 feet) to your source device, such as a Blu-ray player or computer, to transmit a 1080p (60 Hz) signal. The shorter cable connects the B122-000-60 and the HDMI display device, and must be no longer than 16 feet. For distances over 75 feet, a 24 AWG HDMI cable, such as Tripp Lite's P568-100-HD, is required. In addition, this unit can also extend a 3D signal up to 125 feet (24 AWG cable required for 3D transmissions over 50 feet).

**Ready to Use Right from the Package, So You Can Plug and Play Immediately** The plug-and-play unit requires no software, drivers or (usually) external power. In the extreme case that external power is needed, connect a USB Micro-B cable (such as Tripp Lite's UR050-Series) between the unit's USB Micro-B port and a USB wall charger or USB port on your monitor or computer. With its low-profile design, the B122-000-60 is easy to stow in your laptop bag and carry to school, the office or the latest trade show.

**TAA-Compliant for GSA Schedule Purchases** The B122-000-60 is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

**3-Year Warranty** The B122-000-60 is backed by a 3-year warranty, ensuring reliability and performance.

### Highlights

- Allows you to store expensive source device in a secure location for controlled access
- Delivers HD picture quality at resolutions up to 1920 x 1200 (1080p) @ 60 Hz
- Supports DTS-HD, Dolby TrueHD and 7.1 surround sound for rich, clear audio
- Compact unit fits easily into briefcase or laptop bag for instant use anywhere
- Plug-and-play operation with no software required for easy, immediate installation

### Applications

- Digital signage in office lobbies, churches, retail stores, restaurants and hotels
- Video presentations in conference rooms, lecture halls, classrooms and trade shows
- Home theater systems where the source devices are secured in a closet or other room

### System Requirements

- Source device with HDMI output
- Display device with HDMI input
- 24 AWG HDMI cable required for distances over 75 ft. (Tripp Lite P568-Series)

### Package Includes

- B122-000-60 HDMI Signal Booster
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

## Specifications

OVERVIEW	
UPC Code	037332225115
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	4.06 x 11.68 x 15.75
Shipping Dimensions (hwd / in.)	1.60 x 4.60 x 6.20
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	150
Max 480P Range (ft)	154
Max 1440 x 900 Range (ft)	150
Max 1080i Range (ft)	150
Max 1080P Range (ft)	150
Max 480i Range (ft)	154
Max 640 x 480 Range (ft)	150
Max 800 x 600 Range (ft)	150
Max 1600 x 1200 Range (ft)	150
Max 720P Range (ft)	150
CONNECTIONS	
Ports	1
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	HDMI
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>