

SmartRack 2U Vertical Wall-Mount Rack Bracket

MODEL NUMBER: **SRWALLBRKT2U**



2U wall-mount bracket allows vertical installation of a 2U rack-mount device up to 175 lb.

Description

The SRWALLBRKT2U SmartRack® 2U Vertical Wall-Mount Rack Bracket is recommended for home offices and small businesses with rack-mount equipment that doesn't need to be secured and no room on the premises for a standard 19-inch server rack.

Made from heavy-duty cold-rolled steel with a durable black powder-coated finish, this 2U rack-mount bracket easily attaches to the wall of your back office or closet with user-supplied hardware. Wall-mounting holes are spaced 16 inches part to match standard wall-stud placement. Or you can install the bracket horizontally beneath a desk or workbench for instant access.

Use the included hardware to attach your 2U rack-mount equipment, such as a network switch or UPS system, to the steel bracket's rails. Its maximum load capacity is 175 pounds. Connected equipment hangs flush against the wall, allowing you unrestricted access. The SRWALLBRKT2U is compatible with most EIA-standard 19-inch two-post rack equipment.

Features

2U Wall-Mount Bracket Allows Vertical Mounting in a Closet or Back Office

- Recommended for home offices and small businesses with no room for standard 19 in. rack
- Provides open, unrestricted access to equipment and cabling
- Maximum load capacity of 175 lb.
- Cold-rolled steel construction with black powder-coated finish designed for long life
- Ships fully assembled for quick installation

Attaches to the Wall with User-Supplied Hardware

- Wall-mounting holes spaced 16 in. apart for standard wall stud placement

Highlights

- 19-inch wall-mount rack with maximum load capacity of 175 lb.
- Provides open, unrestricted access to equipment and cabling
- Made from cold-rolled steel with black powder-coated finish
- Equipment-mounting hardware included
- Compatible with most EIA-standard 19 in. 2-post rack equipment

Package Includes

- SRWALLBRKT2U SmartRack 2U Vertical Wall-Mount Rack Bracket
- (12) M6 screws
- (12) M6 cup washers
- (12) M6 cage nuts
- Installation guide



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Also mounts horizontally beneath a desk or workbench
- Component hangs flush against the wall for unrestricted out-of-the-way access

Compatible with EIA-Standard 19 in. 2-Post Rack Equipment

- Hardware included for mounting 2U rack equipment
- Rails support square-hole mounting

Specifications

OVERVIEW	
UPC Code	037332203199
Rack Type	Open-Frame
PHYSICAL	
Color	Black
Maximum Device Depth (cm)	121.92
Maximum Device Depth (in.)	48
Maximum Device Depth (mm)	1,219
Maximum Weight Capacity (kg)	79
Maximum Weight Capacity (lbs.)	175
Rack Height	2U
Shipping Dimensions (hwd / cm)	15.01 x 55.50 x 21.49
Shipping Dimensions (hwd / in.)	5.91 x 21.85 x 8.46
Shipping Weight (kg)	1.80
Shipping Weight (lbs.)	3.97
Unit Dimensions (hwd / cm)	10.57 x 50.01 x 10.54
Unit Dimensions (hwd / in.)	4.16 x 19.69 x 4.15
Unit Weight (kg)	1.20
Unit Weight (lbs.)	2.65
CERTIFICATIONS	
Approvals	EIA-310-D, IEC 60297-3-100, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>