

STI Enviro Stopper®



KEY FEATURES

General Information

- Protective cover is ideal for extending the life and reliability of devices exposed to harsh environments.
- Three year guarantee against breakage of polycarbonate in normal use (one year on electromechanical and electronic components).

Design

- Cover, back box and sealed mounting plate achieves IP66 (back box) and IP56 (cover) rating.

Construction

- Tough polycarbonate housing can withstand the severest of knocks.

Installation

- Ideal for use in wet or wash down areas, overall rating of IP56/IP66 for the back box.
- Can accommodate a standard European call point or switch.
- Typical working properties of polycarbonate are -40° to 121°C (-40° to 250°F).

Electronics

- Available with or without a 95 dB integral sounder, powered by a 9V PP3 battery (included).

Options

- One breakseal is supplied with each model. Additional breakseals are available for added security.
- Available in a range of colours.
- Custom labelling available.

PRODUCT OVERVIEW

A protective cover that is ideal for extending the life and reliability of devices exposed to harsh environments. It offers protection to manual call points and switches against dust and water ingress both outside and inside, as well as preventing tampering, vandalism and damage from accidental or malicious operation.

HOW IT WORKS

Easy to install, the Enviro Stopper consists of a clear, tamperproof, tough polycarbonate cover and back box that can accommodate a standard European call point or switch. When the cover is closed, the unit is sealed and achieves a rating of IP66/56, preventing dust, grime and water getting to the device.

STI Enviro Stopper®

Dimensions and Technical Information

BUILD YOUR OWN MODEL

STI-1

Cover Options:
 3 = Dome Cover
 4 = Low Profile Cover*
 * Only available with hood/sounder option "0"

Mounting Options:
 6 = European enclosed back box & sealed mounting plate
 7 = European enclosed back box & open mounting plate
 • with 20mm entry point

Hood/Sounder/Wireless Options:
 0 = No label hood
 1 = Label hood without sounder**
 2 = With sounder**
 3 = With sounder & remote contact & power**
 ** All colours except NC

Special Electronics:
 0 = None

Hood/ Sounder Colour & Label Options:

Fire Label	NW = White
FR = Red - Fire Label	NY = Yellow
Emergency Exit Label	Custom Label*
EG = Emergency Exit Label	CK = Black*
	CB = Blue*
	CG = Green*
	CR = Red*
	CW = White*
	CY = Yellow*
No Label	
NK = Black	
NB = Blue	
NC = Clear	
NG = Green	
NR = Red	

*Must provide custom label wording (2 lines, 30 characters per line including spaces)

MODELS AVAILABLE

STI-13610FR Enviro Stopper, (EU enclosed plate & frosted back box) without integral sounder, with fire label.

STI-13620FR Enviro Stopper, (EU enclosed plate & frosted back box) with integral sounder, with fire label.

Accessories:

- STI/BS** Break Seals (Quantity. 10)
- KIT-319** Wiring harness for remote power
- KIT-EA135** Servicing pin
- CKS001** Replacement Sounder Unit

Options:

COLOURS AVAILABLE Black, blue, green, red, white or yellow (to specify colour refer to Build Your Own Model)

NB:


The Enviro Stopper is supplied in red with operating instructions: 'IN CASE OF FIRE - LIFT COVER BREAK GLASS'.
 Alternative and custom markings available.

APPROVALS

- ADA Compliant
- Cover option '3' only has been tested and approved or listed by:
- UL/CUL Listed No. S2466

Back box, open mounting plate - IP Rating, 56

Back box, sealed mounting plate - IP Rating, 66



Safety Technology International

Taylor House
 34 Sherwood Road
 Bromsgrove
 Worcestershire
 B60 3DR, England

Tel: +44 (0)1527 520 999
 Fax: +44 (0)1527 501 999
 info@sti-emea.com
 www.sti-emea.com

2306 Airport Road
 Waterford, Michigan
 48327, USA

Tel: 248-673-9898
 Fax: 248-673-1246
 Toll-free: 0800-888-4784
 info@sti-usa.com
 www.sti-usa.com