

Tsunami® MP-10250 BeamX Series

Extending the Range of High Bandwidth Services




The Tsunami®MP-10250 BeamX product family uses a beam steering antenna and a secondary, look-ahead scan radio to avoid interference and maximize the use of available radio spectrum. The Tsunami® 10250, builds on the successful 10000 product line, and is extremely robust in the face of high ambient RF interference, delivers more Mbps and opens up additional 5GHz spectrum.



- Point-to-Multipoint base station and subscriber unit that delivers up to 866 Mbps data rate and covers distances up to 10 miles (16 km)
- AES 128 encryption, Radius authentication, and highly-secure remote management via SSL/TLS1.2, SSH, and SNMPv3
- Service flow based QoS with deep packet inspection (DPI) to ensure critical data arrives with priority
- Built-in feature-rich network protocols for IPv4 and IPv6 bridging, routing and gateway functionality

Proxim SmartScan™

- Performs background analysis of the full RF spectrum and creates channel availability tables to allow an immediate switch to a free channel in case of weather radar detection or interference
- By removing the initial transmission delay, SmartScan makes DFS channel more efficient
- It also opens access to the 5.600-5.650 GHz sub-band and enables effective use of up to 355 MHz of DFS spectrum




About Proxim Wireless


Proxim Wireless is a pioneer and global leader in advanced Wi-Fi, point to point, and point to multipoint outdoor wireless systems that deliver high performance and high availability communications.


With over 30 years of wireless experience, Proxim is recognized for its unparalleled reliability, superior performance and drive for innovation.

BeamX[™] Antenna

- Smart antenna delivering a 17° beam that electronically steers itself to the remote subscriber unit over a 60° sector, to limit interference from nearby RF sources
- By improving the radio Signal to Noise Ratio (SNR), BeamX enables higher modulations and thus improves throughput
- BeamX speeds up deployment by removing the antenna alignment phase.
 Roughly aim at the remote end, and the BeamX technology does the fine-tuning, optimizing SNR







Rugged and Reliable

The Tsunami® MP-10250 BeamX product is designed for harsh environments, and is fully IP67 rated, and will deliver years of reliable service in conditions that include, high winds, high salt, and high-temperature extremes.

Key Technologies

The Tsunami® MP-10250-BeamX device supports the following features for applications that include last mile access or video surveillance, both of which need prioritized and continuous high-speed broadband wireless access:

Proxim WORP®

Combines network access control, data scheduling, advanced QoS, and encryption to ensure highly efficient and secure data transmission.

Proxim ClearConnect™

A suite of interference mitigation technologies ensuring robust and reliable communications in high-density wireless deployments.

Proxim SmartConnect™

Delivering exceptional performance in noisy RF locations by combining a beam steering antenna with a secondary look ahead scan radio to seek, manage, and select the best channel.

Product Line Compatibility

- Tsunami® MP-10250-BSX Connects to all existing Tsunami® MP/XP 10100, MP-10100L, MP-8200, MP-820 and MP-830 products
- Tsunami® MP-10250-SRX only connects to Tsunami® MP-10250-BSX
- Fully integrates within ProximVision® Advanced
 Cloud Based Carrier Management System and Controller

Multi-Language Support

Web Interface available in English, French, Spanish and Chinese

Specifications

PRODUCT MODELS		PART NUMBERS	
MP-10250-BSX	Tsunami® MP 10250 Base Station Unit, 867 Mbps, MIMO 2x2, 16 dBi BeamX antenna, Scan radio	901-00291 MP-10250-BSX-US 901-00292 MP-10250-BSX-WD	
MP-10250-SRX	Tsunami MP 10250 Subscriber Unit, 867 Mbps, MIMO 2x2, BeamX antenna, SmartScan radio	901-00340 MP-10250-SRX-US 901-00341 MP-10250-SRX-WD	
INTERFACES			
WIRED ETHERNET WIRELESS PROTOCOL	Two auto MDI-X RJ45 10/100/1000Mbps Ethernet (Port #1 with PoE in & Data, Port #2 with PoE out & Data) WORP® (Wireless Outdoor Router Protocol)		
RADIO & TX SPECS			
MIMO MODULATION FREQUENCY CHANNEL SIZE DATA RATE TX POWER TX POWER CONTROL	2x2:2 and 0x2:2 (scan radio) OFDM with BPSK, QPSK, QAM16, QAM64, QAM256 4.900 – 5.850 GHz (Subject to Country Regulations) 80 MHz, 40 MHz and 20 MHz MCS 0 to 9 with Dynamic Data Rate Selection Up to 28 dBm (dual chain) 0 - 27 dB, in 1 dB steps. Automatic TPC with configurable EIRP limit		

	80 MHz	40 MHz	20 MHz	SCAN RADIO	
TX POWER (dual RF)	MCS0: 28 dBm	MCS0: 28 dBm	MCS0: 29 dBm	N/A	
	MCS9: 21 dBm	MCS9: 22 dBm	MCS8: 25 dBm		
XX SENSITIVITY (Per=10%)	MCS0: -89 dBm	MCS0: -93 dBm	MCS0: -94 dBm	N/A	
	MCS9: -68 dBm	MCS9: -71 dBm	MCS8: -74 dBm		
THROUGHPUT	Up to 672 Mbps	Up to 324 Mbps	Up to 137 Mbps	N/A	
OTHER				on (DFS) based on radar signature	
, <u>.</u>	Automatic Transmit Power Contr			on (b) of basea on radar signature	
ANTENNA - Integrated 2x2 MIMC	Beam Steering Antenna:				
Beam Width	17° spanning over ± 30° sector				
Receive Gain	16 dBi (11 dBi before 5.150 GHz)				
Transmit Gain	20 dBi (11 dBi before 5.150 GHz				
MANAGEMENT					
REMOTE SNMP	Telnet and SSH, Web GUI and SSL, TFTP, SNMPv3				
OTHER	SNMP v1-v2c-v3, RFC-1213, RFC-1215, RFC-2790, RFC-2571, RFC-3412, RFC-3414, Private MIB Syslog, sFlow™ agent, SNTP and local time, Spectrum analyzer				
Multi-Language Support	Web Interface available in English, French, Spanish and Chinese				
SYNCHRONIZATION					
	Pass-trough SyncE and Precisio	n Time Protocol (IEEE 1588v2) Et	hernet Synchronization		
SECURITY					
ENCRYPTION	AES 128				
AUTHENTICATION	Internal MAC Address Control List, Radius based Authentication (with VLAN and QoS provisioning)				
QoS					
Asymmetric Bandwidth Control	Asymmetric UL/DL committed and maximum information rate per service flow				
Packet Classification	802.1p priority, IPTOS, VLAN ID, IP addresses, ports, Ethernet addresses, IP protocol, and EtherType				
Capabilities Scheduling	Best Effort, Real Time Polling Services				
NETWORK	· · · · · · · · · · · · · · · ·				
MODES	Bridging Routing (RIP v2 and IP	tunneling)			
P STACK	Bridging, Routing (RIP v2 and IP tunneling) IPv4 and IPv6 simultaneously				
GATEWAY FEATURES	DHCP Server & relay, NAT with Std ALGs, PPPoE end point with Proxy DNS				
/LAN	-		xed mode. QinQ double tagging		
POWER	INP	UT		DUTPUT	
	36 to 57 VDC via Ethernet port1 (Power over Ethernet)		48 to 57 VDC – 25 Watt on Ethernet port2 (PoE – software		
	12 VDC via Access port		controlled) 12 VDC on Access port		
	Power should not be provided simultaneously on both ports				
POWER CONSUMPTION					
	30 Watt typical, 40 Watt maximu	ım			
ENVIRONMENTAL SPECS	OPERATING TEMPERATURE	STORAGE TEMPERATURE	HUMIDITY - IP RATING	WIND LOADING	
	-40° to 60°C	-50° to 70°C	100% relative humidity - IP67	200 km/h (125 mph)	
	(-40° to 140° Fahrenheit)	(-58° to 158° Fahrenheit)			
PHYSICAL SPECS	DIMENSIONS PACKAGED	DIMENSIONS UNPACKAGED	WEIGHT (PACKAGED)	WEIGHT (UNPACKAGED)	
	18.46 x 7.05 x 21.57 in	14 x 14 x 3.40 in	13.67 lbs (6.2 kg)	7.27 lbs (3.3 kg)	
MP-10250-BSX/SRX	1100 170 510	(371 x 371 x 85 mm)			
MP-10250-BSX/SRX	(469 x 179 x 548 mm)	(371 × 371 × 03 11111)			
MP-10250-BSX/SRX SAFETY STANDARDS	(469 x 1/9 x 548 mm)	(3/1/(3/1/(3/1111))			
	(469 x 1/9 x 548 mm) UL 60950, CAN/CSA-C22.2 No	,	(part -1 and -22)		
		,	(part -1 and -22)		
AFETY STANDARDS		,	(part -1 and -22)		

PACKAGE CONTENTS	
	 One Tsunami® MP-10250-BSX/SRX with integrated BeamX antenna and scan radio One power injector and country specific power cord One Connector weatherproofing kit (Includes all recommended weatherproofing material) One Wall / Pole mounting kit One Antenna alignment (RJ11) dongle One Grounding kit One Quick Installation Guide
MTBF & WARRANTY	
	MTBF over 250 000 hours & 2-year warranty with ServPak Extended Support available

© 2019 Proxim Wireless Corporation. All rights reserved. Proxim is a registered trademark and the Proxim logo and Tsunami® are trademarks of Proxim Wireless Corporation.

All other trademarks mentioned herein are property of their respective owners. Specifications are subject to change without notice.