



# DVI/HDMI over IP Gigabit LAN Ethernet Extender Kit, RS-232 Serial and IR Control, 1080p @ 60 Hz, 328 ft. (100 m), TAA

MODEL NUMBER: **B160-101-HDSI**



Converts HDMI or DVI audio/video to an IP-based signal that is transmitted point-to-point to a display 328 ft. away via Cat5e/6 cable or through a dedicated Ethernet network switch.

## Description

The B160-101-HDSI HDMI over IP Gigabit LAN Ethernet Extender Kit extends and distributes HDMI or DVI audio/video, RS-232 serial and IR (infrared) remote signals from the source to the display located up to 328 feet (100 meters) away, which is more than 200 feet farther than a traditional Cat5e/6 solution. By adding a chain of low-cost unmanaged network switches, such as Tripp Lite's NG5, you can continue extending the distance between source and display up to 328 feet per switch.

Create a multi-in, multi-out installation with up to 64 transmitters and 255 receivers\* by including dedicated managed Ethernet network switches\*\* with Internet Group Management Protocol (IGMP), such as Tripp Lite's NSS-G16D2. With a compatible B160-Series receiver, you can send the HDMI or DVI video source (a DVI adapter cable is included) to any analog or digital display, including VGA and DisplayPort™, allowing you to mix and match technologies and use existing monitors. The IGMP-enabled switch will let you manage all connections for centralized control over which sources show on which displays.

The B160-101-HDSI supports video resolutions up to 1920 x 1080 (1080p) at 60 Hz in a point-to-multipoint switch installation. It extends IR control signals that control a source, such as a Blu-ray™ player, to a remote display, as well as RS-232 signals at serial baud rates up to 57600 Bps. The transmitter and receiver units mount to a wall, rack or pole using the including hardware.

\*Unmanaged switch installations are limited to two transmitter units. Number of receivers is limited to number of ports remaining on unmanaged switch.

\*\*B160-Series designed for use with dedicated network switch. Connecting to a switch used with other networking equipment will result in degraded or non-functional performance.

## Features

### Extends and Distributes HDMI/DVI A/V, Serial and IR Control Signals over Cat5/6 Cabling

- Converts audio/video to an IP-based signal that is transmitted point-to-point to a display 328 ft. away
- Add low-cost network switches between transmitter and receiver to continue extending distance up to

## Highlights

- Units connect point-to-point without a switch up to 328 ft.
- Supports video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- HDMI output on transmitter for connecting local display
- Plug and play—no software or drivers required

## Package Includes

- Transmitter unit
- Receiver unit
- (2) External power supplies (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V 2A)
- Plug adapters for U.S., U.K., Europe and Australia
- IR-In cable
- IR-Out cable
- (2) HDMI to DVI adapter cables
- Mounting hardware
- Owner's manual



328 ft. per switch

- HDMI output on transmitter for connecting a local display

#### Create a Multi-In, Multi-Out Installation Using B160-Series Transmitters and Receivers

- Connect up to 64 transmitters and 255 receivers through multiple dedicated managed network switches
- IGMP-enabled switches allow centralized control over which sources show on which displays
- Video source can be sent to any analog or digital display, so you can mix and match technologies and use existing monitors

#### Enhanced Technical Features

- Supports video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Uses H.264 video compression standard
- Transmits on 20–60 kHz IR frequency
- Extends IR control signals that control a source from a remote display
- Supports RS-232 serial baud rates up to 57600 Bps
- HDCP and 3D compatible

#### Plug-and-Play Functionality

- No software or drivers required
- Hardware included for mounting on wall, rack or pole

#### TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
UPC Code	037332196781
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1.0A
External Power Supply Output Specs (V / A)	5V / 2A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.4
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve



External Power Supply Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
External Power Supply Certifications	BSMI; CB; CE; FCC; GS; PSE; RCM; UL; cUL
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	RJ45 Output (Green / Power, Orange / Signal), Channel Signal (Red), Power (Green)
<b>PHYSICAL</b>	
Color	Black
Material of Construction	SECC
Rackmountable	Yes
Receiver Unit Dimensions (hwd / in.)	1.2 x 5 x 3.9
Receiver Unit Weight (lbs.)	0.2
Shipping Dimensions (hwd / in.)	3.20 x 5.70 x 11.50
Shipping Weight (lbs.)	3.10
Transmitter Unit Dimensions (hwd / in.)	1.2 x 5 x 3.9
Transmitter Unit Weight (lbs.)	0.2
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14 to 167 F (-10 to 75 C)
Storage Temperature Range	-4 to 176 F (-20 to 80 C)
Relative Humidity	0% to 85%, Non-Condensing
BTUs	34 BTU/Hr
Power Consumption (Watts)	10
<b>COMMUNICATIONS</b>	
Signal Range (ft.)	328
Signal Range (m)	100
Latency	2-3 seconds
<b>CONNECTIONS</b>	
Ports	1
Side A - Connector 1	(2) HDMI (FEMALE)
Side A - Connector 2	3.5MM (FEMALE); DB9 (FEMALE); RJ45 (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	3.5MM (FEMALE); DB9 (FEMALE); RJ45 (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	



Max Supported Video Resolution	1920 x 1080 (1080p) @60Hz
HDMI Specification	1.4
HDCP Specification	1.4
Audio Specification	2 Channel Surround Sound
Driver Required	No
Recommended Category Cable	N202-Series Cat6 Patch Cable
Max Supported Color Depth	24-bit True Color
IR Remote Extension Support	Yes
RS-232 Serial Extension Support	Yes
3D Video Supported	Yes
Technology	DVI; HDMI; IR; Serial (RS232); A/V over IP
<b>CERTIFICATIONS</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>