



IDEAL NETWORKS



NavITEK IE

Copper and Fiber Troubleshooter
for PROFINET Industrial Ethernet Networks

NavITEK IE

Copper and Fiber
Troubleshooter for
PROFINET Industrial
Ethernet Networks



The NavITEK IE is a tester for commissioning, preventative maintenance and troubleshooting of PROFINET Industrial Ethernet networks as well standard Ethernet IP networks.

Designed to simplify the process, the NavITEK IE identifies network nodes and configuration without requiring a PC and speciality software.


An easy to understand system health check pinpoints potential issues before they become network failures. Automatically discover cable, network or device configuration/faults with the touch of a button.

To prove the network has been commissioned successfully, NavITEK IE provides professional PDF reports that can be shared with colleagues and clients using the free IDEAL AnyWare™ mobile app.

What does the NavITEK IE do?

- ✓ **Pinpoint cable faults** on copper and fiber cabling
- ✓ **Easily configure nodes** to resolve connectivity issues
- ✓ **Prevent network failures** with the health check feature
- ✓ **Locate hard to find devices** using the device blink feature
- ✓ **Find mis-configured devices** using the NetMAP comparison tool
- ✓ **Find rogue devices** using the 48 hour event log
- ✓ **Create professional PDF reports** for your clients
- ✓ **Send reports anywhere** using the free IDEAL AnyWARE app

Where can I use the NavITEK IE in my network?



Cable Testing


Pinpoint Cable Faults and Minimize Downtime

One of the main causes to network downtime is caused by cable faults. The NaviTEK IE has a series of advanced wiremap tools for PROFINET and standard Ethernet IP network cabling:

Copper Cabling

Using the RJ45 or M12 interfaces the NaviTEK IE offers a wiremap specifically designed for PROFINET Industrial Ethernet networks and Standard Ethernet networks.

- Displays the correct wiring colors for the protocol used
- Supported cable types – 4 twisted wires / 2 twisted pairs / 4 twisted pairs
- Measures the cable length
- Determine where and what the cable fault is including split pairs/opens/shorts/miswires.




2 x M12 D connector cables supplied as standard.
M12 X connectors available as accessories.

Fiber Cabling



Using the optional SFP module the NaviTEK IE measures optical power and provides a good, satisfactory or poor indication of received power

- Poor power levels can indicate bad SFPs, dirty connectors or damaged cabling
- An optional 100Mb/s SFP media converter is available to access a 100Mb/s optical link
(See back page for details)



Why is NaviTEK IE better than other cable testers?

- **Accurate distance to fault** using Time Domain Reflectometry (TDR)
- **Tests every wire in the data cable not every pair** to help isolate issues that other testers cannot find
- **Supports standard and non-standard cabling** as the wiremap can be customized to your specific cabling




Network Testing

Correct network issues using the discovery and configuration tools

The NaviTEK IE will discover the following list of faults:


- Incorrect device names
- Duplicate IP addresses
- Packet loss

If node configuration faults are found, easily correct them using the simple configure tool.



S	IP Address
1	192.168.1.55
2	192.168.1.19
3	192.168.1.4
4	192.168.1.48

DETAILS MAC NODE SETUP



Node Setup

Set IP: [dropdown menu]

Set Name: [dropdown menu]

Factory Default


Flash LEDs

Set Subnetmask: 255.255.255.0

APPLY

Discover mis-configured devices that cause a network conflict


The NETMAP comparison tool can also perform a scan of the entire network to identify all active devices and save this for comparison to future NETMAPS. This enables easy identification of new or removed network devices, incorrectly configured devices or configuration changes, such as those caused by automatic firmware updates.



Map A (Ref): 0001.1.xml

Map B: 0002.1.xml

Nodes: 1 same, 3 mismatch, 1 new, 1 missing




S	MAC
!	28:63:36:e3:83:2f
!	28:63:36:e3:82:a8
!	20:87:56:64:c3:e0
!	28:63:36:fa:fe:2f
✓	28:63:36:e3:83:2f
+	28:63:36:e3:82:a8

DETAILS

Find intermittent issues with the event log

The NaviTEK IE will record key network errors for up to 48 hours including the following parameters. This will help determine if a problem is with the cabling, node, PLC or the network configuration.

- Device status
- Input/output errors



Error Log

Error Event Logging

Duration: 24 Hours

Node Name: et200sp50


Node IP Address: 192.168.1.50

Time Remaining: 10:23:10

Event Count: 36

Event Time: March 1 2010 00:25 51

STOP ERROR DETAILS



Error log

Error Event Details

I/F Port: 1

Event Time: March 1 2010 00:27 28

Input Packets: 1379989

Input Errors: 8

Output Packets: 1256987


Output Errors: 12

Node Status: Up

Display and validate network node details quickly


The NaviTEK IE uses the following protocols to display the most important network node parameters.

- Discovery and Control Protocol (DCP)
- Simple Network Management Protocol (SNMP)
- Link Layer Discovery Protocol (LLDP)



Node: et200sp50: Port In
ErroredPackets: 0
Utilisation (%): 0
Traffic (Mb/s): 0
Unicast Packets: 9,692
Multicast Packets: 170,187
Discarded Packets: 0
Unknown Protocols Packet: 17,549

STATS OUTPUT



Node#4
Vendor Name: xxxx (002a)
Device ID: 010d
System Description: Siemens, SIMATIC S7, CPU-1200
Serial Number: S C-K1LL1636
Firmware Version: 4.2.1
Hardware Version: 6
Order ID: 6ES7 211-1AE40-0XB0

I/F PORTS ERROR LOGGING

Perform a health check to identify issues before network failures occur

The health check feature provides a quick indication of how each of your devices are performing with an easy to understand traffic light system. By clicking on each device you will see why your device is categorized as amber or red and corrective action can be taken.

HEALTH CHECK KEY

Green indication

No abnormal events detected

- No errors
- No alarms
- No duplicated IP address or name
- Link traffic load below 10%

Amber indication

No critical events detected and device is still operational

- Packet errors occur but at an acceptable limit
- Link load 10% - 50%
- Another identical device model found but has different firmware / hardware version
- Device speed is 10Mb/s
- Device port half duplex

Red indication

Critical events detected and device may not be operational


- No or duplicate name set
- Duplicated or wrong IP address set
- No or wrong device subnet mask set
- Device communication failure
- Device IP outside the tester subnet mask
- Packet errors exceeding acceptable limits
- Link load > 50%

PROFINET 06:40	
Nodes	
S	IP Address
1	192.168.1.55
2	192.168.1.19
3	192.168.1.4
4	192.168.1.48
DETAILS MAC NODE SETUP	

Node #1 10:21	
Name of Station	pgr17-02
IP Address	169.254.81.27
NetMask	255.255.0.0
Gateway	0.0.0.0
MAC Address	80:ce:62:a3:f1:b2
Type of Station	SIMATIC-PC
Device Role	0
I/F PORTS	

Locate hidden or poorly labelled devices

Quickly identify a specific device with the NavITEK IE by flashing its LEDs.



NavITEK IE

Ports for copper, fiber

Save money by employing a single device to test entire networks

User-exchangeable RJ45 Inserts

Field replaceable RJ45 contacts reduce downtime

Virtual keyboard

Work efficiently, quickly and easily input data

Autotest function

Predefine common tests under one Autotest button to improve productivity

Share test data

Provides mobile device connectivity using USB Wi-Fi adapter and free IDEAL AnyWARE app



Color touch screen

Reduce the chance of false readings with a clear, bright backlit screen

Durable rubber molded housing

Rubberized housing protects the tester from accidental damage and reduces cost of ownership

A choice of power supply

Choose between mains power or rechargeable batteries to suit your environment



Test Reporting

NavITEK IE automatically generates test reports in PDF or CSV format.

The summary page of each report can be customized to include logo, company and operator details. Choose between 3 different reports than can show either passed, failed or all test reports in each report:

- Summary
- Brief
- Full

NavITEK IE Test Report

Job Name: MyJob
Date Tested: January 12 2019
Time Tested: 16:25

Owner: JOHN SMITH
Company: Automation Ltd
Address 1: Wind Industrial Estate
Address 2: George Street
City: Manchester
State:
Zip: M20 7JG
Country: UK
Phone1: 01490 67890
Phone2: 0750052321

PASS
0003
ESN: 001606-887995

Port	Line Rate	Auto	Static	Results
Ethernet	Auto	Auto	Static	192.168.1.20

NavITEK IE Test Report

Job Name: MyJob
Date Tested: January 12 2019
Time Tested: 16:25

Owner: JOHN SMITH
Company: Automation Ltd
Address 1: Wind Industrial Estate
Address 2: George Street
City: Manchester
State:
Zip: M20 7JG
Country: UK
Phone1: 01490 67890
Phone2: 0750052321

Model: NavITEK IE
Software Version: 1.0.32 08/01/2019
Firmware Version: 0.1
Hardware Version: 1.0

Test Name	Test Result	Date	Time	Port	Switch I/D	Port ID
0001	Pass	01/12/2019	16:19	Ethernet	Switch	
0002	Pass	01/12/2019	16:21	Ethernet	Switch	
0003	Pass	01/12/2019	16:23	Ethernet	Switch	
0004	Pass	01/12/2019	16:26	Ethernet	Switch	
0005	Pass	01/12/2019	16:42	Ethernet	Switch	
0006	Pass	01/12/2019	16:54	Ethernet	Switch	
0007	Pass	01/12/2019	17:08	Ethernet	Switch	

NavITEK IE Test Report

Job Name: MyJob
Date Tested: January 12 2019
Time Tested: 16:54

Owner: JOHN SMITH
Company: Automation Ltd
Address 1: Wind Industrial Estate
Address 2: George Street
City: Manchester
State:
Zip: M20 7JG
Country: UK
Phone1: 01490 67890
Phone2: 0750052321

FAIL
0006
ESN: 001606-887995

Length: 29m

Pair (m)

1-2 25
3-6 29
4-5 -
7-8 -



NP 3C 72

Near Pin1 Shorted to Near Pin2
Far Pin1 Shorted to Far Pin2
Shield is Open

Send test reports from anywhere using the free app



IDEAL
AnyWARE



Step 1

Test

- Create job folder
- Enter job site information
- Perform autotest on copper/fiber cabling and copper/fiber networks

Step 2

Connect

- Activate NaviTEK IE wireless hotspot
- Connect your mobile phone or tablet with the IDEAL AnyWARE App
- Transfer test reports to your mobile device
- View test reports

Step 3

Send

- Select reports (PDF or CSV) to send
- Select preferred transfer method – email, ftp, cloud storage etc.
- Send file
- Alternatively save test reports to USB key

Download the FREE app today



NaviTEK NT Pro

- Display network configuration - IPv4 / IPv6 compatible
- Wiremap for miswires, split pairs, opens and shorts
- Distance to opens and shorts (TDR)
- PoE/PoE+ detection and load test
- Tone generator for cable tracing
- Autotest button performs Ping and Traceroute test (network mode)
- Hub blink for port identification
- DHCP client
- Switch speed detection - 10/100/1000 Mb/s
- User-exchangeable RJ45 inserts
- Support for up to 12 wiremap remotes
- Backlit color screen
- Autotest button performs a suite of network tests: Internet connectivity (Ping, DNS, Gateway, Traceroute) and NetScan
- Network Probe (NET TEST) provides detailed network information of each device
- Port identification using EDP/ CDP/ LLDP protocols
- VLAN detection
- Traffic utilization bar graph
- Generate test reports (PDF or CSV)
- Send test reports from your mobile device using the free IDEAL AnyWARE App
- Logon using the 802.1x protocol
- Optical interface with power level and pass/fail indication with supported SFP
- Loopback mode for transmission testing on both copper and fiber interfaces
- Touchscreen
- Custom wiremap

NaviTEK IE

All features of the NaviTEK NT Pro as well as the following:

- M12 PROFINET cable testing
- PROFINET fiber cable testing
- Traffic light network health check
- Device LED flash to locate devices faster
- NETMAP compare – identify changes in the network
- Configure node settings without the need for a laptop
- List all network node details ie IP address, vendor details, software version etc
- Ability to reset device to factory defaults
- Device alarm/error detection
- Professional industrial Ethernet PDF reports

NaviTEK IE

Copper and Fiber Troubleshooter for
PROFINET Industrial Ethernet Networks



Ordering Information

Part No.	Kit Contents
R151010	NaviTEK IE – Industrial Ethernet Tester. 1 x NaviTEK IE test unit, 1 x Remote unit No. 1, 1 x Rechargeable power module, 1 x PSU EU/UK/US adapters, 2 x Patch cables - 30cm, Cat. 5e STP, USB Wi-Fi adapter, 1 x Quick reference guide, 1 x Carry case, 2 x PROFINET RJ45 (m) - M12 (f) D coded 1m adapter cable (R151058)

Optional Accessories

Part No.	Description
R151058	2 x PROFINET RJ45 (m) - M12 (f) D coded 1m adapter cable
R151059	2 x PROFINET RJ45 (m) - M12 (f) X coded 1m adapter cable
R151060	1 x 100Base-Fx SFP housing media converter
62-164	1 x IDEAL amplifier probe
150058	1 x RJ45 insert extraction tool, 10 x lifejack RJ45 inserts
150050	1 x Full remote set (#2 - 12), - for #2 - 6 order set 150059
MGKSX1	1 x 850nm SX MM SFP + fiber patch cord accessories kit
MGKLX2	1 x 1310nm LX SM SFP + fiber patch cord accessories kit
MGKZX3	1 x 1550nm ZX SM SFP + fiber patch cord accessories kit

For a full list of optional accessories, please visit our website.

Basic Specifications

Max. No. of Jobs	Max. No. of Stored Test	Max. Length	Battery Life	Dimensions per handset in inches	Weight per handset
50	5000	181 m/593 ft.	5 hours	6.89 x 3.15 x 1.58	0.88 lbs

For detailed specifications, please visit our website.



IDEAL NETWORKS

Apple and the Apple logo are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc.

Android is a trademark of Google Inc.

All Rights Reserved. IDEAL NETWORKS, NaviTEK and the IDEAL AnyWARE logos are trademarks or registered trademarks IDEAL INDUSTRIES Networks Limited

IDEAL Networks

1375 Park Ave., Sycamore, IL 60178 U.S.A

Phone: 800-947-3612 | 815-895-5181

Email: contactus@idealn networks.net

www.idealnetworks.net

Specification subject to change without notice. E&OE

P-5596

© IDEAL Networks 2019

Publication no.: 151907 rev.1