

LC Duplex to LC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 µm ClearCurve® multimode (OM2), 2 m



CORNING

Part Number: 050502B5Z20002M

Patch cables are used for non-permanent connections between patch panels, transmission equipment, etc. Preassembled cables allow for the implementation of complete Plug & Play solutions. When such a solution is adopted with accurate dimensioning and appropriate cable routing, it is possible to install even large cabling systems rapidly.

Features and Benefits

Connectors

- LC Duplex connector according to TIA/EIA-604 -10
- All connectors are tested to FOTP -21.
- Connectors are pre-radius polished to provide the optimal end-face geometry for long-term performance.

Cable

- Low smoke (IEC 61034) and zero-halogen (LSZH), flame retardant to IEC 60332-3-24 (C) and noncorrosive to IEC 60754-2 (FRNC)
- Cables are metal free; hence, there are no ground-loop or potential-equalization problems. Completely dry design (without gel).
- Color of outer sheath: OM1, OM2 - orange; OM3, OM4 - aqua; OS2 - yellow

LC Duplex to LC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 μ m ClearCurve® multimode (OM2), 2 m



Specifications

Shipping Dimensions

Height	180 mm
Width	250 mm
Depth	380 mm

Environmental Conditions

Temperature Range, Installation	-5 °C - 50 °C (23 °F - 122 °F)
Temperature Range, Operation	-10 °C - 60 °C (14 °F - 140 °F)
Temperature Range, Storage	-10 °C - 60 °C (14 °F - 140 °F)

Specifications - Connector B

Polish	PC
Insertion Loss, Typical	0.35 dB
Insertion Loss, Max.	0.5 dB
Tensile Strength Jacketed Cable	44 N
Durability	\leq 0.2 dB change, 500 rematings, FOTP-21
Keyed (security)	No
Boot Color	Black / White
Connector Type	LC duplex
Ferrule Material	Ceramic
Housing Color	Black
Housing Material	Composite

LC Duplex to LC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 μ m ClearCurve® multimode (OM2), 2 m

CORNING

Specifications - Connector B

Boot Type	Individual
-----------	------------

Dimensions

Length	2 m
Outer Diameter	2 mm

Mechanical Specifications

Minimum Bend Radius	10 mm
Tensile Strength	300 N
Crush Resistance	1000 N/10 cm

Design

Fiber Count	2
Outer Jacket Material	LSZH™/FRNC
Outer Jacket Color	Orange

Specifications - Connector A

Polish	PC
Insertion Loss, Typical	0.35 dB
Insertion Loss, Max.	0.5 dB
Tensile Strength Jacketed Cable	44 N
Durability	\leq 0.2 dB change, 500 rematings, FOTP-21

LC Duplex to LC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 µm ClearCurve® multimode (OM2), 2 m



Specifications - Connector A	
Keyed (security)	No
Boot Color	Black / White
Connector Type	LC duplex
Ferrule Material	Ceramic
Housing Color	Black
Housing Material	Composite
Boot Type	Individual

General Specifications	
Fiber Category	50 µm MM (OM2)
Product Category	Core Product
Cable Assembly Type	EDGE™ Extender Trunk
Cable Type	Tight-Buffered
Flame Rating	LSZH™/FRNC

Ordering Information	
Packing Type	Cardboard box

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Intermateability	Compliant with TIA/EIA-604-10

LC Duplex to LC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 µm ClearCurve® multimode (OM2), 2 m



Optical Characteristics

Fiber Code	T
Fiber Name	G50/125 ULTRA-BEND 7.5
Fiber Type	Multimode
Fiber Core Diameter	50 µm
Minimum Effective Modal Bandwidth (EMB)	950 MHz*km / -
Maximum Attenuation	2.8 dB/km / 1.0 dB/km
Min. Overfilled Launch (OFL) Bandwidth	700 MHz*km / 500 MHz*km
Serial 1 Gigabit Ethernet	750 MHz*km 600 MHz*km
Serial 10 Gigabit Ethernet	150 MHz*km / -
Typical Attenuation	2.4 / 0.8
Wavelengths	850 nm / 1300 nm
Fiber Category	OM2



Corning Optical Communications GmbH & Co. KG • Lelpziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea