

LC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 62.5 µm multimode (OM1), 20 m

The Corning logo is a blue square with the word "CORNING" in white, uppercase, sans-serif font.

Part Number:
055702K5Z20020M

Patch cables are used for non-permanent connections between patch panels, transmission equipment, etc. Preassembled cables allow for the implementation of complete Plug & Play solutions. When such a solution is adopted with accurate dimensioning and appropriate cable routing, it is possible to install even large cabling systems rapidly.

LC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 62.5 µm multimode (OM1), 20 m

CORNING

Specifications

Shipping Dimensions

Height	180 mm
Width	250 mm
Depth	380 mm

Environmental Conditions

Temperature Range, Installation	-5 °C - 50 °C (23 °F - 122 °F)
Temperature Range, Operation	-10 °C - 60 °C (14 °F - 140 °F)
Temperature Range, Storage	-10 °C - 60 °C (14 °F - 140 °F)

Specifications - Connector B

Polish	PC
Insertion Loss, Typical	0.35 dB
Insertion Loss, Max.	0.5 dB
Tensile Strength Jacketed Cable	44 N
Durability	≤ 0.2 dB change, 1000 rematings, FOTP-21
Keyed (security)	No
Boot Color	Black / White
Connector Type	SC Duplex
Ferrule Material	Ceramic
Housing Color	Beige
Housing Material	Composite

LC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 62.5 µm multimode (OM1), 20 m

CORNING

Specifications - Connector B

Boot Type	Individual
-----------	------------

Dimensions

Length	20 m
--------	------

Outer Diameter	2 mm
----------------	------

Mechanical Specifications

Minimum Bend Radius	30 mm
---------------------	-------

Tensile Strength	300 N
------------------	-------

Crush Resistance	1000 N/10 cm
------------------	--------------

Design

Fiber Count	2
-------------	---

Outer Jacket Material	LSZH™/FRNC
-----------------------	------------

Outer Jacket Color	Orange
--------------------	--------

Specifications - Connector A

Polish	PC
--------	----

Insertion Loss, Typical	0.35 dB
-------------------------	---------

Insertion Loss, Max.	0.5 dB
----------------------	--------

Tensile Strength Jacketed Cable	44 N
---------------------------------	------

Durability	≤ 0.2 dB change, 500 rematings, FOTP-21
------------	---

LC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 62.5 µm multimode (OM1), 20 m

CORNING

Specifications - Connector A

Keyed (security)	No
Boot Color	Black / White
Connector Type	LC duplex
Ferrule Material	Ceramic
Housing Color	Beige
Housing Material	Composite
Boot Type	Individual

General Specifications

Cable Type	Tight-Buffered
Flame Rating	LSZH™/FRNC
Cable Assembly Type	Two Fiber

Ordering Information

Packing Type	Cardboard box
--------------	---------------

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Optical Characteristics

Fiber Code	K
Fiber Name	G62.5L/125 InfiniCor® 300

LC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 62.5 µm multimode (OM1), 20 m

CORNING

Optical Characteristics

Fiber Type	Multimode
Fiber Core Diameter	62.5 µm
Minimum Effective Modal Bandwidth (EMB)	220 MHz*km / -
Maximum Attenuation	2.8 dB/km / 1.0 dB/km
Min. Overfilled Launch (OFL) Bandwidth	200 MHz*km / 600 MHz*km
Serial 1 Gigabit Ethernet	300 MHz*km / 550 MHz*km
Serial 10 Gigabit Ethernet	33 MHz*km / -
Typical Attenuation	2.9 / 0.7
Wavelengths	850 nm / 1300 nm
Fiber Category	OM1



Corning Optical Communications GmbH & Co. KG • Lelpziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea