


REFERENCE:

PERFORMANCE REQUIREMENTS AT DRY AS MOLDED:


- 1. FIR TREE PUSH IN FORCE: REF. 10 LBS MAX IN EACH APPLICABLE OVAL HOLE SIZE AND A PLATE THICKNESS OF 1.8mm
- 2. FIR TREE PULL OUT FORCE: REF. 25 LBS MIN IN EACH APPLICABLE OVAL HOLE SIZE AND A PLATE THICKNESS OF 1.8mm
- 3. SHEET METAL THICKNESS RANGE: 0.60mm 6.0mm
- 4. APPLICABLE OVAL HOLE SIZES:
 - A. 6.2 X 12.2mm
 - B. 6.5 x 12.5mm
 - C. 6.5 x 13.0mm
 - D. 7.0 x 12.0mm
- 5. MINIMUM BUNDLE RANGE: 1.8mm 35.0mm
- 6. CABLE TIE MINIMUM TENSILE: 50lbs







Isometric view



MATERIAL	COLOR
PA66HS	BLACK
PA66HS	GRAY
PA66HIRHS	BLACK
PA46	BROWN

HellermannTyton E N T T O R HellermannTyton All PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANNTYTON | Mario |

R E	D R level	<u></u>	
V	A W by	KVH	
Š	I N date	11/8/12	
O N S	G ECN#	012221	
S	part level	A	

D-8EZ8-0Z	TOLERANCES	.XXXX = \pm 0.25 .XXX = \pm 0.50 .XX = \pm 1.00 .X = \pm 2.00 \angle = \pm 1.00 unless otherwise specified	
N S	units	millimeters	

P	T50SOSFTOVALU phase PRODUCTION				
A	OVAL HOLE FIR TREE WITH 6" 50LB LOW PROFILE CABLE TIE				
K	material SEE CHART				

כ	FORMAT AH VERSION J	CATIA V5		SCALE 3:4	
2	A- SIZE (landscape)_N01		previous drawing number		
A V	S. ADAMS & M. TOLL & & & & & & & & & & & & & & & & & &				
ľ	⁸ 5/5/11 ਵੇਂ 4/4/12 ਛੋ				
Ī	type CUSTOMER		sheet 1 of 1		
ا ج	11-0345-001-CSU				