




P17BH-AB-459G

Gvision's P17BH is a 17" industrial grade resistive touch monitor designed for use in the professional industry. It's the perfect 5-wire resistive touch screen solution for harsh environment.

DIMENSIONS



FEATURES

- 19" Screen Size, 1280 x 1024 Resolution
- 5-Wire Resistive Touch Panel
- Supporting Inputs: DVI-D, VGA
- 400 Nits High Brightness
- LED-Direct Backlight Unit
- Integrated Stereo Speakers
- Designed for 24/7/365 Operation
- 3-Years Warranty

SPECIFICATIONS

MODEL	P17BH-AB-459G
Screen Size	17 In
Resolution	1280 x 1024
Backlight	LED Direct Backlight
Aspect Ratio	5 : 4
Viewing Angle	170° / 160°
Response Time	5ms
Brightness	400cd/m ²
Contrast Ratio	1000 : 1
Display Area	337.9 (H) x 270.3 (V) mm
INTERFACE	
DVI In	1
VGA In	1
USB-A Type	1
RS232	1
SPEAKER	
Audio	1W Per Channel
TOUCH	
Touch Type	Resistive
Touch Panel	5-Wire Resistive
Touch Interface	RS-232 or USB A type
POWER	
Input Voltage	DC12V
Consumption	< 5W
Saving Mode	< 0.5W
TEMPERATURE	
Operating	32° F ~ 104° F (0° C ~ 40° C)
Storage	-4° F ~ 140° F (-20° C ~ 60° C)
Humidity	10% ~ 90%
DIMENSIONS (WxHxD)	
Inch (in)	15.4 x 15.0 x 7.0
Millimeter (mm)	392.0 x 381.5 x 180.0
WEIGHT	
Net Weight	14.3 lbs (6.5 kg)
VESA™	
Mount Size (mm)	75 x 75

Specifications subject to change without any notice