

# LC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 µm ClearCurve® multimode (OM3), 4 m

The CORNING logo is located in the top right corner of the page. It consists of the word "CORNING" in a white, sans-serif font, centered within a solid blue square.

**Part Number:**  
**055702T5Z20004M**

Patch cables are used for non-permanent connections between patch panels, transmission equipment, etc. Preassembled cables allow for the implementation of complete Plug & Play solutions. When such a solution is adopted with accurate dimensioning and appropriate cable routing, it is possible to install even large cabling systems rapidly.

# LC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 µm ClearCurve® multimode (OM3), 4 m

CORNING

## Specifications

### Shipping Dimensions

Height	180 mm
Width	250 mm
Depth	380 mm

### Environmental Conditions

Temperature Range, Installation	-5 °C - 50 °C (23 °F - 122 °F)
Temperature Range, Operation	-10 °C - 60 °C (14 °F - 140 °F)
Temperature Range, Storage	-10 °C - 60 °C (14 °F - 140 °F)

### Specifications - Connector B

Polish	PC
Insertion Loss, Typical	0.35 dB
Insertion Loss, Max.	0.5 dB
Tensile Strength Jacketed Cable	44 N
Durability	≤ 0.2 dB change, 1000 rematings, FOTP-21
Keyed (security)	No
Boot Color	Aqua / White
Connector Type	SC Duplex
Ferrule Material	Ceramic
Housing Color	Black
Housing Material	Composite

# LC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 $\mu$ m ClearCurve® multimode (OM3), 4 m

CORNING

## Specifications - Connector B

Boot Type	Individual
-----------	------------

## Dimensions

Length	4 m
--------	-----

Outer Diameter	2 mm
----------------	------

## Mechanical Specifications

Minimum Bend Radius	10 mm
---------------------	-------

Tensile Strength	300 N
------------------	-------

Crush Resistance	1000 N/10 cm
------------------	--------------

## Design

Fiber Count	2
-------------	---

Outer Jacket Material	LSZH™/FRNC
-----------------------	------------

Outer Jacket Color	Aqua
--------------------	------

## Specifications - Connector A

Polish	PC
--------	----

Insertion Loss, Typical	0.35 dB
-------------------------	---------

Insertion Loss, Max.	0.5 dB
----------------------	--------

Tensile Strength Jacketed Cable	44 N
---------------------------------	------

Durability	$\leq$ 0.2 dB change, 500 rematings, FOTP-21
------------	--

# LC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 $\mu$ m ClearCurve® multimode (OM3), 4 m



## Specifications - Connector A

Keyed (security)	No
Boot Color	Aqua / White
Connector Type	LC duplex
Ferrule Material	Ceramic
Housing Color	Black
Housing Material	Composite
Boot Type	Individual

## General Specifications

Cable Type	Tight-Buffered
Flame Rating	LSZH™/FRNC
Cable Assembly Type	Two Fiber

## Ordering Information

Packing Type	Cardboard box
--------------	---------------

## Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

## Optical Characteristics

Fiber Code	T
Fiber Name	G50/125 ULTRA-BEND 7.5

# LC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 µm ClearCurve® multimode (OM3), 4 m



Optical Characteristics	
Fiber Type	Multimode
Fiber Core Diameter	50 µm
Minimum Effective Modal Bandwidth (EMB)	2000 MHz*km / -
Maximum Attenuation	2.8 dB/km / 1.0 dB/km
Min. Overfilled Launch (OFL) Bandwidth	1500 MHz*km / 500 MHz*km
Serial 1 Gigabit Ethernet	1100 MHz*km / 600 MHz*km
Serial 10 Gigabit Ethernet	300 MHz*km/ 333 MHz*km
Typical Attenuation	2.4 / 0.8
Wavelengths	850 nm / 1300 nm
Fiber Category	OM3



Corning Optical Communications GmbH & Co. KG • Lelpziger Strasse 121 • 10117 Berlin, Germany  
+00 800 2675 4641 • FAX: +49 30 5303 2335 • [www.corning.com/opcomm/emea](http://www.corning.com/opcomm/emea)