



Data Sheet | Model: **Armorgard**

CuttingStation™ SS7



- ⚠ A multi-purpose cutting platform, with a secure cabinet beneath the workbench area
- ⚠ Recessed 110V inlet power supply
- ⚠ 2 x 110V internal sockets
- ⚠ Extendable support arms with 4 configurations
- ⚠ Heavy-duty all-swivel wheels for easy moving
- ⚠ Extendable back panel provides extra workspace for mitre saws
- ⚠ Sound deadening fire-rated foam to reduce noise pollution
- ⚠ Rubber mat to reduce vibration
- ⚠ PVC curtains to contain sparks
- ⚠ Swarf collector with dust extractor connection point
- ⚠ Improved lighting position for increased productivity
- ⚠ European Patent Application Number EP17183824.6
- ⚠ European Community Design Registration Number 004511525

Product	Armorgard CuttingStation™ SS7
Internal dimensions	Top (with extended back): 1125x955x1000mm Bottom: 1125x710x550mm
External dimensions (including protrusions)	Standard: 1390x780x1900mm Extended: 3225x1090x1900mm
Weight (kg)	175
Colour	Charcoal grey: RAL7021, Pillar box red: RAL 3020
Finished Coating	Powder coated steel
Material	Steel
Material Thickness	1.5mm
Locking mechanism	Highly Secure, keyed alike 5-Lever Deadlock
Does it have Forklift Skids?	Yes
Does it have Gas Arms?	No
Newton Loading of Gas Arms	N/A
Safety stay	No
Quantity of keys supplied	2 keys
Optional Extras Available	SS7X, SS7C, CLEK
Quantity of Shelves as standard	0
Are Castors standard or optional extra	Standard - heavy duty
How are the Castors fitted?	Quick-fix bolt on Castor kit. Extra Heavy-duty Castors using Armorgard castor plates.
Sump capacity	N/A
Safety Signage	N/A
Fire resistant?	Yes - fire resistant foam

