

EDGE™ Housing 2 rack unit, holds up to 24 EDGE modules or panels

CORNING

Part Number: EDGE-02U

EDGE™ Solutions are high-density preterminated optical cabling solutions offering industry-leading connector density. With unprecedented finger access, there is no need for additional tools enabling faster moves, adds and changes (MACs).



EDGE™ Housing 2 rack unit, holds up to 24 EDGE modules or panels

CORNING

Specifications

Design

Number of Modules	24
Cable entry type	Side brush entry
Cable Entry Direction	Rear
Housing Type	EDGE™ HD
Number of Panels per Housing	24
Color	Silver
Fiber Capacity	288

General Specifications

Access Type	Front and rear access slidable
Lockable	Yes, rear side
Mounting Type	Rack Mount , Cabinet-mount
Product Type	Fiber Optic Hardware
Application	Data Center , Data Center LAN/SAN , Enterprise Networks

Mechanical Specifications

Minimum Cabinet Size	800 mm
----------------------	--------

Dimensions

Height	88 mm
Width	432 mm

EDGE™ Housing 2 rack unit, holds up to 24 EDGE modules or panels

CORNING

Dimensions

Depth	561 mm
-------	--------

Shipping Dimensions

Height	216 mm
--------	--------

Width	565 mm
-------	--------

Depth	660 mm
-------	--------

Ordering Information

Weight	8.6 kg
--------	--------

Shipping Weight	10.9 kg
-----------------	---------

Module Capacity	24
-----------------	----

Units per Delivery	1/1
--------------------	-----

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---



Corning Optical Communications GmbH & Co. KG • Lelpziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea