

FutureCom™ D Patch Cord, FRNC, RJ45 - RJ45 connector Green, 1 m



Part Number: CCADGF-D4002-A010-C0

The application-neutral FutureCom™ D patch cords have four stranded pairs sheathed with a foil shield (F/UTP) and additional with a braid shield (SF/UTP). They are assembled with a shielded RJ45 connector on each end. The zero halogen patch cords (LSZH) are non-corrosive according to IEC 60754-2 (FRNC) and EN 50267, low smoke according to IEC 61034 and EN 50268 and flame retardant according to IEC 60332-1, Category B and EN 50266-2-1. They are available in various lengths and colors.

Features and Benefits

SF/UTP flex cable, specified up to 300 MHz

Application-neutral due to using all four pairs of RJ45 connectors

Minimum surface transfer impedance of cable (<10 mΩ/m at 10 MHz)

Outstanding transmission characteristics according to class D (ISO/IEC 11801 Ed.2.2) link specification

Category 5 / 5e

FutureCom™ D Patch Cord, FRNC, RJ45 - RJ45 connector Green, 1 m



Specifications

General Specifications

Cable Assembly Type	Patch Cords
Environment	Indoor
Category	5/5e
Cable Type	SF/UTP
Halogen-free	Yes

Mechanical Specifications

Fire Load	0.43 MJ/m
Min. Bend Radius Installation	46 mm

Electrical Specifications

Delay skew	300 ns/100 m
DC resistance unbalance	4.5 %
Insulation Resistance	150 MΩ*km
Surface transfer impedance	100 mΩ

Specifications - Connector A

Connector Type	RJ45 - 8/8
Durability Cycles	750 N/A

FutureCom™ D Patch Cord, FRNC, RJ45 - RJ45 connector Green, 1 m

CORNING

Cable Design

Outer Jacket Material LSZH™ /FRNC

Outer Jacket Color Green

Specifications - Connector B

Connector Type RJ45 - 8/8

Durability Cycles 750 N/A

Standards

RoHS Free of hazardous substances according to RoHS 2011/65/EU

Environmental Conditions

Temperature Range, Installation 0 °C - 50 °C (32 °F - 122 °F)

Temperature Range, Operation -20 °C - 60 °C (-4 °F - 140 °F)



Corning Optical Communications GmbH & Co. KG • Leipzig Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea