


Pop-Out Video Wall Mount w/Security for 45" to 70" TVs and Monitors - Flat Screens, UL Certified

MODEL NUMBER: DMVWSC4570XUL



Pop-out wall mount supports use of 45" to 70" flat screen TVs or monitors in video walls. Included lock deters theft.

Features

Pop-Out Display Mount is Designed for Video Wall Installations

A pop-out feature and micro-adjustability make the DMVWSC4570XUL wall mount a purpose-built solution for video walls in home theaters, offices, conference centers, medical facilities, airports, hotels, bars, restaurants and security stations. Designed for use with flat screens from 45 to 70 inches, this wall mount is function- and weight-tested to 154 lb. in accordance with UL Standard 2442.

Pop-Out Feature Supports Convenient Cable Access and Screen Adjustments

To unlock the pop-out mechanism, press lightly on the front of your display and pull it toward you. It can extend anywhere from 3.7 to 11 inches from the wall, providing space to access cables or make adjustments. This is especially helpful in video wall installations, where adjacent screens may limit access. The extension also makes it easier to replace a display.

Multi-Directional Micro-Adjustments Provide Exact Alignment

You can move the display left or right, adjust the screen level from -3° to +3° and adjust the tilt from -2° to +4°. For exact positioning in a video wall, there are six micro-adjustments for tilt, height and depth (user-supplied hex key required). When the display is in the perfect position, insert the included plastic locks in the brackets to prevent unintentional movement.

Included Combination Lock Deters Display Theft

A three-position combination lock (included) secures the display bracket to the wall plate to deter theft, which can be a concern in public areas with unguarded traffic. Deterring display theft also protects the mount, which is often damaged beyond repair when a display is stolen. The heavy-duty steel frame withstands the stress of frequent adjustments, and the black powder-coated finish offers durability and scratch resistance. Your display hides the mount and the padlock, maintaining a professional look.

VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 200 x 200, 200 x 300, 200 x 400, 300 x 200, 300 x 300, 300 x 400, 400 x 200, 400 x 300, 400 x 400, 500 x 200, 500 x 300, 500 x 400, 600 x 300 and 600 x 400.

Mounting hardware is included.

Highlights

- Accommodates most displays with flat screens from 45 to 70 in.
- Pop-out design provides access for adjustments during installation and maintenance
- Micro-adjustments allow creation of a uniform look in a video wall
- Combination lock secures brackets to help deter theft of your display
- Function- and weight-tested up to 154 lb. in accordance with UL Standard 2442

Applications

- Group multiple mounts to create a large video wall for digital signage in a lobby, conference room, bar or restaurant
- Deter theft of displays in a video wall located in a hotel, library or other public area
- Adjust a screen in a video wall without disturbing other displays

Package Includes

- All DMVWSC4570XUL components (some assembly required)
- Assembly and mounting fasteners
- Display mounting fasteners
- Three-position combination lock
- Owner's manual

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332240545
PHYSICAL	
Color	Black
Material of Construction	Steel
Maximum Screen Size (cm)	177.8
Maximum Screen Size (in.)	70
Maximum Weight Capacity (kg)	70
Maximum Weight Capacity (lbs.)	154
Min/Max Arm Extension (cm)	9.4 - 28.4
Min/Max Arm Extension (in.)	3.7 - 11.2
Minimum Screen Size (cm)	114.3
Minimum Screen Size (in.)	45
Motion	Fixed
Mounting Location	Wall
Number of Displays	1
Shipping Dimensions (hwd / cm)	13.72 x 27.18 x 74.93
Shipping Dimensions (hwd / in.)	5.40 x 10.70 x 29.50
Shipping Weight (kg)	11.25
Shipping Weight (lbs.)	24.80
Unit Dimensions (hwd / cm)	67.6 x 28.45 x 52.32
Unit Dimensions (hwd / in.)	26.4 x 11.2 x 20.6
Unit Weight (kg)	11.39
Unit Weight (lbs.)	25.1
VESA Pattern (mm)	200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400; 500x200; 500x300; 500x400; 600x300; 600x400
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	No
CERTIFICATIONS	
Approvals	RoHS3, REACH and CE
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	5-year limited warranty
--	-------------------------

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>