

# LANscape® Fiber Housing front panel loaded with LC Duplex shuttered adapters (Breakout version), 24 Fibers, 1U, Multimode OM3/OM4, black



## **Part Number: LAN1-24AD-ADPT-B**

The LANscape® housing family was designed for various applications in 19-in racks and main distribution frames. The fixed or sliding housings can be equipped with industry common adapter types in different fiber categories and are suitable for direct field termination, fusion splicing with pigtails as well as preterminated solutions. The four back openings accommodate cable glands. Additional brackets for cable strain relief for FTTD/FTTO applications or U-Clips for Plug & Play™ and EDGE™ trunks can be mounted at the backside.

The space-optimized interior makes it easy to work with ongoing moves, adds and changes (MACs), thus reducing the risk of network disruptions.

## Features and Benefits

### **Easy to remove top cover**

No tools needed

---

### **Housing made of aluminium**

Lightweight, but robust

---

### **Quick-mount feature**

Allows single-person mounting of housing

---

### **Accomodate different termination methods**

Pigtail splicing, field connectorisation, preterminated cables, Plug & Play™ or EDGE™ trunks can be installed in the same housing

---

### **Low installation depth**

Mountable in shallow cabinets or racks

---

### **Multiple labelling options**

Port numbering above and below adapter modules or customised labels

---

### **LC Duplex adapter modules with self-closing shutters**

Additional protection at no extra cost

# LANscape® Fiber Housing front panel loaded with LC Duplex shuttered adapters (Breakout version), 24 Fibers, 1U, Multimode OM3/OM4, black



## Specifications

### Design - Adapter

Adapter Housing Color	Aqua
Adapter Type	LC duplex shuttered

### Design

Fiber Count	24
Housing Material	Aluminum
Additional cable number reachable with accessories	4
Maximum cable number in basic unit with accessories	4
Cable entry type	Prepunched circular
Number of Adapters	12
Number of Splice Protectors	0

### General Specifications

Fiber Category	50 μm MM (OM3/OM4)
Access Type	Front, top, rear
Mounting Type	Rack 19-in

### Dimensions

Height	44 mm
Width	483 mm
Depth	233 mm

# LANscape® Fiber Housing front panel loaded with LC Duplex shuttered adapters (Breakout version), 24 Fibers, 1U, Multimode OM3/OM4, black



## Ordering Information

Package Contents	LANscape Fiber Housing with adapters, 1 x M20 cable gland and all accessories needed for the installation
Units per Delivery	1/1

## Shipping Dimensions

Height	44 mm
Width	483 mm
Depth	233 mm



Corning Optical Communications GmbH & Co. KG • Lelpziger Strasse 121 • 10117 Berlin, Germany  
+00 800 2675 4641 • FAX: +49 30 5303 2335 • [www.corning.com/opcomm/emea](http://www.corning.com/opcomm/emea)