

FutureCom™ Top hat rail adapter, LANscape® FutureCom™ Top hat rail adapter, LANscape®

CORNING

Part Number: WAXISE-V0103-C001

The FutureCom™ Industrial top hat rail adapter is suitable for installation on 35 mm top hat rails.

It provides a potential equalization spring and, due to its modular design, allows a free configuration of each single port with FutureCom copper modules as well as LANscape® fiber optic modules.



Features and Benefits

Compact design with small dimensions

Electrical spring contact to top hat rail (bonding, grounding)

Inclined design with labeling field and dust protection flap

Tool-less and fast installation on top hat rails

Tool-less installation of module

Top hat rail adapter light grey, RAL 7035

Flame retardant, fire Class UL94 V-0

Temperature range: -20°C to +70°C

Recyclable and free of heavy metal

FutureCom™ Top hat rail adapter, LANscape® FutureCom™ Top hat rail adapter, LANscape®

CORNING

Specifications

Environmental Conditions

Temperature Range, Installation	-20 °C - 70 °C (-4 °F - 158 °F)
---------------------------------	---------------------------------

Design

Color	Gray
-------	------

Number of Ports	1
-----------------	---

General Specifications

Product Category	Core Product
------------------	--------------

Halogen-free	Yes
--------------	-----

Ordering Information

Weight	16 g
--------	------

Units per Delivery	1/1
--------------------	-----

Standards

Flame Retardance	Flame retardant, fire Class UL94 V-0
------------------	--------------------------------------

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---



Corning Optical Communications GmbH & Co. KG • Leipzig Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea