


# ÖLFLEX® VFD 1XL with Signal

Flexible VFD cable; 600V/1000V; UL & c(UL) TC-ER approval



ÖLFLEX® VFD 1XL w/Signal is a robust oil- and UV-resistant shielded motor cable for VFD drives. Enhanced electrical properties of XLPE insulation provide problem-free performance where precision control is critical. The new leaner design enables reduced cable diameters and increases flexibility. UL TC-ER rating allows for installation without conduit.

## Recommended applications

VFD drive and motor connections; pumps; compressors; conveyors; elevators; extruders; presses; HVAC; on/off, slow down/speed up applications.

## Approvals



Cable attributes		page <?>
OIL	OR-03	FLAME FR-03
MOTION	FL-02	MECH. MP-03

## Construction

**Conductors:** tinned copper fine wire

**Insulation:** XLPE (plus)

**Shielding:** barrier tape; triple layer foil tape (100% coverage); tinned copper braid (85% coverage); tinned copper drain wire

**Signal Pair:** individually foil shielded with TC drain wire

**Jacket:** specially formulated thermoplastic elastomer (TPE); black

## Application advantage

- One cable for applications
- Low capacitance design
- UL TC-ER & c(UL) CIC approved
- Industrial grade phthalate-free jacket design for harsh environments
- Reduces space and weight in tray
- No conduit required due to TC-ER rating
- Resistant to a wide range of disinfecting solutions used in the food, beverage, chemical and related industries, according to ECOLAB® PM 40-1 test procedure

Complete the installation

SKINTOP®  
MS-M BRUSH  
page 524

EPIC®  
ULTRA HB  
page 407

## Technical data

<p> <b>Minimum bend radius:</b> for installation: 7.5 x OD</p> <p> <b>Temperature range:</b> - UL/CSA: -25°C to +90°C - for stationary use: -40°C to +90°C - for flexible use: -25°C to +90°C</p> <p> <b>Nominal voltage:</b> - UL TC: 600V - UL Flexible Motor Supply: 1000V - UL/CSA AWM: 1000V</p> <p> <b>Test voltage:</b> - 18 AWG - 10 AWG: 3000V - 8 AWG - 4 AWG: 3500V - 2 AWG: 4000V</p> <p> <b>Conductor stranding:</b> - 16 AWG - 2 AWG Class K</p>	<p> <b>Color code:</b> black with white numbers, plus green/yellow ground 1-pair: black with white numbers</p> <p> <b>Approvals:</b> UL: TC-ER per UL 1277 Flexible Motor Supply Cable per UL 2277 AWM 22022 per UL 758 Attributes: UL Oil Res I/II 90°C wet or dry -40°C cold bend; -25°C cold impact sunlight resistant direct burial NFPA 79 NEC: Class 1 Division 2 per NEC Article 501 Canada: c(UL) CIC FT4 cRU AWM II A/B FT4 Additional: NFPA 79 RoHS II Meets XHHW-2 performance requirements per UL 44</p>
--	--

Part number	Number of conductors incl. ground	Nominal outer diameter in mm	Copper weight lbs/mft	Approx. weight lbs/mft	SKINTOP® MS-SC metric thread	SKINTOP® MS-M BRUSH metric thread
<b>16 AWG (1.5 mm²)</b>						
701710	4 + (18 AWG)	0.446 11.3	72.1	137	53112630	53112676
<b>14 AWG (2.5 mm²)</b>						
701711	4 + (18 AWG)	0.486 12.3	93.4	166	53112630	53112676
<b>12 AWG (4 mm²)</b>						
701712	4 + (18 AWG)	0.533 13.5	129.1	210	53112640	53112676
<b>10 AWG (6 mm²)</b>						
701713	4 + (18 AWG)	0.593 15.1	179.1	289	53112650	53112677

Part number	Number of conductors incl. ground	Nominal outer diameter in mm	Copper weight lbs/mft	Approx. weight lbs/mft	SKINTOP® MS-SC metric thread	SKINTOP® MS-M BRUSH metric thread
<b>8 AWG (10 mm²)</b>						
701714	4 + (14 AWG)	0.767 19.5	292.5	448	53112650	53112677
<b>6 AWG (16 mm²)</b>						
701715	4 + (14 AWG)	0.958 24.3	442.9	694	53112660	53112678
<b>4 AWG (21 mm²)</b>						
701716	4 + (14 AWG)	1.079 27.4	652.1	976	53112660	53112678
<b>2 AWG (33.7 mm²)</b>						
701717	4 + (14 AWG)	1.234 31.3	1008.6	1483	53112670	53112679

ECOLAB® is a registered trademark of Ecolab, Inc. Recommended SKINTOP® assumes minimal OD variance. Additional configurations are available; please see our SKINTOP® section. If not otherwise specified, all values relating to the product are nominal values. Photographs are not to scale and are not true representations of the products in question.