

Single-Display Sit-Stand Wall-Mount Workstation with Thin-Client Mount

MODEL NUMBER: WWSS1327RWTC



Sit-stand workstation transforms your desk space into an ergonomic working environment without modifying the surface.

Features

Enjoy the Benefits of Standing During Your WorkdayThis WorkWise™ sit-stand workstation mounts to the wall using the included hardware, allowing you to enjoy the benefits of better workplace ergonomics.

Standing for part of the day can help increase metabolism, improve alertness and productivity, reduce fatigue and decrease the risk of repetitive stress injuries. Ideal for home, school or office use, the WWSS1327RWTC lets you sit or stand with 28.7 inches of single-motion height extension.

Easy to Adjust to Your LikingThe keyboard and monitor are attached to separate arms, so you can adjust them independently to accommodate your perfect set. You can rotate the monitor 360 degrees for viewing in portrait or landscape orientation. The monitor also swivels -90° to +90° and tilts -15° to +15° for the perfect viewing angle. Increase or decrease tension in both arms using the included hex key to compensate for heavier or lighter loads. The keyboard arm and tray fold up to save space when not in use.

VESA-Compliant Mount Supports Monitor and Keyboard Up to 18 lb.The VESA-compliant mount fits most flat-panel monitors, televisions and other displays from 13 to 27 inches. It's compatible with 75 x 75 mm and 100 x 100 mm VESA mounting-hole patterns.

Integrated Thin-Client Mount and Cable ManagementBy integrating your thin client into your display mount set, you can create a complete system right at your fingertips. The thin-client bracket mounts directly behind the monitor. Cable managers cut down on workspace clutter.

5-Year Warranty and Environmentally Responsible DesignThe WWSS1327RWTC sit-stand workstation comes with a 5-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

Highlights

- Mounts firmly to wall to leave valuable desk or table space clear
- Adjusts to fit wide range of flat-screen monitors from 13 to 27 in.
- Thin-client mount integrates a small CPU into your display mount configuration
- Monitor swivels from -90° to +90° and rotates 360° to customize the ideal viewing angle
- Includes necessary mounting hardware so you can start installation immediately

Applications

- Transform your work area into a sit-stand environment to reap the health benefits of standing for part of your workday

Package Includes

- Display arm
- (2) Keyboard arms
- Thin-client bracket
- Keyboard tray
- Wall rail
- Keyboard tray holder
- Keyboard arm attachment
- Mounting hardware
- Owner's manual

Specifications

OVERVIEW



UPC Code	037332210906
PHYSICAL	
Color	Black; Silver
Degrees of Motion	-15/+15 Tilt; -90/+90 Swivel; 360 Rotate
Material of Construction	Steel and plastic
Maximum Screen Size (cm)	68.58
Maximum Screen Size (in.)	27
Maximum Weight Capacity (kg)	8
Maximum Weight Capacity (lbs.)	18
Minimum Screen Size (cm)	33.02
Minimum Screen Size (in.)	13
Motion	Full
Mounting Location	Wall
Number of Displays	1
Unit Dimensions (hwd / in.)	28.7 x 23.6 x 34.8
Unit Weight (kg)	5.22
Unit Weight (lbs.)	11.50
VESA Pattern (mm)	75x75; 100x100
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	Yes
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>