

# DCN-CCUB2 Central Control Unit Basic

www.boschsecurity.com



**BOSCH**  
Invented for life



- ▶ Cost effective solution for basic DCN Next Generation systems
- ▶ Maximum 245 wired contribution units
- ▶ Ethernet connection for configuration and control computers

The Central Control Unit (CCU) includes features for controlling wired delegate microphones, distributing simultaneous interpretation and conducting voting sessions, all without an operator.

In combination with a PC, this control unit brings greater sophistication to conference control. Users can access an extensive range of software modules, each with a specific function in controlling and monitoring a conference. These modules greatly expand the capacity to manage a conference. In the event of PC failure, this control unit will revert to its stand-alone operation mode, enabling the conference to proceed.

## Functions

- For wired DCN Next Generation systems
- Basic microphone management facilities
- Four operational microphone modes:
  - Open: microphone button control with request-to-speak (Auto)
  - Override: microphone button with override of activated microphones (FIFO)
  - Voice: voice activated microphones
  - Push-to-talk (push and hold button to speak)
- Number of open microphones between 1 and 25
- Configuration of CCU and system via a display and a single rotary push button
- Basic voting control for parliamentary voting procedure. Delegates can register 'Present', 'Yes', 'No' and 'Abstain'. The Concentus Chairman unit can start, stop and suspend the voting. The total results can be displayed on hall displays and on the LCD screens of the units
- A page function which activates a voting tone. With this tone the chairman can indicate that a voting round is about to start
- Simultaneous interpretation function with 31 language channels plus one floor channel
- Distribution of up to 31 language channels plus floor to DCN wired channel selectors
- Basic intercom function with function to assign intercom operator and intercom chairman (both can be called from the interpreter desk)
- Stand-alone automatic camera control
- Extended conference facilities when using control PC software or remote controllers
- Adjustable sensitivity for the audio inputs
- Adjustable level for the audio outputs
- Audio insertion facility to connect external audio processing devices or telephone couplers
- The CCU can be assigned a unique name by the installer for easy identification
- VU meter readings to monitor audio inputs and audio outputs. The audio can be monitored using a headphone
- 19" (2U) housing for tabletop or rack mounting

- Handgrips for easy transportation

### Controls and Indicators

#### Front

- Power on/off switch
- 2 x 16 Character LCD display for status information and configuration
- Rotary control to navigate through the LCD menus

#### Back

- Three red LED overload indicators for the DCN network outputs
- Green and yellow LED indicating Ethernet activity

### Interconnections

#### Front

- One stereo headphone output 3.5 mm (0.14 in)

#### Back

- Euro power socket with built-in fuse
- Three DCN outlet sockets including locking facility for connection of units
- Two stereo Cinch unbalanced audio line inputs
- One three-pole XLR balanced audio line output
- Two stereo Cinch unbalanced audio line outputs
- One Ethernet connection for Control PC or Open Interface
- One RS-232 serial data connector for controlling cameras

### Certifications and approvals

Region	Certification
Europe	CE

### Parts included

Quantity	Component
1	DCN-CCUB2 Central Control Unit Basic
1	Set of mounting brackets for 19" rack
1	Set of feet
1	System installation and user instruction on DVD
1	US power cord
1	Euro power cord

### Technical specifications

#### Electrical

Supply voltage	100-240 Vac 50-60 Hz
Power consumption	295 W
DCN system supply	40 Vdc, max 85 W per DCN socket
Total power supply	255 W
RS-232 connection	1 x nine-pole Sub-D female socket
Frequency response	30 Hz - 20 kHz (-3 dB at nominal level)

THD at nominal level	< 0.5 %
Cross talk attenuation	> 85 dB at 1 kHz
Dynamic range	> 90 dB
Signal-to-noise ratio	> 87 dBA

#### Audio inputs

Cinch nominal input	-24 dBV (+/- 6 dB)
Cinch maximum input	+0 dBV

#### Audio outputs

XLR nominal output	-12 dBV (+6 / -24 dB)
XLR maximum output	+12 dBV
Cinch nominal output	-24 dBV (+6 / -24 dB)
Cinch maximum output	+0 dBV

#### Mechanical

Mounting	Tabletop or mounted in a 19" rack
Dimensions (H x W x D)	
for tabletop use, with feet	92 x 440 x 400 mm (3.6 x 17.3 x 15.7 in)
for 19" rack use, with brackets	88 x 483 x 400 mm (3.5 x 19 x 15.7 in)
in front of brackets	40 mm (1.6 in)
behind brackets	360 mm (14.2 in)
Weight	7.9 kg (17.5 lbs)
Color	Charcoal (PH 10736) with silver

### Ordering information

#### DCN-CCUB2 Central Control Unit Basic

DCN Next Generation basic central control unit for controlling delegate microphones, distributing simultaneous interpretation, and conducting voting sessions.

Order number **DCN-CCUB2**

**Represented by:**

**Americas:**

Bosch Security Systems, Inc.  
12000 Portland Avenue South  
Burnsville MN 55337, USA  
Phone: +1-800-392-3497  
Fax: +1-800-955-6831  
audiosupport@us.bosch.com  
www.boschsecurity.com

**Europe, Middle East, Africa:**

Bosch Security Systems B.V.  
P.O. Box 80002  
5617 BA Eindhoven, The Netherlands  
Phone: + 31 40 2577 284  
Fax: +31 40 2577 330  
emea.securitysystems@bosch.com  
www.boschsecurity.com

**Asia-Pacific:**

Robert Bosch (SEA) Pte Ltd, Security  
Systems  
11 Bishan Street 21  
Singapore 573943  
Phone: +65 6571 2808  
Fax: +65 6571 2699  
apr.securitysystems@bosch.com  
www.boschsecurity.asia

**China:**

Bosch (Shanghai) Security Systems Ltd.  
201 Building, No. 333 Fuquan Road  
North IBP  
Changning District, Shanghai  
200335 China  
Phone +86 21 22181111  
Fax: +86 21 22182398  
www.boschsecurity.com.cn

**America Latina:**

Robert Bosch Ltda Security Systems Division  
Via Anhanguera, Km 98  
CEP 13065-900  
Campinas, Sao Paulo, Brazil  
Phone: +55 19 2103 2860  
Fax: +55 19 2103 2862  
latam.boschsecurity@bosch.com  
www.boschsecurity.com