

FREEDM™ Tight Buffer Indoor/Outdoor Cable 24F G50 MMF ClearCurve® OM3 0.9mm TB3, Cca-s1a,d1,a1


CORNING

Part Number: 024T8X-32188E2G

Corning MPC (multipurpose cable) tight-buffered cables are flame-retardant, indoor/outdoor cables designed for interbuilding and intrabuilding backbones in duct and riser applications.

The tight-buffered construction facilitates easier termination for low-fiber-count applications in the local area network (LAN) and eliminates need for fan-out kits.

These cables are designed for installation in conduits, ducts and in-house.



Features and Benefits

Waterblocking technology

OSP (outdoor) applications

All-dielectric construction

Requires no grounding or bonding

UV- and microbe-resistant

Can be installed in ducts or conduits

Dry cable core by means of water swellable elements

Allows efficient and craft-friendly cable preparation in outdoor or indoor/outdoor applications

Small diameter and bend radius

Easy installation in space-constrained areas

TB3 tight buffered construction

Easy and consistent stripping up to 10 cm

Flame retardant

LSZHTM/FRNC

FREEDM™ Tight Buffer Indoor/Outdoor Cable 24F G50 MMF ClearCurve® OM3 0.9mm TB3, Cca-s1a,d1,a1



Specifications

Mechanical Specifications	
Crush Resistance	500 N/10 cm
Fire Load	1.15 MJ/m
Min. Bend Radius Installation	160 mm
Min. Bend Radius Operation	121.5 mm
Nominal Outer Diameter	8.1 mm

Cable Design	
Cable Marking	Meter - Handset - CE 17 EN 50575 Cca-s1a,d1,a1 - Sine - CORNING - Fibre Optic Cable - Year - FREEDM(TM) U-VQ(ZN)H 24 OM3CC TB3 0.9 LSZH(TM)/FRNC
Central Element	FRNC/LSZH
Fiber Count	24
Number of Ripcords	1
Buffer Tube Diameter	900 mm
Outer Jacket Color	Black
Buffering Diameter	900 µm
Outer Jacket Material	Flame-retardant, non-corrosive/low-smoke, silicon-free, zero-halogen (FRNC/LSZH) material
Central Element Diameter	1.95 mm
Outer Jacket Nominal Thickness	0.8 mm
Tensile Strength Elements and/or Armoring - Layer 1	Aramid yarn with swellable elements
Tensile Strength Elements and/or Armoring - Layer 2	Aramid yarn with swellable elements

FREEDM™ Tight Buffer Indoor/Outdoor Cable 24F G50 MMF ClearCurve® OM3 0.9mm TB3, Cca-s1a,d1,a1



Cable Design

Tight Buffer Color, Layer 1	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow
Tight Buffer Color, Layer 2	Violet, Rose, Aqua, Blue*, Orange*, Green*, Brown*, Slate*, White *, Red*, Black*, Yellow*, Violet*, Rose*, Aqua*
Tight Buffer Type	TB3 (easy strip up to 10 cm)
Flame Rating	LSZH™/FRNC

Environmental Conditions

Temperature Range, Storage	-25 °C - 70 °C (-13 °F - 158 °F)
Temperature Range, Installation	-5 °C - 50 °C (23 °F - 122 °F)
Temperature Range, Operation	-20 °C - 60 °C (-4 °F - 140 °F)

General Specifications

Environment	Indoor/Outdoor
Cable Type	Tight-Buffered
Product Type	Dielectric
Fiber Category	50 µm MM (OM3)
Flame Rating	LSZH™/FRNC
Coding according to EN 60794-1-1 (DIN VDE 0888-100-1)	U-VQ(ZN)H
Application	Direct Buried , Duct , Vertical Riser , General Purpose Horizontal

Ordering Information

Weight	65 kg/km
--------	----------

FREEDM™ Tight Buffer Indoor/Outdoor Cable 24F G50 MMF ClearCurve® OM3 0.9mm TB3, Cca-s1a,d1,a1



Standards

Reaction to fire	Cca, s1a, d1, a1
RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Waterblocking	IEC 60794-1-2 F5
Flame propagation test	Flame retardant according to IEC 60332-1-2 (single cable) and IEC 60332-3-24 (bunch of cables)
Reaction to fire requirements	Reaction to fire according to EN 50575 and EN 13501-6
Smoke density	Low Smoke to IEC 61034
Halogen content test	Zero Halogen to IEC 60754-1
Level of corrosion	Non-corrosive according to IEC 60754-2

Optical Characteristics

Fiber Code	T
Fiber Name	G50/125 ULTRA-BEND 7.5
Fiber Type	Multimode
Fiber Core Diameter	50 µm
Minimum Effective Modal Bandwidth (EMB)	2000 MHz*km / -
Maximum Attenuation	2.8 dB/km / 1.0 dB/km
Min. Overfilled Launch (OFL) Bandwidth	1500 MHz*km / 500 MHz*km
Serial 1 Gigabit Ethernet	1100 MHz*km / 600 MHz*km
Serial 10 Gigabit Ethernet	300 MHz*km/ 333 MHz*km
Typical Attenuation	2.4 / 0.8
Wavelengths	850 nm / 1300 nm
Fiber Category	OM3

**FREEDM™ Tight Buffer Indoor/Outdoor
Cable 24F G50 MMF ClearCurve® OM3 0.9mm
TB3, Cca-s1a,d1,a1**

CORNING



Corning Optical Communications GmbH & Co. KG • Lelpziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea