

LC Duplex to LC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 µm ClearCurve® multimode (OM3), 1 m



CORNING

Part Number: 050502T5Z20001M

Patch cables are used for non-permanent connections between patch panels, transmission equipment, etc. Preassembled cables allow for the implementation of complete Plug & Play solutions. When such a solution is adopted with accurate dimensioning and appropriate cable routing, it is possible to install even large cabling systems rapidly.

Features and Benefits

Connectors

- LC Duplex connector according to TIA/EIA-604 -10
- All connectors are tested to FOTP -21.
- Connectors are pre-radius polished to provide the optimal end-face geometry for long-term performance.

Cable

- Low smoke (IEC 61034) and zero-halogen (LSZH), flame retardant to IEC 60332-3-24 (C) and noncorrosive to IEC 60754-2 (FRNC)
- Cables are metal free; hence, there are no ground-loop or potential-equalization problems. Completely dry design (without gel).
- Color of outer sheath: OM1, OM2 - orange; OM3, OM4 - aqua; OS2 - yellow

LC Duplex to LC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 µm ClearCurve® multimode (OM3), 1 m



Specifications

Shipping Dimensions

Height	180 mm
Width	250 mm
Depth	380 mm

Environmental Conditions

Temperature Range, Installation	-5 °C - 50 °C (23 °F - 122 °F)
Temperature Range, Operation	-10 °C - 60 °C (14 °F - 140 °F)
Temperature Range, Storage	-10 °C - 60 °C (14 °F - 140 °F)

Specifications - Connector B

Polish	PC
Insertion Loss, Typical	0.35 dB
Insertion Loss, Max.	0.5 dB
Tensile Strength Jacketed Cable	44 N
Durability	≤ 0.2 dB change, 500 rematings, FOTP-21
Keyed (security)	No
Boot Color	Aqua / White
Connector Type	LC duplex
Ferrule Material	Ceramic
Housing Color	Black
Housing Material	Composite

LC Duplex to LC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 μ m ClearCurve® multimode (OM3), 1 m



Specifications - Connector B

Boot Type	Individual
-----------	------------

Dimensions

Length	1 m
--------	-----

Outer Diameter	2 mm
----------------	------

Mechanical Specifications

Minimum Bend Radius	10 mm
---------------------	-------

Tensile Strength	300 N
------------------	-------

Crush Resistance	1000 N/10 cm
------------------	--------------

Design

Fiber Count	2
-------------	---

Outer Jacket Material	LSZH™/FRNC
-----------------------	------------

Outer Jacket Color	Aqua
--------------------	------

Specifications - Connector A

Polish	PC
--------	----

Insertion Loss, Typical	0.35 dB
-------------------------	---------

Insertion Loss, Max.	0.5 dB
----------------------	--------

Tensile Strength Jacketed Cable	44 N
---------------------------------	------

Durability	\leq 0.2 dB change, 500 rematings, FOTP-21
------------	--

LC Duplex to LC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 µm ClearCurve® multimode (OM3), 1 m



Specifications - Connector A

Keyed (security)	No
Boot Color	Aqua / White
Connector Type	LC duplex
Ferrule Material	Ceramic
Housing Color	Black
Housing Material	Composite
Boot Type	Individual

General Specifications

Fiber Category	50 µm MM (OM3)
Cable Type	Tight-Buffered
Flame Rating	LSZH™/FRNC
Cable Assembly Type	Two Fiber

Ordering Information

Packing Type	Cardboard box
--------------	---------------

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Intermateability	Compliant with TIA/EIA-604-10

LC Duplex to LC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 µm ClearCurve® multimode (OM3), 1 m



Optical Characteristics

Fiber Code	T
Fiber Name	G50/125 ULTRA-BEND 7.5
Fiber Type	Multimode
Fiber Core Diameter	50 µm
Minimum Effective Modal Bandwidth (EMB)	2000 MHz*km / -
Maximum Attenuation	2.8 dB/km / 1.0 dB/km
Min. Overfilled Launch (OFL) Bandwidth	1500 MHz*km / 500 MHz*km
Serial 1 Gigabit Ethernet	1100 MHz*km / 600 MHz*km
Serial 10 Gigabit Ethernet	300 MHz*km/ 333 MHz*km
Typical Attenuation	2.4 / 0.8
Wavelengths	850 nm / 1300 nm
Fiber Category	OM3



Corning Optical Communications GmbH & Co. KG • Lelpziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea