

LC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 µm ClearCurve® multimode (OM2), 1 m

The Corning logo is a blue square with the word "CORNING" in white, uppercase, sans-serif font.

Part Number:
055702B5Z20001M

Patch cables are used for non-permanent connections between patch panels, transmission equipment, etc. Preassembled cables allow for the implementation of complete Plug & Play solutions. When such a solution is adopted with accurate dimensioning and appropriate cable routing, it is possible to install even large cabling systems rapidly.

LC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 µm ClearCurve® multimode (OM2), 1 m

CORNING

Specifications

Shipping Dimensions

Height	180 mm
--------	--------

Width	250 mm
-------	--------

Depth	380 mm
-------	--------

Environmental Conditions

Temperature Range, Installation	-5 °C - 50 °C (23 °F - 122 °F)
---------------------------------	--------------------------------

Temperature Range, Operation	-10 °C - 60 °C (14 °F - 140 °F)
------------------------------	---------------------------------

Temperature Range, Storage	-10 °C - 60 °C (14 °F - 140 °F)
----------------------------	---------------------------------

Specifications - Connector B

Polish	PC
--------	----

Insertion Loss, Typical	0.35 dB
-------------------------	---------

Insertion Loss, Max.	0.5 dB
----------------------	--------

Tensile Strength Jacketed Cable	44 N
---------------------------------	------

Durability	≤ 0.2 dB change, 1000 rematings, FOTP-21
------------	--

Keyed (security)	No
------------------	----

Boot Color	Black / White
------------	---------------

Connector Type	SC Duplex
----------------	-----------

Ferrule Material	Ceramic
------------------	---------

Housing Color	Black
---------------	-------

Housing Material	Composite
------------------	-----------

LC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 µm ClearCurve® multimode (OM2), 1 m

CORNING

Specifications - Connector B

Boot Type	Individual
-----------	------------

Dimensions

Length	1 m
--------	-----

Outer Diameter	2 mm
----------------	------

Mechanical Specifications

Minimum Bend Radius	10 mm
---------------------	-------

Tensile Strength	300 N
------------------	-------

Crush Resistance	1000 N/10 cm
------------------	--------------

Design

Fiber Count	2
-------------	---

Outer Jacket Material	LSZH™/FRNC
-----------------------	------------

Outer Jacket Color	Orange
--------------------	--------

Specifications - Connector A

Polish	PC
--------	----

Insertion Loss, Typical	0.35 dB
-------------------------	---------

Insertion Loss, Max.	0.5 dB
----------------------	--------

Tensile Strength Jacketed Cable	44 N
---------------------------------	------

Durability	≤ 0.2 dB change, 500 rematings, FOTP-21
------------	---

LC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 µm ClearCurve® multimode (OM2), 1 m

CORNING

Specifications - Connector A

Keyed (security)	No
Boot Color	Black / White
Connector Type	LC duplex
Ferrule Material	Ceramic
Housing Color	Black
Housing Material	Composite
Boot Type	Individual

General Specifications

Product Category	Core Product
Cable Type	Tight-Buffered
Flame Rating	LSZH™/FRNC
Cable Assembly Type	Two Fiber

Ordering Information

Packing Type	Cardboard box
--------------	---------------

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Optical Characteristics

Fiber Code	T
------------	---

LC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.0 mm legs 50 µm ClearCurve® multimode (OM2), 1 m

CORNING

Optical Characteristics

Fiber Name	G50/125 ULTRA-BEND 7.5
Fiber Type	Multimode
Fiber Core Diameter	50 µm
Minimum Effective Modal Bandwidth (EMB)	950 MHz*km / -
Maximum Attenuation	2.8 dB/km / 1.0 dB/km
Min. Overfilled Launch (OFL) Bandwidth	700 MHz*km / 500 MHz*km
Serial 1 Gigabit Ethernet	750 MHz*km 600 MHz*km
Serial 10 Gigabit Ethernet	150 MHz*km / -
Typical Attenuation	2.4 / 0.8
Wavelengths	850 nm / 1300 nm
Fiber Category	OM2



Corning Optical Communications GmbH & Co. KG • Lelpziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea