

**SC Duplex to SC Duplex Patch cord, 2 F,
Zipcord Tight-Buffered Cable, LSZH, 2.8 mm
legs 62.5 µm multimode (OM1), 2 m**

CORNING

**Part Number:
575702K5Z41002M**

SC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.8 mm legs 62.5 μm multimode (OM1), 2 m



Specifications

Environmental Conditions	
Temperature Range, Storage	-25 °C - 70 °C (-13 °F - 158 °F)
Temperature Range, Installation	-5 °C - 50 °C (23 °F - 122 °F)
Temperature Range, Operation	-10 °C - 60 °C (14 °F - 140 °F)

Specifications - Connector B	
Polish	PC
Insertion Loss, Typical	0.35 dB
Insertion Loss, Max.	0.5 dB
Tensile Strength Jacketed Cable	44 N
Durability	≤ 0.2 dB change, 1000 rematings, FOTP-21
Keyed (security)	No
Boot Color	Black / White
Connector Type	SC Duplex
Ferrule Material	Ceramic
Housing Color	Beige
Housing Material	Composite
Boot Type	Individual

Dimensions	
Length	2 m
Outer Diameter	2.8 mm

SC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.8 mm legs 62.5 μm multimode (OM1), 2 m



Mechanical Specifications

Minimum Bend Radius	30 mm
Tensile Strength	400 N
Crush Resistance	1000 N/10 cm

Design

Fiber Count	2
Outer Jacket Material	LSZH™ /FRNC
Outer Jacket Color	Orange

Specifications - Connector A

Polish	PC
Insertion Loss, Typical	0.35 dB
Insertion Loss, Max.	0.5 dB
Tensile Strength Jacketed Cable	44 N
Durability	≤ 0.2 dB change, 1000 rematings, FOTP-21
Keyed (security)	No
Boot Color	Black / White
Connector Type	SC Duplex
Ferrule Material	Ceramic
Housing Color	Beige
Housing Material	Composite
Boot Type	Individual

SC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.8 mm legs 62.5 μm multimode (OM1), 2 m



General Specifications

Cable Type	Tight-Buffered
Flame Rating	LSZH™ /FRNC
Cable Assembly Type	Two Fiber

Shipping Dimensions

Height	180 mm
Width	250 mm
Depth	380 mm

Ordering Information

Packing Type	Cardboard box
--------------	---------------

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Optical Characteristics

Fiber Code	K
Fiber Name	G62.5L/125 InfiniCor® 300
Fiber Type	Multimode
Fiber Core Diameter	62.5 μm
Minimum Effective Modal Bandwidth (EMB)	220 MHz*km / -
Maximum Attenuation	2.8 dB/km / 1.0 dB/km

SC Duplex to SC Duplex Patch cord, 2 F, Zipcord Tight-Buffered Cable, LSZH, 2.8 mm legs 62.5 μm multimode (OM1), 2 m



Optical Characteristics

Min. Overfilled Launch (OFL) Bandwidth	200 MHz*km / 600 MHz*km
Serial 1 Gigabit Ethernet	300 MHz*km / 550 MHz*km
Serial 10 Gigabit Ethernet	33 MHz*km / -
Typical Attenuation	2.9 / 0.7
Wavelengths	850 nm / 1300 nm
Fiber Category	OM1



Corning Optical Communications GmbH & Co. KG • Lelpziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea