


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

 $-B \pm .063$ REF. -F REF.-NYLON PLASTIC CINCH RING



								<del></del>			
PANDUIT PART NO.	in	MAX. (mm)	/ \	B in (mm)	in (mm)	in (mm)	in (mm)	F in (mm)	$\sim$	MIN. LOOP TENSILE lbs.	CROSS SECTION
HLC3S	2.0 (50.8)	3.0 (76.2)	.080 (2.0)	.750 (19.1)			1.10			50 (222)	STANDARD
HLC5S	3.0 (76.2)	5.0 (127)	.080 (2.0)							50 (222)	STANDARD

NOTES:

- 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR. 2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.

								TITLE	1
								TAK-TY HOOK \$ LOOP CABLE TIES	
Α								HLC SERIES	
								CUSTOMER DRAWING	
								SS-26935/AD  DATASET FILE NAME  OD COORSE (AD	
	9	01-25-19	SAT	DWW	ML	C. REMOVED WEIGHT COLUMN.	SS-26935	SS_26935/AD MATERIAL:	
	8	3/16/18	JSP	DWW	ML	B. ADDED TOLERNACE TO DIM. B.	SS-26935	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] WOVEN NYLON	
	7	5/20/14	RVU	DJW	KLN	A: .080 WAS .100. D: .183 WAS .156. G: .080 WAS .100. REMOVE .150 LEADER.	GAECN01997	.x ± .xxx ± .030 [.762] HOOK/LOOP COLOR: BLACK	
	6	3/31/06	ERW			ADDED "APPROXIMATE WEIGHT PER 100PCS" COLUMN.	26935	THIRD ANGLE PROJECTION  THIRD ANGLE SS-26935	
	REV	DATE	ВҮ	CHK	APR	DESCRIPTION	ECN	DRAWN BY   DATE   CHK   SCALE   KET   11/23/94   HVP   NONE   SHT 1 0F 1   A	
2						2		1	•