

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	DESCRIPTION	FIBER COUNT	DIAMETER	FLAME RATING	BEND RADIUS (INSTALLATION)	BEND RADIUS (LONG TERM)	TENSILE LOAD (INSTALLATION)	TENSILE LOAD (LONG TERM)	ATTENUATION				
FSKP506	MULTIMODE 50/125 OM2 INDOOR/OUTDOOR CABLE	6	0.20" [5.0mm]	OFNP	4.0" [10.2cm]	2.0" [5.1mm]	100lbs [440 N]	30lbs [133 N]	3.5dB/km @ 850nm 1.5dB/km @ 1300nm				
FSKR506			0.24" [5.6mm]	OFNR	4.4" [11.2mm]	2.2" [5.6mm]							
FSKP508		8	0.20" [5.0mm]	OFNP	4.0" [10.2mm]	2.0" [5.1mm]							
FSKR508			0.25" [6.2mm]	OFNR	5.0" [12.7mm]	2.5" [6.4mm]							
FSKP606	MULTIMODE 62.5/125 OM1 INDOOR/OUTDOOR CABLE	6	0.20" [5.0mm]	OFNP	4.0" [10.2cm]	2.0" [5.1mm]			100lbs [440 N]	30lbs [133 N]	3.5dB/km @ 850nm 1.0dB/km @ 1300nm		
FSKR606			0.24" [5.6mm]	OFNR	4.4" [11.2mm]	2.2" [5.6mm]							
FSKP608		8	0.20" [5.0mm]	OFNP	4.0" [10.2mm]	2.0" [5.1mm]							
FSKR608			0.25" [6.2mm]	OFNR	5.0" [12.7mm]	2.5" [6.4mm]							
FOKPX06	MULTIMODE 50/125 OM3 INDOOR/OUTDOOR CABLE	6	0.20" [5.0mm]	OFNP	4.0" [10.2cm]	2.0" [5.1mm]					100lbs [440 N]	30lbs [133 N]	3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FOKRX06			0.24" [5.6mm]	OFNR	4.4" [11.2mm]	2.2" [5.6mm]							
FOKPX08		8	0.20" [5.0mm]	OFNP	4.0" [10.2mm]	2.0" [5.1mm]							
FOKRX08			0.25" [6.2mm]	OFNR	5.0" [12.7mm]	2.5" [6.4mm]							
FOKPZ06	MULTIMODE 50/125 OM4 INDOOR/OUTDOOR CABLE	6	0.20" [5.0mm]	OFNP	4.0" [10.2cm]	2.0" [5.1mm]	100lbs [440 N]	30lbs [133 N]					3.5dB/km @ 850nm 1.5dB/km @ 1300nm
FOKRZ06			0.24" [5.6mm]	OFNR	4.4" [11.2mm]	2.2" [5.6mm]							
FOKPZ08		8	0.20" [5.0mm]	OFNP	4.0" [10.2mm]	2.0" [5.1mm]							
FOKRZ08			0.25" [6.2mm]	OFNR	5.0" [12.7mm]	2.5" [6.4mm]							
FSKP906	SINGLEMODE 9/125 INDOOR/OUTDOOR CABLE	6	0.20" [5.0mm]	OFNP	4.0" [10.2cm]	2.0" [5.1mm]			100lbs [440 N]	30lbs [133 N]			0.7dB/km @ 1310nm 0.7dB/km @ 1550nm
FSKR906			0.24" [5.6mm]	OFNR	4.4" [11.2mm]	2.2" [5.6mm]							
FSKP908		8	0.20" [5.0mm]	OFNP	4.0" [10.2mm]	2.0" [5.1mm]							
FSKR908			0.25" [6.2mm]	OFNR	5.0" [12.7mm]	2.5" [6.4mm]							

						TITLE 6, 8 FIBER INDOOR/OUTDOOR CABLE WITH 900um BUFFERED FIBERS CUSTOMER DRAWING						
						ITEM REVISION NAME M02055JG/00						
						DATASET FILE NAME M02055JG_DC/00A						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .xxx ± .010 [0.3] .xx ± .03 [0.8] ANGLES ±			PART NO. SEE TABLE			
00 02-04-14 SAT WMA TCB RELEASED TO PRODUCTION						M02055JG-DC			DRAWING NUMBER: M02055JG-DC			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 2 OF 2	SIZE
							SAT	02-04-14	WMA	NONE		A