

DS-2TP21B-6AVF/W¹

Thermographic Handheld Camera



- Resolution: 160 × 120 Thermal, 8 MP Optical
- Thermographic Accuracy up to ±0.9° F (±0.5° C) at 3.3 ft to 6.6 ft (1.0 m to 2.0 m)
- Display Fusion of Thermal and Optical Views
- 640 × 480 Resolution 3.5" LCD Touch Display
- Supports Live View on PC or Mobile Device
- Supports Audio Intercom
- Supports Color Highlight Alarm and Audio Alarm

The Hikvision DS-2TP21B-6AVF/W Thermographic handheld camera is specially designed for temperature measurement applications, where heat leaks and other abnormal changes in temperature must be identified.

It is equipped with a 160×120 resolution thermal detector and 8 MP optical resolution. It combines thermal and optical images into a fusion display.

Available Models:

DS-2TP21B-6AVF/W













Canada Disclaimer: Hikvision's Thermographic Cameras are designed for immediate detection and preliminary screening of elevated skin-surface temperature in hightraffic areas. When measuring core body temperature, please verify through the use of clinical measurement devices and/or by consulting a medical professional. Hikvision's Thermographic Cameras must be used in accordance with local laws and reg-










 $^{^{}m 1}$ U.S. Disclaimer: Hikvision USA Inc. products depicted herein are not FDA approved medical devices and are not intended for use in the diagnosis of disease or other conditions, or in the cure, mitigation, treatment, or prevention of disease. When configured correctly, the Hikvision products discussed herein can identify elevated human skin-surface temperature relative to a sample population.

Specifications

	DS-2TP21B-6AVF/W
Thermal Module	
	Uncooled focal plane arrays
	25 Hz: 160 × 120
Pixel Pitch	
Response Waveband	8 µm to 14 µm
	<40 mK (@ 25° C, F#=1.0)
Field of View	
	6.2 mm (manual focus)
	2.74 mrad
Aperture	
Optical Module	
Picture Resolution	Configurable: 2 MP, 5 MP, 8 MP
Video Resolution	
	640 × 480 resolution 3.5" LCD touch display
	Black hot, white hot, red hot, rainbow, ironbow, fusion, rain
Image Display	
	Thermal: 1x, 2x, 4x
Ihermal/Optical	Thermal/optical/fusion image/picture-in-picture
	Supports thermal view in optical view
	Supports thermal view and optical view combined
	Supports on-board video recording
Thermography	
Rules	Maximum temperature; minimum temperature; center temperature; custom point/line/area thermography
Recommended Subject Distance	±0.9° F (±0.5° C) at 3.3 ft to 6.6 ft (1.0 m to 2.0 m)
Recommended Subject distance Battery	
	Removable, li-ion battery rechargeable via USB-C port
	5 hours in normal temperature, with Wi-Fi and Bluetooth off
Battery Operating Time	4 hours in normal temperature, with Wi-Fi and Bluetooth on
Storage	Built-in microSD slot, 128 GB maximum (16 GB pre-installed), which can be accessed via PC through the USB-C port
Photo	Thermal/optical/fusion image
Video	Thermal/optical/fusion image
Wi-Fi	Supported
Text Comment	
Voice Comment	
Language	
General	-
	5 VDC/2 A
Power Consumption	
Hardware Interface	
	50° to 95° F (10° to 35° C) indoor and windless environment use only
Protection Level	
Drop Test Height	
	LCD touchscreen
Mounting Option	
	9.6" × 3.9" × 4.1" (244 mm × 100 mm × 104 mm)
Weight	With battery: 1.44 lb (653 g)
	Without battery: 1.13 lb (511 g)



Dimensions



Accessories





Box Contents (Subject To Change)

User manual
5 V @ 2.0 A power supply
Power plug adapters (6 types)
USB-C cable (USB-C to USB-A)
Wrist strap (pre-installed)
3.7 V, 5000 mAh li-ion battery (pre-installed)
16 GB microSDHC card (pre-installed)
Protective hard case

