

OVERVIEW

Upgradeable Unit Level EC Monitored rPDUs provide reliable power distribution to critical IT equipment while delivering a comprehensive view of input level power usage via remote network access. Includes environmental monitoring capabilities to obtain realtime environmental metrics. Upgrade the hot-swappable monitoring device on select units to leverage new technologies and accommodate changing business needs.

Benefits

- Reliable power distribution with local and remote power monitoring options offer quick access to critical power usage information to evaluate energy usage trends and maximize uptime.
- **Environmental monitoring** capabilities with the addition of optional environmental sensors ensure users have critical infrastructure data at their fingertips to prevent climate-related equipment failure and system downtime.
- Gather comprehensive power data at the palm of your hand with the use of the Vertiv VLC mobile app.
- Fault-Tolerant Daisy Chaining with RSTP simplifies intelligent rPDU connectivity and ensures data is reported even when a break in the network chain occurs. Supports up to 40 rPDUs.
- Every unit is 100% tested for reliability and functionality.



Part #: VP8830

Model Number: MN03E4B0-24D203-2TL5A0A10-S

Category: Monitored

Sub Category: Unit Level EC

Power Configuration: 20A, 120V, 1.9kW

Physical Configuration: 66in / 1683mm, Vertical

Product Summary: VP8830 - rPDU, Monitored Unit Level EC, 20A, 120V, 1.9kW, Vertical, (24) NEMA 5-20R,

10ft power cord with L5-20P, Black Powder Coat.

Monitoring: Input power monitoring. Environmental monitoring via optional remote sensors. Daisy

chain Ethernet connectivity. Local high visibility LED display.

Plug Form: Receptacle:





L5-20P

NEMA 5-20R (Quantity: 24)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Monitoring	Input power monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.
Monitoring Level 1	Phase (A) Monitoring (kWh, W, VA, PF, V, A)
	Power Measurements Compliant with ANSI C12.1 and IEC 62053 21 at 1% Accuracy Class Requirements
VLC Support	Yes
Quantity Of Inputs	1
Voltage	100-120V
Current	20A
VA per Input (Load Capacity)	1.9kW (120V)
Frequency	50/60Hz
Over Current Protection	None
Switch	No
Scrolling / Rotatable Digital Display	Yes
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Power Entry Location	Bottom Front
Plug Type	NEMA L5-20P Twistlock
Receptacle/Socket Type #1	NEMA 5-20R
- Quantity on Face	24
- Style	Duplex
- Voltage per Receptacle/Socket	120V
Internal RMS Voltage Sensor	Yes
Internal RMS Current Sensor	Yes
Network Connection	Dual 10/100Mbps Ethernet
Protocols Supported	DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RADIUS, RSTP, SSH, SMTP, SNMP (v1/v2c/v3), Syslog, TACACS+
Data Access Formats	CSV datalog, JSON API, JSON datalog
USB Support	Yes
IP Reset Button	Yes
Hard Reboot Button	Yes
Serial Connection	RS232 via RJ45
Remote Sensor RJ Connection Jacks	1 (Supports up to 16 Sensors)
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	66in / 1683mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes, TAA Compliant
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years

Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 2.0in x 2.0in
Shipped Weight	15lbs (6.8kg)