

# **Product Name**

Novanex PoE Analog Clock •ONTA12-BK(single-sided) •ONTA12DS-BK (double-sided)

## **Product Manufacturer**

Novanex, Inc. 1180 Seminole Trail, # 327 Charlottesville, VA 22901 Phone: 434-509-1108 Email: sales@novanexsolutions.com Web: www.novanexsolutions.com

# **Product Description**

### Features

Novanex PoE analog clocks are specifically designed for facilities that require accurate, highly visible, synchronized time.

The clocks are built on Power-over-Ethernet technology. Time and energy-efficient power are provided by the network through an powered Ethernet cable making them easy to install and simple to maintain.

Novanex clocks to not require a master clock, electrical outlet or batteries, simply a powered switch or single port power injector. Clocks may be backed up using a centralized Uninterrupted Power Supply (UPS). Novanex clocks do not rely on an "atomic time signal" for updates, just common access to a network time server.



ONTA12DS-BK - Wall-mounted; double-sided



ONTA12-BK - Surface Mounted, single-sided

### **Benefits**

- Continual synchronization
- · Easy installation
- · Easy maintenance and management
- Energy efficiency
- Reliability
- Three-year warranty
- Novanex POE clocks are assembled in the USA



ONTA12DS-BK - Ceiling-mounted; double-sided



# Warranty

Novanex warranties all products for a period of three years from date of purchase.

### Maintenance

Novanex PoE clocks are powered directly from the network. Maintenance consists of periodic physical and visual checks on clocks and verification of the clocks' network configuration. A clock monitoring and connection alerting system is available. Surfaces can be cleaned with mild detergent. Contact Novanex for literature describing resistance qualities with other cleaning agents.

## **Specifications**

Power supplied over standard Cat-5 cabling using the IEEE 802.3af (PoE+ compatible) Power over Ethernet standard Low power consumption—3 watts (single) 4 watts (double) No master clock or serial connection required UL 60950-1, CAN/C22.2 ETL Listed CE Marked, RoHS compliant

## **Technical Specification Table**

# **Availability and Cost**

Novanex maintains stock of most models to allows order fulfillment within 1-2 business days. For current inventory and pricing inquires contact your authorized distributor: <u>http://novanex-solutions-inc.myshopify.com/apps/storelocator</u>

Or contact Novanex directly: sales@novanexsolutions.com +1-434-509-1108

# **Technical Services**

Contact Novanex for installation and user guides.

12-hour circular clock face visible from 100+ feet (30 m) Highly accurate to within ±1 second Time set automatically by SNTP (Simple Network Time Protocol) Automatic adjustment for Daylight Saving Time Compatible with DHCP or static IP addressable

Compatible with DHCP or static IP addressable 10/100BaseT Ethernet

	Single-sided Clocks	Double-sided Clocks
Model	ONTA12-BK	ONTA12DS-BK
Cabinets	Diameter: 12 <sup>3/4</sup> " (29.5 cm)	Diameter: 12 <sup>3/4</sup> " (29.5 cm)
	Depth: 1 7/8 " (5.1 cm)	Depth: 4 " (10.8 cm)
	Material: injection-molded black ABS plastic	Material: black injection-molded ABS plastic
Weight	1.6 lb. (0.73 kg) including bracket	7 lb. (3.2 kg) including bracket
Viewing Distance	100+ feet	100+ feet
Accuracy	±1 second	±1 second
Operating temperature	32–104° F (0–40 C)	32–104° F (0–40 C)
Operating humidity	95% maximum, non-condensing	95% maximum, non-condensing
Power consumption	4 watts, single PoE cable	4 watts, single PoE cable drives both clocks
Mounting option	Ceiling or cantilever wall mount	Ceiling or cantilever wall mount

Note: specifications and design are subject to change without notice.