

AXIS Q1645 Network Camera

High-speed video with 1/2" sensor and i-CS lens

With AXIS Q1645 Network Camera it's easier than ever to capture details even in challenging lighting or low light. The 1/2" sensor and i-CS lens ensure sharp images in high resolution at full frame rate, and with Forensic WDR and Lightfinder, AXIS Q1645 provides superior light sensitivity and excellent image usability. AXIS Q1645 enables proactive surveillance with preinstalled AXIS Motion Guard and AXIS Fence Guard, and orientation aid with compass rose and street names for quick orientation with multiple monitors. Zipstream optimizes the video stream to maintain high video quality while saving bandwidth and storage.

- > HDTV 1080p/2 MP resolution at up to 100/120 fps
- > 1/2" sensor
- > Forensic WDR and Lightfinder
- > Electronic image stabilization (EIS)
- > AXIS Motion Guard and AXIS Fence Guard







AXIS Q1645 Network Camera

Camera			AXIS Digital Autotracking, AXIS Perimeter Defender
Image sensor	1/2" progressive scan RGB CMOS		Support for AXIS Camera Application Platform enabling
Lens	Varifocal, IR corrected, CS-mount 3.9-10.0 mm, F1.5 2 MP (16:9): Horizontal field of view: 109°-42° Vertical field of view: 58°-23° i-CS lens	Event conditions	installation of third-party applications, see axis.com/acap Analytics, external input, edge storage events, virtual inputs through API Audio: audio detection Device status: above operating temperature, above or below operating temperature, IP address
Day and night	Automatically removable infrared-cut filter		removed, network lost, new IP address, storage failure, system ready, within operating temperature
Minimum illumination	1080p 25/30 fps with WDR and Lightfinder: Color: 0.05 lux, at 50 IRE F1.5, B/W: 0.01 lux, at 50 IRE F1.5 1080p 50/60 fps with WDR and Lightfinder: Color: 0.1 lux, at 50 IRE F1.5, B/W: 0.02 lux, at 50 IRE F1.5 1080p 100/120 fps: Color: 0.2 lux, at 50 IRE F1.5, B/W: 0.04 lux, at 50 IRE F1.5 1080p 25/30 fps with WDR and Lightfinder: Color: 0.02 lux, at 50 IRE F0.9, B/W: 0.004 lux, at 50 IRE F0.9	Event actions	Edge storage: recording ongoing, storage disruption I/O: digital input, manual trigger, virtual input PTZ: PTZ malfunctioning, PTZ movement, PTZ preset position reached, PTZ ready Scheduled and recurring: scheduled event Video: average bitrate degradation, day-night mode, live stream open, tampering File upload: FTP, SFTP, HTTP, HTTPS, network share and email,
Shutter time	1/100000 to 2 s	Event detions	send video clip
Pan/Tilt/Zoom	Digital PTZ, uploadable PTZ driver (Pelco D pre-installed)		Notification: email, HTTP, HTTPS and TCP Overlay text, Send SNMP Trap
Video			Video and audio recording to edge storage
Video compression	H.264 (MPEG-4 Part 10/AVC), Main, Baseline and High Profile Motion JPEG		Pre- and post-alarm video buffering External output activation, day/night vision mode, play audio clip status LED, WDR mode, defog mode, PTZ control
Resolution	1920x1080 to 320x180	Data streaming	Event data
Frame rate	HDTV 1080p (1920x1080) with WDR: Up to 50/60 fps with power line frequency 50/60 Hz HDTV 1080p (1920x1080) without WDR: Up to 100/120 fps with power line frequency 50/60 Hz	Built-in installation aids	i-CS: Remote zoom and focus Other lens: Remote back focus Traffic wizard, pixel counter, levelling assistant, autorotation
Video streaming	Multiple, individually configurable streams in H.264 and Motion	General	Martin V
	JPEG Axis Zipstream technology in H.264 Controllable frame rate and bandwidth	Casing	Metal (zinc) Color lid: Silver - RAL 9006 Color chassi: Black - NCS S 9000-N
	VBR/ABR/MBR H.264	Sustainability	PVC free
Image settings	Saturation, contrast, brightness, sharpness, Forensic WDR – 120 dB, white balance, day/night threshold, exposure mode, exposure zones, compression, orientation: auto, 0°, 90°, 180°, 270° including corridor format, mirroring of images, dynamic text overlay, image overlay, privacy masks, defogging, noise reduction, electronic image stabilization, barrel distortion correction, orientation aid, fine tuning of behavior at low light Scene profiles: forensic, vivid, traffic overview, backlit entrance	Memory	1 GB RAM, 512 MB Flash
		Power Connectors	Power over Ethernet (PoE) IEEE 802.3af/802.3at Type 1 Class 3 Typical 4.5 W, max 9.1 W 8–28 V DC, typical 4.3 W, max 9.5 W Shielded RJ45 10BASE-T/100BASE-TX PoE
			I/O: 6-pin 2.5 mm terminal block for four configurable inputs/outputs (12 V DC output, max load 50 mA) RS485/RS422, 2 pcs, 2 pos, full duplex, terminal block
Audio Audio streaming	Two-way, full duplex		3.5 mm mic/line in, 3.5 mm line out
Audio encoding	AAC-LC 8/16/32/48 kHz, G.711 PCM 8 kHz, G.726 ADPCM 8 kHz,		i-CS connector (compatible with P-Iris and DC-iris)
	Opus 8/16/48 kHz Configurable bit rate	Storage	Support for microSD/microSDHC/microSDXC card Support for SD card encryption Support for recording to network-attached storage (NAS)
Audio input/output	External balanced/unbalanced microphone or line input, line output, built-in microphone, automatic gain control		For SD card and NAS recommendations see axis.com
Network	24 bit AD/DA-conversion	Operating conditions	-20 °C to 60 °C (-4 °F to 140 °F) Humidity 10-85% RH (non-condensing)
Security	Password protection, IP address filtering, HTTPS ^a encryption,	Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F) Humidity 5-95% RH (non-condensing)
···· • ,	IEEE 802.1x (EAP-TLS) ^a network access control, digest authentication, user access log, centralized certificate management, brute force delay protection, signed firmware	Approvals	EMC EN 55032 Class A, EN 61000-3-2, EN 61000-3-3, EN 55024,
Supported protocols	IPv4, IPv6 USGv6, HTTP, HTTP/2, HTTPS³, SSL/TLS³, QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, Bonjour, UPnP TM , SNMPv1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SFTP, SRTP, TCP, UDP, IGMP, RTCP, ICMP, DHCPv4/v6, ARP, SOCKS, SSH, LLDP, CDP, MQTT, Syslog.		EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class A, ICES-003 Class A, VCCI Class A, RCM AS/NZS CISPR 32 Class A, KCC KN32 Class A, KN35 Safety IEC/EN/UL 62368-1, IS 13252 Environment
System integro	ntion		IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-6, IEC 60068-2-14
Application Programming Interface	Open API for software integration, including VAPIX® and AXIS Camera Application Platform; specifications at axis.com AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF Profile G, ONVIF Profile S, and ONVIF Profile T,		IEC 60068-2-27, IEC 60068-2-78 Network NIST SP500-267
meriaec		Dimensions	82 x 66 x 210 mm (3.23 x 2.60 x 8.25 in)
A b. d'	specifications at onvif.org	Weight	950 g (2.1 lb)
Analytics	Included AXIS Video Motion Detection, AXIS Fence Guard, AXIS Motion Guard, AXIS Loitering Guard, active tampering	Included accessories	Stand, connector kit, resistorx® T20 tool, installation guide, Windows® decoder 1-user license
	alarm, audio detection Supported		

WWW.CIXIS.COM T10113090/EN/M12.3/2010

Optional accessories	AXIS T90B Illuminators, AXIS T92G Housings, AXIS T93F Housings, Axis network cable couplers, AXIS T8129 PoE Extender, AXIS T8415 Wireless Installation Tool, Axis midspans For more accessories, see axis.com AXIS Companion, AXIS Camera Station, video management software from Axis Application Development Partners available at axis.com/vms		
Video management software			
Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese		
Warranty	5-year warranty see axis com/warranty		

a. This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (openssl.org), and cryptographic software written by Eric Young (eay@cryptsoft.com).

Environmental responsibility:

axis.com/environmental-responsibility

