

DURO 200[®] Series




200°C

**600V
1,000V**

**UL 3512/3604
UL 3604/3644**

HARBOUR CANADA

DURO 200[®]



Description

DURO 200[®] Series is a full line of extremely durable and highly flexible high temperature lead wires to be used in commercial, industrial and household appliances and equipment. DURO 200[®] high grade crush-resistant silicone rubber provides an unsurpassed combination of electrical and mechanical performance as well as handling characteristics. Available in different insulation thicknesses and also with or without fiberglass reinforcement. Standard colors are white, black and red. Other colors are available upon request.

Construction

Conductors: Stranded tinned copper or nickel-plated copper

Insulation: High grade crush-resistant silicone rubber, optional fiberglass reinforcement

Applications

Fully enclosed internal wiring of appliances, electrical equipment and lighting fixtures

| DURO 200 [®] Series | SR | XR35 | XR40 | XR45 | XG | XG VW-1 |
|------------------------------|-----------|-----------|-----------|-----------|-----------|------------|
| UL Styles | 3512/3604 | 3512/3604 | 3512/3604 | 3512/3604 | 3512/3604 | 3512/3604 |
| | 3604/3644 | 3604/3644 | 3604/3644 | 3604/3644 | 3604/3644 | 3604/3644 |
| Wire Diameter - 18 AWG | 0.108" | 0.116" | 0.126" | 0.136" | 0.122" | 0.122" |
| Fiberglass Reinforcement | No | No | No | No | Yes | Yes |
| Electrical Performance | | | | | | |
| Dielectric | Good | Very Good | Very Good | Excellent | Good | Good |
| Mechanical Performance | | | | | | |
| Abrasion | Fair | Good | Very Good | Excellent | Good | Good |
| Compression | Fair | Good | Very Good | Excellent | Good | Good |
| Handling Characteristics | | | | | | |
| Cutting | Very Good | Very Good | Very Good | Very Good | Good | Good |
| Stripability | Very Good | Very Good | Very Good | Very Good | Good | Good |
| Flexibility | Very Good | Very Good | Very Good | Very Good | Good | Good |

DURO 200[®] Series



DURO 200 SR, 200C/600V, UL 3512/3604, CSA AWM I A/B FT2

| Part Number | Size (AWG) | Stranding | Plating | Insulation Thickness (mil) | Outer Diameter (in.) | Weight (lb/1,000 ft) |
|-------------|------------|-----------|---------|----------------------------|----------------------|----------------------|
| F04796 | 22 | 7/.0096 | 2% NPC | 31 | 0.091 | 5 |
| F04774 | 20 | 7/.0121 | 2% NPC | 31 | 0.098 | 7 |
| F04477 | 18 | 7/.0152 | TPC | 31 | 0.108 | 9 |
| F04469 | 16 | 7/.0192 | TPC | 31 | 0.120 | 13 |
| F04478 | 14 | 7/.0242 | TPC | 31 | 0.133 | 18 |
| F04728 | 12 | 19/.0185 | TPC | 31 | 0.150 | 26 |
| F04911 | 10 | 19/.0234 | TPC | 46 | 0.205 | 45 |
| F04991 | 8 | 54/.0175 | TPC | 46 | 0.232 | 65 |
| F04992 | 6 | 84/.0180 | TPC | 61 | 0.300 | 107 |
| F04957 | 4 | 133/.0180 | TPC | 61 | 0.383 | 164 |
| F04956 | 2 | 259/.0160 | TPC | 61 | 0.451 | 256 |
| F01306 | 1 | 259/.0180 | TPC | 81 | 0.534 | 329 |
| F01362 | 1/0 | 259/.0200 | TPC | 81 | 0.572 | 409 |
| F01363 | 2/0 | 259/.0226 | TPC | 81 | 0.627 | 487 |
| F01364 | 3/0 | 259/.0255 | TPC | 81 | 0.677 | 618 |
| F01365 | 4/0 | 259/.0290 | TPC | 96 | 0.778 | 768 |

DURO 200 SR, 200C/600V-1000V, UL 3604/3644, CSA AWM I A/B FT2

| Part Number | Size (AWG) | Stranding | Plating | Insulation Thickness (mil) | Outer Diameter (in.) | Weight (lb/1,000 ft) |
|-------------|------------|-----------|---------|----------------------------|----------------------|----------------------|
| F07080 | 22 | 7/.0096 | 2% NPC | 31 | 0.091 | 5 |
| F07081 | 20 | 7/.0121 | 2% NPC | 31 | 0.098 | 7 |
| F07082 | 18 | 7/.0152 | TPC | 31 | 0.108 | 9 |
| F07083 | 16 | 7/.0192 | TPC | 31 | 0.120 | 13 |
| F07084 | 14 | 7/.0242 | TPC | 31 | 0.133 | 18 |
| F07085 | 12 | 19/.0185 | TPC | 31 | 0.150 | 26 |
| F07086 | 10 | 19/.0234 | TPC | 46 | 0.205 | 45 |
| F07087 | 8 | 54/.0175 | TPC | 46 | 0.232 | 65 |
| F07088 | 6 | 84/.0180 | TPC | 61 | 0.300 | 107 |
| F07089 | 4 | 133/.0180 | TPC | 61 | 0.383 | 164 |
| F07090 | 2 | 259/.0160 | TPC | 61 | 0.451 | 256 |
| F07091 | 1 | 259/.0180 | TPC | 81 | 0.534 | 329 |
| F07092 | 1/0 | 259/.0200 | TPC | 81 | 0.572 | 409 |
| F07093 | 2/0 | 259/.0226 | TPC | 81 | 0.627 | 487 |
| F07094 | 3/0 | 259/.0255 | TPC | 81 | 0.677 | 618 |
| F07095 | 4/0 | 259/.0290 | TPC | 96 | 0.778 | 768 |

Compliance: UL Listed File No. E76475. CSA Certified LL37586. All dimensions listed are nominal and subject to normal manufacturing tolerances. Specific marking and/or striping available. Other constructions are available upon request.

DURO 200[®] Series



DURO 200 XR35, 200C/600V, UL 3512/3604, CSA AWM I A/B FT2

| Part Number | Size (AWG) | Stranding | Plating | Insulation Thickness (mil) | Outer Diameter (in.) | Weight (lb/1,000 ft) |
|-------------|------------|-----------|---------|----------------------------|----------------------|----------------------|
| F07020 | 22 | 7/.0096 | 2% NPC | 35 | 0.099 | 6 |
| F07021 | 20 | 7/.0121 | 2% NPC | 35 | 0.106 | 7 |
| F07022 | 18 | 7/.0152 | TPC | 35 | 0.116 | 10 |
| F07023 | 16 | 7/.0192 | TPC | 35 | 0.128 | 14 |
| F07024 | 14 | 7/.0242 | TPC | 35 | 0.141 | 19 |
| F07025 | 12 | 19/.0185 | TPC | 35 | 0.158 | 28 |
| F07026 | 10 | 19/.0234 | TPC | 50 | 0.213 | 46 |
| F07027 | 8 | 54/.0175 | TPC | 50 | 0.240 | 67 |
| F07028 | 6 | 84/.0180 | TPC | 65 | 0.308 | 110 |
| F07029 | 4 | 133/.0180 | TPC | 65 | 0.391 | 167 |
| F07030 | 2 | 259/.0160 | TPC | 65 | 0.459 | 260 |
| F07031 | 1 | 259/.0180 | TPC | 85 | 0.542 | 331 |
| F07032 | 1/0 | 259/.0200 | TPC | 85 | 0.580 | 413 |
| F07033 | 2/0 | 259/.0226 | TPC | 85 | 0.635 | 492 |
| F07034 | 3/0 | 259/.0255 | TPC | 85 | 0.685 | 624 |
| F07035 | 4/0 | 259/.0290 | TPC | 100 | 0.786 | 775 |

DURO 200 XR35, 200C/600V-1000V, UL 3604/3644, CSA AWM I A/B FT2

| Part Number | Size (AWG) | Stranding | Plating | Insulation Thickness (mil) | Outer Diameter (in.) | Weight (lb/1,000 ft) |
|-------------|------------|-----------|---------|----------------------------|----------------------|----------------------|
| F07120 | 22 | 7/.0096 | 2% NPC | 35 | 0.099 | 6 |
| F07121 | 20 | 7/.0121 | 2% NPC | 35 | 0.106 | 7 |
| F07122 | 18 | 7/.0152 | TPC | 35 | 0.116 | 10 |
| F07123 | 16 | 7/.0192 | TPC | 35 | 0.128 | 14 |
| F07124 | 14 | 7/.0242 | TPC | 35 | 0.141 | 19 |
| F07125 | 12 | 19/.0185 | TPC | 35 | 0.158 | 28 |
| F07126 | 10 | 19/.0234 | TPC | 50 | 0.213 | 46 |
| F07127 | 8 | 54/.0175 | TPC | 50 | 0.240 | 67 |
| F07128 | 6 | 84/.0180 | TPC | 65 | 0.308 | 110 |
| F07129 | 4 | 133/.0180 | TPC | 65 | 0.391 | 167 |
| F07130 | 2 | 259/.0160 | TPC | 65 | 0.459 | 260 |
| F07131 | 1 | 259/.0180 | TPC | 85 | 0.542 | 331 |
| F07132 | 1/0 | 259/.0200 | TPC | 85 | 0.580 | 413 |
| F07133 | 2/0 | 259/.0226 | TPC | 85 | 0.635 | 492 |
| F07134 | 3/0 | 259/.0255 | TPC | 85 | 0.685 | 624 |
| F07135 | 4/0 | 259/.0290 | TPC | 100 | 0.786 | 775 |

Compliance: UL Listed File No. E76475. CSA Certified LL37586. All dimensions listed are nominal and subject to normal manufacturing tolerances. Specific marking and/or striping available. Other constructions are available upon request.

DURO 200[®] Series



DURO 200 XR40, 200C/600V, UL 3512/3604, CSA AWM I A/B FT2

| Part Number | Size (AWG) | Stranding | Plating | Insulation Thickness (mil) | Outer Diameter (in.) | Weight (lb/1,000 ft) |
|-------------|------------|-----------|---------|----------------------------|----------------------|----------------------|
| F07040 | 22 | 7/.0096 | 2% NPC | 40 | 0.109 | 7 |
| F07041 | 20 | 7/.0121 | 2% NPC | 40 | 0.116 | 8 |
| F07042 | 18 | 7/.0152 | TPC | 40 | 0.126 | 11 |
| F07043 | 16 | 7/.0192 | TPC | 40 | 0.138 | 15 |
| F07044 | 14 | 7/.0242 | TPC | 40 | 0.151 | 20 |
| F07045 | 12 | 19/.0185 | TPC | 40 | 0.168 | 29 |
| F07046 | 10 | 19/.0234 | TPC | 55 | 0.223 | 48 |
| F07047 | 8 | 54/.0175 | TPC | 55 | 0.250 | 69 |
| F07048 | 6 | 84/.0180 | TPC | 70 | 0.318 | 112 |
| F07049 | 4 | 133/.0180 | TPC | 70 | 0.401 | 171 |
| F07050 | 2 | 259/.0160 | TPC | 70 | 0.469 | 264 |
| F07051 | 1 | 259/.0180 | TPC | 90 | 0.552 | 336 |
| F07052 | 1/0 | 259/.0200 | TPC | 90 | 0.590 | 418 |
| F07053 | 2/0 | 259/.0226 | TPC | 90 | 0.645 | 498 |
| F07054 | 3/0 | 259/.0255 | TPC | 90 | 0.695 | 629 |
| F07055 | 4/0 | 259/.0290 | TPC | 105 | 0.796 | 781 |

DURO 200 XR40, 200C/600V-1000V, UL 3604/3644, CSA AWM I A/B FT2

| Part Number | Size (AWG) | Stranding | Plating | Insulation Thickness (mil) | Outer Diameter (in.) | Weight (lb/1,000 ft) |
|-------------|------------|-----------|---------|----------------------------|----------------------|----------------------|
| F07140 | 22 | 7/.0096 | 2% NPC | 40 | 0.109 | 7 |
| F07141 | 20 | 7/.0121 | 2% NPC | 40 | 0.116 | 8 |
| F07142 | 18 | 7/.0152 | TPC | 40 | 0.126 | 11 |
| F07143 | 16 | 7/.0192 | TPC | 40 | 0.138 | 15 |
| F07144 | 14 | 7/.0242 | TPC | 40 | 0.151 | 20 |
| F07145 | 12 | 19/.0185 | TPC | 40 | 0.168 | 29 |
| F07146 | 10 | 19/.0234 | TPC | 55 | 0.223 | 48 |
| F07147 | 8 | 54/.0175 | TPC | 55 | 0.250 | 69 |
| F07148 | 6 | 84/.0180 | TPC | 70 | 0.318 | 112 |
| F07149 | 4 | 133/.0180 | TPC | 70 | 0.401 | 171 |
| F07150 | 2 | 259/.0160 | TPC | 70 | 0.469 | 264 |
| F07151 | 1 | 259/.0180 | TPC | 90 | 0.552 | 336 |
| F07152 | 1/0 | 259/.0200 | TPC | 90 | 0.590 | 418 |
| F07153 | 2/0 | 259/.0226 | TPC | 90 | 0.645 | 498 |
| F07154 | 3/0 | 259/.0255 | TPC | 90 | 0.695 | 629 |
| F07155 | 4/0 | 259/.0290 | TPC | 105 | 0.796 | 781 |

Compliance: UL Listed File No. E76475. CSA Certified LL37586. All dimensions listed are nominal and subject to normal manufacturing tolerances. Specific marking and/or striping available. Other constructions are available upon request.

DURO 200[®] Series



DURO 200 XR45, 200C/600V, UL 3512/3604, CSA AWM I A/B FT2

| Part Number | Size (AWG) | Stranding | Plating | Insulation Thickness (mil) | Outer Diameter (in.) | Weight (lb/1,000 ft) |
|-------------|------------|-----------|---------|----------------------------|----------------------|----------------------|
| F07060 | 22 | 7/.0096 | 2% NPC | 45 | 0.119 | 7 |
| F07061 | 20 | 7/.0121 | 2% NPC | 45 | 0.126 | 9 |
| F07062 | 18 | 7/.0152 | TPC | 45 | 0.136 | 12 |
| F07063 | 16 | 7/.0192 | TPC | 45 | 0.148 | 16 |
| F07064 | 14 | 7/.0242 | TPC | 45 | 0.161 | 22 |
| F07065 | 12 | 19/.0185 | TPC | 45 | 0.178 | 30 |
| F07066 | 10 | 19/.0234 | TPC | 60 | 0.223 | 49 |
| F07067 | 8 | 54/.0175 | TPC | 60 | 0.260 | 71 |
| F07068 | 6 | 84/.0180 | TPC | 75 | 0.328 | 115 |
| F07069 | 4 | 133/.0180 | TPC | 75 | 0.411 | 174 |
| F07070 | 2 | 259/.0160 | TPC | 75 | 0.479 | 267 |
| F07071 | 1 | 259/.0180 | TPC | 95 | 0.562 | 340 |
| F07072 | 1/0 | 259/.0200 | TPC | 95 | 0.600 | 423 |
| F07073 | 2/0 | 259/.0226 | TPC | 95 | 0.655 | 503 |
| F07074 | 3/0 | 259/.0255 | TPC | 95 | 0.705 | 635 |
| F07075 | 4/0 | 259/.0290 | TPC | 110 | 0.806 | 788 |

DURO 200 XR45, 200C/600V-1000V, UL 3604/3644, CSA AWM I A/B FT2

| Part Number | Size (AWG) | Stranding | Plating | Insulation Thickness (mil) | Outer Diameter (in.) | Weight (lb/1,000 ft) |
|-------------|------------|-----------|---------|----------------------------|----------------------|----------------------|
| F07160 | 22 | 7/.0096 | 2% NPC | 45 | 0.119 | 7 |
| F07161 | 20 | 7/.0121 | 2% NPC | 45 | 0.126 | 9 |
| F07162 | 18 | 7/.0152 | TPC | 45 | 0.136 | 12 |
| F07163 | 16 | 7/.0192 | TPC | 45 | 0.148 | 16 |
| F07164 | 14 | 7/.0242 | TPC | 45 | 0.161 | 22 |
| F07165 | 12 | 19/.0185 | TPC | 45 | 0.178 | 30 |
| F07166 | 10 | 19/.0234 | TPC | 60 | 0.223 | 49 |
| F07167 | 8 | 54/.0175 | TPC | 60 | 0.260 | 71 |
| F07168 | 6 | 84/.0180 | TPC | 75 | 0.328 | 115 |
| F07169 | 4 | 133/.0180 | TPC | 75 | 0.411 | 174 |
| F07170 | 2 | 259/.0160 | TPC | 75 | 0.479 | 267 |
| F07171 | 1 | 259/.0180 | TPC | 95 | 0.562 | 340 |
| F07172 | 1/0 | 259/.0200 | TPC | 95 | 0.600 | 423 |
| F07173 | 2/0 | 259/.0226 | TPC | 95 | 0.655 | 503 |
| F07174 | 3/0 | 259/.0255 | TPC | 95 | 0.705 | 635 |
| F07175 | 4/0 | 259/.0290 | TPC | 110 | 0.806 | 788 |

Compliance: UL Listed File No. E76475. CSA Certified LL37586. All dimensions listed are nominal and subject to normal manufacturing tolerances. Specific marking and/or striping available. Other constructions are available upon request.

DURO 200[®] Series



DURO 200 XG, 200C/600V, UL 3512/3604, CSA AWM I A/B FT2

| Part Number | Size (AWG) | Stranding | Plating | Insulation Thickness (mil) | Outer Diameter (in.) | Weight (lb/1,000 ft) |
|-------------|------------|-----------|---------|----------------------------|----------------------|----------------------|
| F07000 | 22 | 7/.0096 | 2% NPC | 36 | 0.101 | 6 |
| F07001 | 20 | 7/.0121 | 2% NPC | 37 | 0.110 | 8 |
| F07002 | 18 | 7/.0152 | TPC | 38 | 0.122 | 11 |
| F07003 | 16 | 7/.0192 | TPC | 38 | 0.134 | 15 |
| F07004 | 14 | 7/.0242 | TPC | 38 | 0.147 | 21 |
| F07005 | 12 | 19/.0185 | TPC | 38 | 0.164 | 29 |
| F07006 | 10 | 19/.0234 | TPC | 50 | 0.213 | 48 |
| F07007 | 8 | 54/.0175 | TPC | 50 | 0.240 | 69 |
| F07008 | 6 | 84/.0180 | TPC | 65 | 0.308 | 113 |
| F07009 | 4 | 133/.0180 | TPC | 65 | 0.391 | 172 |
| F07010 | 2 | 259/.0160 | TPC | 65 | 0.459 | 266 |
| F07011 | 1 | 259/.0180 | TPC | 85 | 0.542 | 339 |
| F07012 | 1/0 | 259/.0200 | TPC | 85 | 0.580 | 424 |
| F07013 | 2/0 | 259/.0226 | TPC | 85 | 0.635 | 504 |
| F07014 | 3/0 | 259/.0255 | TPC | 85 | 0.685 | 637 |
| F07015 | 4/0 | 259/.0290 | TPC | 100 | 0.786 | 791 |

DURO 200 XG, 200C/600V-1000V, UL 3604/3644, CSA AWM I A/B FT2

| Part Number | Size (AWG) | Stranding | Plating | Insulation Thickness (mil) | Outer Diameter (in.) | Weight (lb/1,000 ft) |
|-------------|------------|-----------|---------|----------------------------|----------------------|----------------------|
| F07180 | 22 | 7/.0096 | 2% NPC | 36 | 0.101 | 6 |
| F07181 | 20 | 7/.0121 | 2% NPC | 37 | 0.110 | 8 |
| F07182 | 18 | 7/.0152 | TPC | 38 | 0.122 | 11 |
| F07183 | 16 | 7/.0192 | TPC | 38 | 0.134 | 15 |
| F07184 | 14 | 7/.0242 | TPC | 38 | 0.147 | 21 |
| F07185 | 12 | 19/.0185 | TPC | 38 | 0.164 | 29 |
| F07186 | 10 | 19/.0234 | TPC | 50 | 0.213 | 48 |
| F07187 | 8 | 54/.0175 | TPC | 50 | 0.240 | 69 |
| F07188 | 6 | 84/.0180 | TPC | 65 | 0.308 | 113 |
| F07189 | 4 | 133/.0180 | TPC | 65 | 0.391 | 172 |
| F07190 | 2 | 259/.0160 | TPC | 65 | 0.459 | 266 |
| F07191 | 1 | 259/.0180 | TPC | 85 | 0.542 | 339 |
| F07192 | 1/0 | 259/.0200 | TPC | 85 | 0.580 | 424 |
| F07193 | 2/0 | 259/.0226 | TPC | 85 | 0.635 | 504 |
| F07194 | 3/0 | 259/.0255 | TPC | 85 | 0.685 | 637 |
| F07195 | 4/0 | 259/.0290 | TPC | 100 | 0.786 | 791 |

Compliance: UL Listed File No. E76475. CSA Certified LL37586. All dimensions listed are nominal and subject to normal manufacturing tolerances. Specific marking and/or striping available. Other constructions are available upon request.

DURO 200[®] Series



DURO 200 XG VW-1, 200C/600V, UL 3512/3604, CSA AWM I A/B FT1

| Part Number | Size (AWG) | Stranding | Plating | Insulation Thickness (mil) | Outer Diameter (in.) | Weight (lb/1,000 ft) |
|-------------|------------|-----------|---------|----------------------------|----------------------|----------------------|
| F07100 | 22 | 7/.0096 | 2% NPC | 36 | 0.101 | 6 |
| F07101 | 20 | 7/.0121 | 2% NPC | 37 | 0.110 | 8 |
| F07102 | 18 | 7/.0152 | TPC | 38 | 0.122 | 11 |
| F07103 | 16 | 7/.0192 | TPC | 38 | 0.134 | 15 |
| F07104 | 14 | 7/.0242 | TPC | 38 | 0.147 | 21 |
| F07105 | 12 | 19/.0185 | TPC | 38 | 0.164 | 29 |
| F07106 | 10 | 19/.0234 | TPC | 50 | 0.213 | 48 |
| F07107 | 8 | 54/.0175 | TPC | 50 | 0.240 | 69 |
| F07108 | 6 | 84/.0180 | TPC | 65 | 0.308 | 113 |
| F07109 | 4 | 133/.0180 | TPC | 65 | 0.391 | 172 |
| F07110 | 2 | 259/.0160 | TPC | 65 | 0.459 | 266 |
| F07111 | 1 | 259/.0180 | TPC | 85 | 0.542 | 339 |
| F07112 | 1/0 | 259/.0200 | TPC | 85 | 0.580 | 424 |
| F07113 | 2/0 | 259/.0226 | TPC | 85 | 0.635 | 504 |
| F07114 | 3/0 | 259/.0255 | TPC | 85 | 0.685 | 637 |
| F07115 | 4/0 | 259/.0290 | TPC | 100 | 0.786 | 791 |

DURO 200 XG VW-1, 200C/600V-1000V, UL 3604/3644, CSA AWM I A/B FT1

| Part Number | Size (AWG) | Stranding | Plating | Insulation Thickness (mil) | Outer Diameter (in.) | Weight (lb/1,000 ft) |
|-------------|------------|-----------|---------|----------------------------|----------------------|----------------------|
| F07200 | 22 | 7/.0096 | 2% NPC | 36 | 0.101 | 6 |
| F07201 | 20 | 7/.0121 | 2% NPC | 37 | 0.110 | 8 |
| F07202 | 18 | 7/.0152 | TPC | 38 | 0.122 | 11 |
| F07203 | 16 | 7/.0192 | TPC | 38 | 0.134 | 15 |
| F07204 | 14 | 7/.0242 | TPC | 38 | 0.147 | 21 |
| F07205 | 12 | 19/.0185 | TPC | 38 | 0.164 | 29 |
| F07206 | 10 | 19/.0234 | TPC | 50 | 0.213 | 48 |
| F07207 | 8 | 54/.0175 | TPC | 50 | 0.240 | 69 |
| F07208 | 6 | 84/.0180 | TPC | 65 | 0.308 | 113 |
| F07209 | 4 | 133/.0180 | TPC | 65 | 0.391 | 172 |
| F07210 | 2 | 259/.0160 | TPC | 65 | 0.459 | 266 |
| F07211 | 1 | 259/.0180 | TPC | 85 | 0.542 | 339 |
| F07212 | 1/0 | 259/.0200 | TPC | 85 | 0.580 | 424 |
| F07213 | 2/0 | 259/.0226 | TPC | 85 | 0.635 | 504 |
| F07214 | 3/0 | 259/.0255 | TPC | 85 | 0.685 | 637 |
| F07215 | 4/0 | 259/.0290 | TPC | 100 | 0.786 | 791 |

Compliance: UL Listed File No. E76475. CSA Certified LL37586. All dimensions listed are nominal and subject to normal manufacturing tolerances. Specific marking and/or striping available. Other constructions are available upon request.

DURO 200[®] Series



DURO 200 SR/XR Construction



DURO 200 XG Construction

