RITTAL

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 08.05.2017 Version number 75 Revision: 19.01.2016

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- · 1.1 Product identifier
- · Trade name: Decklack-Spray
- · 1.2 Relevant identified uses of the substance or mixture and uses advised against

No further relevant information available.

- · Application of the substance / the mixture Color spray
- · 1.3 Details of the supplier of the safety data sheet
- · Manufacturer/Supplier:

RITTAL GmbH & Co.KG Auf dem Stützelberg D-35745 Herborn Phone: +49 2772 505 0 e-mail: info@rittal.de

· 1.4 Emergency telephone number:

Informationszentrale gegen Vergiftungen Bonn

Tel.: 0228/19240 (emergency) 0228/287-3-3480 (office) Fax: 0228/287-3-3278

SECTION 2: Hazards identification

- · 2.1 Classification of the substance or mixture
- · Classification according to Regulation (EC) No 1272/2008



GHS02 flame

Aerosol 1 H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.



Eye Irrit. 2 H319 Causes

Causes serious eye irritation.

STOT SE 3 H336 May cause drowsiness or dizziness.

· 2.2 Label elements

· Labelling according to Regulation (EC) No 1272/2008

The product is classified and labelled according to the CLP regulation.

- · Hazard pictograms GHS02, GHS07
- · Signal word Danger
- · Hazard-determining components of labelling:

acetone

Butyl acetate

· Hazard statements

H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.

H319 Causes serious eye irritation.H336 May cause drowsiness or dizziness.

· Precautionary statements

P101 If medical advice is needed, have product container or label at hand.

P102 Keep out of reach of children.

(Contd. on page 2)

RITTAL

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 08.05.2017 Version number 75 Revision: 19.01.2016

Trade name: Decklack-Spray

(Contd. of page 1)

P103 Read label before use.

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition

sources. No smoking.

P251 Do not pierce or burn, even after use.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact

lenses, if present and easy to do. Continue rinsing.

P405 Store locked up.

P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.

P501 Dispose of contents/container in accordance with local/regional/national/

international regulations.

· Additional information:

EUH066 Repeated exposure may cause skin dryness or cracking. Buildup of explosive mixtures possible without sufficient ventilation.

- · 2.3 Other hazards
- · Results of PBT and vPvB assessment
- PBT: Not applicable.vPvB: Not applicable.

SECTION 3: Composition/information on ingredients

- · 3.2 Chemical characterisation: Mixtures
- · Description: Mixture of substances listed below with nonhazardous additions.

· Dangerous components:		
CAS: 67-64-1 EINECS: 200-662-2 Reg.nr.: 01-2119471330-49	acetone Flam. Liq. 2, H225; Eye Irrit. 2, H319; STOT SE 3, H336	25-50%
CAS: 123-86-4 EINECS: 204-658-1 Reg.nr.: 01-2119485493-29	Butyl acetate ♠ Flam. Liq. 3, H226; ♠ STOT SE 3, H336	10- <u><</u> 20%
CAS: 74-98-6 EINECS: 200-827-9 Reg.nr.: 01-21194869440-21	propane Flam. Gas 1, H220; Press. Gas C, H280	10-25%
CAS: 106-97-8 EINECS: 203-448-7 Reg.nr.: 01-2119474691-31	butane ♦ Flam. Gas 1, H220; Press. Gas C, H280	10-25%
CAS: 108-65-6 EINECS: 203-603-9 Reg.nr.: 01-2119475791-29	2-methoxy-1-methylethyl acetate	0.1-<2.5%

· Additional information: For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

- · 4.1 Description of first aid measures
- · After inhalation: Supply fresh air; consult doctor in case of complaints.
- · After skin contact: Immediately wash with water and soap and rinse thoroughly.
- · After eve contact:
- Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- · After swallowing: If symptoms persist consult doctor.

(Contd. on page 3)

according to 1907/2006/EC, Article 31

Printing date 08.05.2017 Version number 75 Revision: 19.01.2016

Trade name: Decklack-Spray

(Contd. of page 2)

- 4.3 Indication of any immediate medical attention and special treatment needed No further relevant information available.
- · Information for doctor:

SECTION 5: Firefighting measures

- · 5.1 Extinguishing media
- · Suitable extinguishing agents: CO2, sand, extinguishing powder. Do not use water.
- · For safety reasons unsuitable extinguishing agents: Water with full jet
- · 5.2 Special hazards arising from the substance or mixture

No further relevant information available.

- · 5.3 Advice for firefighters
- · Protective equipment:

Wear self-contained respiratory protective device.

Do not inhale explosion gases or combustion gases.

SECTION 6: Accidental release measures

· 6.1 Personal precautions, protective equipment and emergency procedures

Wear protective equipment. Keep unprotected persons away.

· 6.2 Environmental precautions:

Do not allow product to reach sewage system or any water course.

Inform respective authorities in case of seepage into water course or sewage system.

Do not allow to enter sewers/ surface or ground water.

· 6.3 Methods and material for containment and cleaning up:

Ensure adequate ventilation.

Do not flush with water or aqueous cleansing agents

· 6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

· 7.1 Precautions for safe handling

Keep away from heat and direct sunlight.

Ensure good ventilation/exhaustion at the workplace.

Open and handle receptacle with care.

· Information about fire - and explosion protection:

Do not spray onto a naked flame or any incandescent material.

Keep ignition sources away - Do not smoke.

Protect against electrostatic charges.

Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50 °C, i.e. electric lights. Do not pierce or burn, even after use.

- · 7.2 Conditions for safe storage, including any incompatibilities
- Storage:
- · Requirements to be met by storerooms and receptacles:

Store in a cool location.

Observe official regulations on storing packagings with pressurised containers.

(Contd. on page 4)

RITTAL

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 08.05.2017 Version number 75 Revision: 19.01.2016

Trade name: Decklack-Spray

(Contd. of page 3)

- Information about storage in one common storage facility: Store away from foodstuffs.
- · Further information about storage conditions:

Do not seal receptacle gas tight.

Keep container tightly sealed.

Store in cool, dry conditions in well sealed receptacles.

Protect from heat and direct sunlight.

- · Storage class: 2 B
- · 7.3 Specific end use(s) No further relevant information available.

SECTION 8: Exposure controls/personal protection

- · Additional information about design of technical facilities: No further data; see item 7.
- 8.1 Control parameters

	dients with limit values that require monitoring at the workplace: -1 acetone
WEL	Short-term value: 3620 mg/m³, 1500 ppm
	Long-term value: 1210 mg/m³, 500 ppm
123-8	6-4 Butyl acetate
WEL	Short-term value: 966 mg/m³, 200 ppm
	Long-term value: 724 mg/m³, 150 ppm
106-9	7-8 butane
WEL	Short-term value: 1810 mg/m³, 750 ppm
	Long-term value: 1450 mg/m³, 600 ppm
	Carc (if more than 0.1% of buta-1.3-diene)
108-6	5-6 2-methoxy-1-methylethyl acetate
WEL	Short-term value: 548 mg/m³, 100 ppm
	Long-term value: 274 mg/m³, 50 ppm
	Sk

- · Additional information: The lists valid during the making were used as basis.
- · 8.2 Exposure controls
- Personal protective equipment:
- · General protective and hygienic measures:

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing

Wash hands before breaks and at the end of work.

Do not inhale gases / fumes / aerosols.

Avoid contact with the eyes.

Avoid contact with the eyes and skin.

Respiratory protection:



In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

Filter AX/P2 (EN 141, EN 143)

(Contd. on page 5)

according to 1907/2006/EC, Article 31

Printing date 08.05.2017 Version number 75 Revision: 19.01.2016

Trade name: Decklack-Spray

(Contd. of page 4)

· Protection of hands:



Protective gloves (EN 374)

- · Material of gloves
- Butyl rubber, BR

Recommended thickness of the material: ≥ 0.7 mm

- · Breakthrough time of glove material Value for the permeation: Level ≤ 4
- · Eye protection:



Tightly sealed goggles

SECTION 9: Physical and chemical properties

- · 9.1 Information on basic physical and chemical properties
- · General Information
- · Appearance:

Form: Aerosol

Colour: According to product specification

· Odour: Characteristic · Odour threshold: Not determined.

Not determined. · pH-value:

· Change in condition

Melting point/freezing point: Undetermined.

Initial boiling point and boiling range: -44 °C

<0 °C (DIN 53213) · Flash point:

· Flammability (solid, gas): Not applicable.

· Ignition temperature: 365 °C (DIN 51794)

Not determined. · Decomposition temperature:

Product is not selfigniting. · Auto-ignition temperature:

· Explosive properties: Product is not explosive. However, formation of

explosive air/vapour mixtures are possible.

· Explosion limits:

Lower: 1.2 Vol % **Upper:** 13.0 Vol %

· Vapour pressure at 20 °C: 8300 hPa

0.805 g/cm3 (DIN 53217) · Density at 20 °C:

· Relative density Not determined. · Vapour density Not determined. · Evaporation rate Not applicable.

(Contd. on page 6)

Page 6/9

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 08.05.2017 Version number 75 Revision: 19.01.2016

Trade name: Decklack-Spray

	(Contd. of page 5)
· Solubility in / Miscibility with water:	Not miscible or difficult to mix.
· Partition coefficient: n-octanol/water:	Not determined.
· Viscosity: Dynamic: Kinematic:	Not determined. Not determined.
· Solvent content: VOC (EC)	81.06 %
Solids content (weight-%): · 9.2 Other information	18.9 % No further relevant information available.

SECTION 10: Stability and reactivity

- · 10.1 Reactivity No further relevant information available.
- · 10.2 Chemical stability
- · Thermal decomposition / conditions to be avoided:

No decomposition if used according to specifications.

- · 10.3 Possibility of hazardous reactions No dangerous reactions known.
- · 10.4 Conditions to avoid No further relevant information available.
- 10.5 Incompatible materials: No further relevant information available.
- · 10.6 Hazardous decomposition products: Carbon monoxide

SECTION 11: Toxicological information

- · 11.1 Information on toxicological effects
- · Acute toxicity Based on available data, the classification criteria are not met.
- · Primary irritant effect:
- · Skin corrosion/irritation Based on available data, the classification criteria are not met.
- · Serious eye damage/irritation
- Causes serious eye irritation.
- · Respiratory or skin sensitisation Based on available data, the classification criteria are not met.
- · CMR effects (carcinogenity, mutagenicity and toxicity for reproduction)
- · Germ cell mutagenicity Based on available data, the classification criteria are not met.
- · Carcinogenicity Based on available data, the classification criteria are not met.
- · Reproductive toxicity Based on available data, the classification criteria are not met.
- STOT-single exposure
- May cause drowsiness or dizziness.
- · STOT-repeated exposure Based on available data, the classification criteria are not met.
- · Aspiration hazard Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- · 12.1 Toxicity
- · Aquatic toxicity: No further relevant information available.
- · 12.2 Persistence and degradability No further relevant information available.
- 12.3 Bioaccumulative potential No further relevant information available.

(Contd. on page 7)

according to 1907/2006/EC, Article 31

Printing date 08.05.2017 Version number 75 Revision: 19.01.2016

Trade name: Decklack-Spray

(Contd. of page 6)

- · 12.4 Mobility in soil No further relevant information available.
- · Additional ecological information:
- · General notes:

Water hazard class 1 (German Regulation): slightly hazardous for water

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

- · 12.5 Results of PBT and vPvB assessment
- · **PBT:** Not applicable.
- · vPvB: Not applicable.
- 12.6 Other adverse effects No further relevant information available.

SECTION 13: Disposal considerations

- · 13.1 Waste treatment methods
- · Recommendation

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

· European waste catalogue		
08 01 11*	waste paint and varnish containing organic solvents or other hazardous substances	
15 01 04	metallic packaging	
14 06 03*	other solvents and solvent mixtures	

- · Uncleaned packaging:
- · Recommendation: Disposal must be made according to official regulations.

SECTION 14: Tran	sport information
------------------	-------------------

	14.1	UN-Number	-
--	------	------------------	---

· ADR, IMDG, IATA UN1950

· 14.2 UN proper shipping name

· **ADR** UN1950 AEROSOLS

· **IMDG** AEROSOLS

· IATA AEROSOLS, flammable

- · 14.3 Transport hazard class(es)
- · ADR



· Class 2 5F Gases.

· Label 2.1

(Contd. on page 8)

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 08.05.2017 Version number 75 Revision: 19.01.2016

Trade name: Decklack-Spray

	(Contd. of page 7
· IMDG, IATA	
· Class · Label	2.1 2.1
· 14.4 Packing group · ADR, IMDG, IATA	Void
· 14.5 Environmental hazards: · Marine pollutant:	No
 14.6 Special precautions for user Danger code (Kemler): EMS Number: Stowage Code Segregation Code	Warning: Gases. F-D,S-U SW1 Protected from sources of heat. SW22 For AEROSOLS with a maximum capacity of 1 litre: Category A. For AEROSOLS with a capacity above 1 litre: Category B. For WASTE AEROSOLS: Category C, Clear of living quarters. SG69 For AEROSOLS with a maximum capacity of 1 litre: Segregation as for class 9. Stow "separated from" class 1 except for division 1.4. For AEROSOLS with a capacity above 1 litre. Segregation as for the appropriate subdivision of class 2. For WASTE AEROSOLS: Segregation as for the appropriate subdivision of class 2.
· 14.7 Transport in bulk according to An of Marpol and the IBC Code	nex II Not applicable.
· Transport/Additional information:	
· ADR · Transport category · Tunnel restriction code	2 D
· IMDG · Limited quantities (LQ)	1L
· UN "Model Regulation":	UN 1950 AEROSOLS, 2.1

SECTION 15: Regulatory information

- · 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
- · Directive 2012/18/EU
- · Named dangerous substances ANNEX I None of the ingredients is listed.
- · Seveso category P3a FLAMMABLE AEROSOLS
- · Qualifying quantity (tonnes) for the application of lower-tier requirements 150 t
- Qualifying quantity (tonnes) for the application of upper-tier requirements 500 t

(Contd. on page 9)

according to 1907/2006/EC, Article 31

Printing date 08.05.2017 Version number 75 Revision: 19.01.2016

Trade name: Decklack-Spray

(Contd. of page 8)

· REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 3

· National regulations:

Class	Share in %
NK	50-100

· 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

Relevant phrases

H220 Extremely flammable gas.

H225 Highly flammable liquid and vapour.

H226 Flammable liquid and vapour.

H280 Contains gas under pressure; may explode if heated.

H319 Causes serious eye irritation.

H336 May cause drowsiness or dizziness.

Abbreviations and acronyms:

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)

ICAO: International Civil Aviation Organisation

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU)

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

Flam. Gas 1: Flammable gases - Category 1

Aerosol 1: Aerosols – Category 1 Press. Gas C: Gases under pressure – Compressed gas

Flam. Liq. 2: Flammable liquids - Category 2

Flam. Liq. 3: Flammable liquids - Category 3

Eye Irrit. 2: Serious eye damage/eye irritation – Category 2 STOT SE 3: Specific target organ toxicity (single exposure) - Category 3

* Data compared to the previous version altered.