


631 Pipe Saddle for 1 1/2" Insulation – 6311200PL



- Designed for high temperature service or where heat losses are to be kept at a minimum and to protect insulation against damage at the point of support
- Conforms with Federal Specification WW-H-171 (Type 40A or 40B), Manufacturers Standardization Society ANSI®/MSS-SP-58 (Type 39)



Part Number	6311200PL
Material	Steel
Finish	Plain
Pipe Size	12"
Length (L)	12"
Insulation Thickness	1 1/2"
Standard Packaging Quantity	1 pc
UPC	78285637098

Part Number	Pipe Size	Cover Thickness	Size of Pipe Roll for Model #			Center Line of Pipe to Outside of Saddle	Center Line of Pipe to Center Line of Roll for Model #			Static Load F
			605, 615	610	617, 619		605, 615	610	617, 619	
6310150PL	3/4"	1 7/16"	3"	3 1/2"	2" - 3 1/2"	2 1/8"	2 11/16"	2 11/16"	3 13/16"	1,200 lb
	1"	1 9/16"	3"	4"	2" - 3 1/2"	2 7/16"	3"	3"	3 1/8"	1,200 lb
	1 1/4"	1 5/8"	3 1/2"	5"	2" - 3 1/2"	2 9/16"	3 1/16"	3 1/16"	3 3/16"	1,200 lb
	1 1/2"	1 1/2"	3 1/2"	5"	2" - 3 1/2"	2 11/16"	3 5/16"	3 5/16"	3 5/16"	1,200 lb
6310350PL	2"	1 9/16"	4"	5"	2" - 3 1/2"	3"	3 5/8"	3 5/8"	3 5/8"	1,200 lb
	2 1/2"	1 7/16"	5"	6"	2" - 3 1/2"	3 1/4"	3 15/16"	3 15/16"	3 7/8"	1,200 lb
	3"	1 9/16"	5"	6"	2" - 3 1/2"	3 5/8"	4 5/16"	4 5/16"	4 1/4"	1,800 lb
	3 1/2"	1 13/16"	6"	8"	4" - 6"	3 7/8"	4 3/4"	4 3/4"	4 11/16"	1,800 lb
6310500PL	4"	1 9/16"	6"	8"	4" - 6"	3 7/8"	4 11/16"	4 11/16"	4 9/16"	1,800 lb
	5"	1 1/2"	8"	8"	4" - 6"	4 1/2"	5 5/16"	5 5/16"	5 3/16"	1,800 lb
6310800PL	6"	1 1/2"	8"	10"	8" - 10"	5 3/16"	6"	5 13/16"	6 1/8"	1,800 lb
	8"	1 1/2"	10"	12"	8" - 10"	6 5/16"	7 3/8"	7 3/8"	7 3/8"	1,800 lb
6311000PL	10"	1 9/16"	12"	14"	8" - 10"	7 1/4"	8 5/16"	8 1/2"	8 5/16"	1,800 lb
6311200PL	12"	1 1/2"	14"	16"	12" - 14"	8 1/16"	8 1/16"	9 1/2"	9 1/4"	5,000 lb

Part Number	Pipe Size	Cover Thickness	Size of Pipe Roll for Model #			Center Line of Pipe to Outside of Saddle	Center Line of Pipe to Center Line of Roll for Model #			Static Load F
			605, 615	610	617, 619		605, 615	610	617, 619	
6311400PL	14"	1 1/2"	16"	18"	12" - 14"	8 7/8"	8 7/8"	10 1/2"	10 3/16"	5,000 lb
6311600PL	16"	1 1/2"	18"	20"	16" - 20"	9 7/8"	11 5/16"	11 5/16"	11 3/16"	5,000 lb
6311800PL	18"	1 1/2"	20"	-	16" - 20"	10 7/8"	12 3/8"	-	12 1/4"	5,000 lb
6312000PL	20"	1 1/2"	24"	-	24" - 26"	11 3/4"	13 11/16"	-	13 3/16"	7,200 lb
6312400PL	24"	1 1/2"	30"	-	22" - 30"	13 5/8"	16 7/16"	-	15 3/8"	7,200 lb

Maximum recommended loads are applicable only when the saddle is used on a flat bearing surface and tack welded to the pipe. When a saddle is used with a pipe roll, the maximum load given for the pipe roll applies to the saddle.

Install in accordance with applicable code.

ANSI is a registered trademark of American National Standards Institute.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2020 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

