

Product data sheet

Characteristics

BR1350MS

Back UPS PRO BR 1350VA, SineWave, 10
Outlets, 2 USB Charging Ports, AVR, LCD
interface



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	Coaxial cable User Manual USB cable
--------------------	---

Physical

Cable length	6 ft (1.83 m)
Maximum Depth	14.49 in (36.8 cm)
Maximum Height	10.24 in (26 cm)
Net Weight	25.79 lb(US) (11.7 kg)
Maximum Width	3.94 in (10 cm)

Input

Input Frequency	60 Hz +/- 3 Hz
Plug standard	NEMA 5-15P
Efficiency at full load	88...147 V
Maximum Input Current per phase	12 A
Switching current capacity	15 A
Nominal Input Voltage	120 V

Output

Kw Rating	810 W
Max Configurable Power (Watts)	810 W

Output Frequency (sync to mains)	60 Hz +/- 3 Hz sync to mains
Topology	Line Interactive
Waveform Type	Sine wave
Nb of power socket outlets	6 NEMA 5-15R 4 NEMA 5-15R surge
Output voltage	120 V

Conformance

Product certifications	ENERGY STAR V2.0 (USA) NOM TUV C-US certified
Standards	FCC Part 15 class B
Equipment protection policy	Lifetime : \$500000

Environmental

Ambient air temperature for operation	32...104 °F (0...40 °C)
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	5...104 °F (-15...40 °C)
Storage altitude	0...10000 ft (0.00...3048.00 m)
Acoustic level	45 dBA

Batteries & Runtime

Battery type	Lead-Acid battery
Included Battery Modules	1
Battery Slots Empty	0
Typical recharge time	16 h
RBC Quantity	2
Liquid Electrolyte Value	0

Communications & Management

Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm

Surge Protection and Filtering

Surge energy rating	1080 J
Filtering	Full time multi-pole noise filtering :5% of IEEE surge let-through : zero clamping response time: in
Data Line Protection	RJ45 10/100/1000 Base-T Ethernet protection Co-axial Video / Cable protection

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00731304335399
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No

Packing Units

Package 1 Height	14.12 in (35.87 cm)
Package 1 width	8.78 in (22.3 cm)
Package 1 Length	18.98 in (48.2 cm)
SCC14	10731304335396

Number of Units in Package 2	1
Package 2 Weight	29.32 lb(US) (13.30 kg)
Package 2 Height	19 in (482.60 mm)
Package 2 width	9 in (228.60 mm)
Package 2 Length	14 in (355.60 mm)
Number of Units in Package 3	16

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Optimized Energy Efficiency	Energy efficient product

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------