


Telescoping Strut Replacement, Retrofit – TSR1220R



- Slotted ends allow the bracket to be installed with four nVent CADDY SN Nuts on threaded rod above an existing trapeze, saving contractor time and limiting building downtime
- Telescopes to the desired length and is locked in place by snapping closed a spring retainer clip
- Standard strut profile runs the entire length of the part, allowing most standard fittings to be placed anywhere between the rods
- Integrated ruler displays space between hanger rods in inches and centimeters
- Supports up to seven 2" (50 DN) conduits, six 2" (50 DN) water filled pipes at 10' (3 m) spacing, or up to 18" (450 mm) cable tray
- Conduit can be supported on the top and bottom, eliminating the need for double sided strut
- Conduit and pipe can be placed directly on the strut profile, saving vertical space in buildings with limited room for installation
- Winner of the EC&M 2017 Product of the Year Platinum Award
- Meets requirements of the Buy American Act



Part Number	TSR1220R
Material	Steel
Finish	Pregalvanized
Rod Size (RS)	3/8"
Thickness (T)	0.04"
A	12 1/2" – 20"
B	14" – 21 1/2"
C	1 5/8"
D	7/8"
E	1 3/8"
Static Load 1 (F1)	300 lb
Static Load 2 (F2)	200 lb
Standard Packaging Quantity	25 pc
UPC	78285691646
EAN-13	0782856916468

Static Load 1 represents a distributed load for 12" – 20" (300 - 500 mm) installations and a point load for 12" – 16" (300 - 400 mm) installations. Static Load 2 represents a point load for 16" – 20" (400 - 500 mm) installations.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2020 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

