

Management Interface

The management interface for this PDU model is transitioning to a new technology platform. The new interface can be distinguished by a USB-A port (for EnviroSense2 modules) in place of the round ENVIROSENSE port. For managing the units containing the round port, Tripp Lite recommends using the [PowerAlert Console Launcher](#) rather than a web browser. This application enables local access of the PDU using a self-contained, compatible Java Runtime Environment version. The Console Launcher can be downloaded for free; click the above link or go to the Management Solutions / Utilities page. Units with the new interface work with most current web browsers.

7.4kW Single-Phase Switched Automatic Transfer Switch PDU, 2 230V IEC309 32A Blue Inputs, 16-C13 2-C19 Outlets, 2U, TAA

MODEL NUMBER: PDUMH32HVATNET



High-capacity 7.4kW 230V PDU with ATS provides remote power monitoring and enables redundant power for non-redundant hardware. LED display and LX Platform network interface enables remote outlet control and monitoring of site power status and PDU load levels.

Description

The PDUMH32HVATNET 7.4kW Single-Phase 230V Switched Automatic Transfer Switch / ATS PDU provides remote power monitoring and enables redundant power for network devices with non-redundant power supply configurations. Ideal for data centers and server rooms, it mounts in 2U of space in EIA-standard racks and features 18 switched outlets (16 C13 and two C19) in two load banks, each bank protected by a 20A circuit breaker.

Dual 3-meter input cords with IEC309 32A Blue (2P+E) plugs connect to separate primary and secondary single-phase 230V power sources. The PDU constantly evaluates the power quality of both input sources. Dynamic solid-state (TRIAC) automatic transfer switching allows the PDU to switch to the secondary source within 1–5 milliseconds should the primary source fail or become unstable to ensure your connected equipment operates without interruption.

Built-in LX Platform network management interface. The Java-free LX Platform HTML5-based network interface enables full remote access for PDU status monitoring and email notifications via secure web browser, SNMP, telnet or SSH. It supports 10/100 Mbps auto-sensing for optimum communication with an Ethernet network. Optional EnviroSense2 modules (sold separate) provide a variety of environmental monitoring capabilities. Protocols supported include HTTP, HTTPS, SMTP, SNMPv1, SNMPv2, SNMPv3, telnet, SSH, FTP, DHCP and NTP.

Features

Primary and Secondary Inputs for Power Redundancy Provides remote power monitoring and enables redundant power for network devices single-corded and other non-redundant power supply configurations
Dual 3m input cords with IEC309 32A Blue (2P+E) plugs connect to separate primary and secondary single-phase power sources

Automatic Transfer Switching Dynamic solid-state (TRIAC) automatic transfer switching
Switches to

Highlights

- Single-phase IEC309 230V 32A Blue (2P+E) input
- 16 C13 and 2 C19 230V switched outlets in 2 breakered load banks
- Automatic transfer switching within 1–5 ms
- Ethernet network interface for remote access
- Digital LED display for real-time status and current monitoring

Package Includes

- PDUMH32HVATNET 7.4kW Single-Phase 230V ATS / Switched PDU
- Rack-mounting brackets
- Plug-lock cable retention sleeves
- USB configuration cable
- Owner's manual



secondary power source if primary source fails or becomes unstable 1–5 ms transfer time ensures uninterrupted operation of connected equipment Built-in processor monitors both sources and prevents switching if secondary source is unavailable or of lower quality than primary source

Multifunction Digital LED Display Reports source A and source B input power status and other information, including power availability, line voltage, frequency, amps, kilowatts and power factor
Advanced LX Platform Interface LX Platform interface allows full remote access for power monitoring with email notifications via secure web browser, SNMP, telnet or SSH Real-time load/current data with billing-grade accuracy (+/- 1 percent) Automated alerts help prevent accidental overloads, power loss and downtime Optional EnviroSense2 modules (sold separately) provide a variety of environmental monitoring capabilities

Broad Communications Compatibility Protocols supported include HTTP, HTTPS, SMTP, SNMPv1, SNMPv2, SNMPv3, telnet, SSH, FTP, DHCP and NTP

Breaker Protected Output Load Banks Protect each of 2 single-phase output banks Front-panel LED indicates when breaker has tripped

Cord Retention Sleeves Set of Plug-lock output power cable retention sleeves prevent accidental disconnection of connected devices

Mounts Horizontally in 2U of Rack Space Compatible with EIA-standard 19 in. 4-post racks and rack enclosures

TAA-Compliant Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332186874
PDU Type	Switched; Auto-Transfer Switch
INPUT	
PDU Input Voltage	200; 208; 220; 230; 240
Recommended Electrical Service	32A 230V Single Phase
Maximum Input Amps	32
PDU Plug Type	(2) IEC-309 32A BLUE (2P+E)
Input Phase	Single-Phase
Input Cord Details	Set of two inputs connect to separate PRIMARY and SECONDARY power sources; accepts inputs at all phase angles
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
OUTPUT	
Output Capacity Details	7.7kW (240V), 7.4kW (230V), 7.0kW (220V), 6.7kW (208V), 6.4kW (200V); 32A maximum total output; 16A maximum per breaker load bank; 16A maximum per C19 outlet; 10A maximum per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(16) C13; (2) C19
Output Nominal Voltage	200; 208; 220; 230; 240V
Overload Protection	Includes two branch-rated 20A output circuit breakers; Breaker 1 controls the upper row of 9 outlets (8 C13, 1 C19); Breaker 2 controls the lower row of outlets (8 C13, 1 C19)



USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital display reports output amps in 3 separately metered load segments (BANK 1: Outlets #1-9; BANK 2: Outlets #10-18; BANK 3: Total Output), whole-PDU output kW load level and input voltage on primary and secondary input lines
Front Panel LEDs	Front panel LEDs confirm amp / kilowatt / voltage reporting information
Switches	ENTER and MODE switches toggle the digital display to show output amps (Bank 1, Bank 2 and Total), total kW output and input voltage (primary, secondary)
Current Measurement Accuracy (Amps)	+/-1%
Voltage Measurement Accuracy (Volts)	+/-1%
Power Measurement Accuracy (Watts)	+/-1%
PHYSICAL	
Form Factors Supported	2U rackmount
Material of Construction	Metal
Minimum Required Rack Depth (cm)	40.64
Minimum Required Rack Depth (inches)	16
PDU Form Factor	Horizontal (2U)
Shipping Dimensions (hwd / cm)	19.81 x 42.42 x 50.55
Shipping Dimensions (hwd / in.)	7.80 x 16.70 x 19.90
Shipping Weight (kg)	8.75
Shipping Weight (lbs.)	19.30
Unit Dimensions (hwd / cm)	8,8 x 44,4 x 31,7
Unit Dimensions (hwd / in.)	3.5 x 17.5 x 12.5
Unit Weight (kg)	6.21
Unit Weight (lbs.)	13.7
ENVIRONMENTAL	
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5 to 95% (non-condensing)
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
SPECIAL FEATURES	
High Availability PDU Features	Auto Probe Monitoring and Reboot (included)
STANDARDS & COMPLIANCE	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Certifications	Tested to CE IEC 60950-1, EN CLASS A (Emissions), NOM (Mexico), RoHS Complaint, TAA Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>