

SmartPro 230V 1000VA 900W Line-Interactive Sine Wave UPS, 2U, WEBCARDLX, LCD, USB, DB9, 6 Outlets

MODEL NUMBER: **SMX1000RT2UN**



Line-interactive UPS offers complete power protection for professional applications, including retail, casino and hotel management.

Features

1kVA/900W/230V Battery Backup for PC Networks, Security Systems or Digital SignageThe SmartPro® line-interactive SMX1000RT2UN UPS system with AVR provides reliable battery backup and AC power protection against blackouts, brownouts, overvoltages, surges and line noise that can damage valuable electronics or destroy data. The six-outlet 230V battery backup with 0.9 power factor is ideal protection for small networks, wiring closets, security systems, telecom, high-end PC gaming, digital signage equipment and other professional applications, including retail, casino and hotel/motel management.

Reliable, Expandable Battery Backup Keeps You Operational Through Power OutagesThe field-replaceable, hot-swappable internal battery provides 11.9 minutes of support at half load (450W) and 3.6 minutes at full load (900W), allowing you to work through short power failures and giving you enough time to safely save files and shut down your system in case of a prolonged blackout.

WEBCARDLX Network Interface Offers 24/7 Remote Access for Monitoring and ControlThe Java-free HTML5-based WEBCARDLX enables full remote access for site power and UPS status monitoring, configuration, control and email notifications via secure web browser, SNMP, telnet or SSH. It supports 10/100 Mbps auto-sensing for optimum communication with an Ethernet network. Automated alerts help prevent accidental overloads, power loss and downtime. WEBCARDLX allows you to use the Auto Probe feature, which can prevent costly service calls by automatically rebooting non-responsive network devices.

6 Outlets Protect Your Connected ComponentsSix C13 outlets provide battery backup, 350 joules of surge protection and voltage regulation for your crucial components. Two independently switched two-outlet load banks enable both scheduled and real-time remote rebooting and load shedding.

Automatic Voltage Regulation (AVR) Corrects Low- and High-Voltage ConditionsAVR protects your equipment from incremental hardware damage, data loss and performance problems caused by brownouts and overvoltages. The SMX1000RT2UN can correct brownouts as low as 182V and overvoltages as high as 278V back to nominal 230V power continuously, all while keeping the battery fully charged and ready to take over in case of power failure.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform BetterThis UPS system filters out disruptive electromagnetic and radio frequency interference that can inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Designed for High Efficiency to Help You Save Money and Protect the EnvironmentA 97% efficiency rating reduces BTU emissions, energy consumption and, ultimately, your energy costs.

Silenceable Alarm and Easy-to-Read LCD Keep You Informed Around the ClockThe front-panel LCD

Highlights

- Protects equipment against blackouts, brownouts, overvoltages, surges and line noise
- Keeps AC power running during blackouts to allow time for file saves and safe shutdown
- Maintains continuous 230V nominal output during brownouts and overvoltages
- Pre-installed WEBCARDLX network interface supports Auto Probe feature
- Easy-to-read LCD allows real-time monitoring of voltage, battery status and other data

Applications

- Protect your small network server and other network components against power surges, line noise, brownouts, overvoltages and blackouts
- Operate essential equipment during short-term power outages using battery backup power
- Shut down desktop PCs and other equipment without data loss during long-term power outages
- Connect high-end security systems, casino gaming machines or digital signage in a small network

Package Includes

- SMX1000RT2UN 230V 1000VA 900W Line-Interactive UPS with



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

lets you monitor important data, such as load level, power factor, voltage, battery charge and estimated runtimes. It rotates for comfortable viewing in both rack and tower configurations. The audible alarm sounds for power failure, low battery and overloads. You may silence it using the built-in switch or disable it.

Advanced Communications Ports Allow for Automatic Saves and Shutdowns RS-232 and HID-compliant USB ports connect to a computer running Tripp Lite's free downloadable PowerAlert® software to enable safe unattended file saves and system shutdown in case of a prolonged power failure. The EPO port supports emergency shutdown in large facilities. Cables are included.

Versatile Installation Options Hardware is included for mounting the Tripp Lite SmartPro UPS system in 2U of space in an EIA-standard 19-inch 4-post rack. Using optional mounting accessories (sold separately), you can adapt the SMX1000RT2UN for 2-post (2POSTRMKITWM), front-rail (UPSHDEARKIT), 4-post short-depth (4POSTRAILKITWM), tower (2-9USTAND) or wall mounting (2POSTRMKITWM).

6 Outlets

- WEBCARDLX network management card
- USB cable
- DB9 cable
- EPO cable
- (2) C13-to-C14 AC power cords
- Rack-mounting hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332256416
UPS Type	Line-Interactive
INPUT	
Rated input current (Maximum Load)	4.8A
Nominal Input Voltage(s) Supported	230V AC
UPS Input Connection Type	C14 inlet
UPS Input Connection Description	IEC320-C14 input connection accepts a variety of user supplied detachable C13 output cordsets to match country or site-specific power sources
Input Circuit Breakers	10A
Input Phase	Single-Phase
OUTPUT	
Output Volt Amp Capacity (VA)	1000
Output kVA Capacity (kVA)	1
Output Watt Capacity (Watts)	900
Power Factor	0.9
Nominal Voltage Details	230V nominal output in battery mode
Frequency Compatibility	50 / 60 Hz
Frequency Compatibility Details	Automatic frequency selection
Output Voltage Regulation (Line Mode)	+6%, -11%
Output Voltage Regulation (Battery Mode)	+/- 5%



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Included Output Power Cables	Includes 2 C13 to C14 output power cables
Load Management Receptacles	Two switchable two-outlet C13 load banks
Hot-Swap PDU options	PDUBHV10 (2U / 8 C13 outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	220V; 230V; 240V
Output Receptacles	(6) C13
Individually Controllable Load Banks	Yes
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Full Load Runtime (min.)	3.6 min. (900w)
Half Load Runtime (min.)	11.9 min (450w)
Expandable Runtime	No
DC System Voltage (VDC)	24
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90% (typical, full load discharge)
Battery Access	Front panel battery access door
Internal UPS Replacement Battery Cartridge	RBC24V-LCD (quantity 1)
Battery Replacement Description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 182 to 278
Overvoltage Correction	Input voltages between 244 and 278 are reduced by 12%
Undervoltage Correction	Input voltages between 182 and 206 are boosted by 12%
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, operating mode, alarm function and a variety of additional options (see manual for detailed LCD configuration and monitoring options)
Switches	3 pushbutton switches control OFF / ON power status, MODE selection and MUTE / ENTER control functions
Alarm Cancel Operation	Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	350



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Cooling Method	Fan
Included Mounting Accessory Description	Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm)
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2 post rackmount); 2-4 post front rail rackmount (2-4 post front rail rackmount); 4 post rackmount short-depth (4 post rackmount short-depth); Tower (Tower); Wallmount (Wallmount); Rackmount (Rackmount)
Minimum Required Rack Depth (cm)	40.00
Minimum Required Rack Depth (inches)	15.75
Optional Mounting Accessory Notes	Optional (2 post rackmount); (2-4 post front rail rackmount); (4 post rackmount short-depth); (Tower); (Wallmount); (Rackmount)
Primary Form Factor	Rackmount
Primary UPS Depth (mm)	343
Primary UPS Height (mm)	89
Primary UPS Width (mm)	445
Rack Height	2U
Shipping Dimensions (hwd / in.)	8.50 x 23.10 x 18.20
Shipping Weight (kg)	20.82
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, in.)	3.5 x 17.5 x 13.5
UPS Power Module Weight (kg)	15.42
UPS Power Module Weight (lbs.)	34
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	100
AC Mode Efficiency Rating (100% Load)	97%
Audible Noise	45 dBA maximum, front side 1m
COMMUNICATIONS	
Network Management Cards	 WEBCARDLX
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at http://www.tripplite.com/poweralert
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Communications Interface	DB9 Serial; EPO (emergency power off); Pre-installed network card; Slot for SNMP/Web interface; USB (HID enabled)
LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	182
High Voltage Transfer to Battery Power (Setpoint)	278
SPECIAL FEATURES	
Grounding Lug	Back panel grounding lug
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Auto Probe Monitoring and Reboot (included); Automatic Voltage Regulation (AVR); Hot swappable batteries; Remote management; Sine wave output; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks
STANDARDS & COMPLIANCE	
UPS Certifications	CE; ROHS (Restriction of Hazardous Substances); Tested to GOST (Russia)
Certification Details	IEC 62040-1, IEC 62040-2 Class A EMI
WARRANTY	
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	2-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>