

Rittal – The System.

Faster – better – everywhere.

Gland plate module, multi-piece, with brush strip, super- airtight for VX IT – VX 5301.334

Date : Dec 17, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Gland plate module, multi-piece, with brush strip, super-airtight for VX IT – VX 5301.334

created: 17.12.2020 on www.rittal.com/com-en



Product description

Design:	two-piece, with brush strip
Description:	For targeted cable entry from below. With correct cable entry, special brush strips with alternating offset brushes provide a more effective seal from the environment to support climate control. The two-piece design even allows retrospective fitting of the base module with the cables already installed.
Material:	Module plate: Sheet steel Brush strip: Plastic, UL 94 HB, halogen-free
Surface finish:	Module plate: Zinc-plated
Assembly instruction:	Several gland module plates must be combined to seal the base completely in the VX IT. The gland plate module may be combined in exchange with other base modules with a depth of 237.5 mm.
Supply includes:	Assembly parts
Note:	Gland plate modules with brush strip not suitable for applications with a protection category to IEC 60 529

Product features

To fit:	Enclosure type: VX IT Width: = 600 mm
Dimensions:	Depth: 237.5 mm

Packs of:	1 pc(s).
Copper weight (kg per piece):	0
EAN:	4028177950863
Customs tariff number:	94039010
ETIM 7.0:	EC002620
ETIM 6.0:	EC002620
eCl@ss 8.0/8.1:	27189261
eCl@ss 6.0/6.1:	27182003
Product description:	VX IT gland plate module with brush strip, for width 600 mm, W x D 600 x 237.5 mm, two-piece, sheet steel