

# Rittal – The System.

Faster – better – everywhere.

## **482.6 mm (19") mounting angles, standard for VX IT – VX IT 5302.106**

Date : Dec 17, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# 482.6 mm (19") mounting angles, standard for VX IT – VX IT 5302.106

created: 17.12.2020 on [www.rittal.com/com-en](http://www.rittal.com/com-en)



## Product description

<b>Description:</b>	Suitable for assembling a 482.6 mm (19") mounting level or for 482.6 mm (19") partial installation. The L-shaped design directly accommodates all commercially available installation kits for server systems, which are fastened directly to the 482.6 mm (19") system punchings.
<b>Benefits:</b>	Integral, bidirectional U labelling Integral system punchings on a U pitch pattern on the front and sides, allows U-specific mounting of cable routing components for structured cabling
<b>Applications:</b>	For mounting a 482.6 mm (19") mounting level within the VX IT rack system
<b>Material:</b>	Sheet steel, 2 mm
<b>Surface finish:</b>	Primed
<b>Colour:</b>	RAL 9005
<b>Technical specifications:</b>	Side punchings, round and square, on a U pitch pattern Potential equalisation within the mounting level and with the locating frame is achieved via the assembly components 482.6 mm (19") mounting hole including U centre fixing attachment to standard EIA 310 E
<b>Assembly instruction:</b>	A combination with cross-member, depth stays or mounting bracket is required for attachment Use of the different mounting options depends on the relevant enclosure dimensions
<b>Supply includes:</b>	Assembly parts

## Product features

<b>To fit:</b>	Height: = 42 U
<b>Dimensions:</b>	Width: 19"
<b>Installation options:</b>	Alternative installation widths from 21" – 24", depending on the mounting variant and rack dimensions selected
<b>Mounting position:</b>	front
<b>Packs of:</b>	2 pc(s).
<b>Copper weight (kg per piece):</b>	0
<b>EAN:</b>	4028177955448
<b>Customs tariff number:</b>	73269098
<b>ETIM 7.0:</b>	EC002620
<b>ETIM 6.0:</b>	EC002620
<b>eCl@ss 8.0/8.1:</b>	27189261
<b>eCl@ss 6.0/6.1:</b>	27189261
<b>Product description:</b>	Mounting angles standard, 482.6 mm (19") for VX IT, to build an inch-based mounting level within the VX IT housing system, for enclosure height 42 U, sheet steel, 2 mm, primed, RAL 9005