

Rittal – The System.

Faster – better – everywhere.

Circuit-breaker component adaptor 3- pole – SV 9635.100

Date : Dec 17, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Circuit-breaker component adaptor 3-pole – SV 9635.100

created: 17.12.2020 on www.rittal.com/com-en



Product description

Function principle:	For mechanical attachment and direct contacting of circuit-breakers on the board Circuit-breaker is fitted using variably adjustable fixing points (M4)
Material:	Polyamide Fire protection corresponding to UL 94-V0
Colour:	RAL 7035
Note:	Consider the mounting distance of the circuit-breaker when selecting the circuit-breaker component adaptor Depending on the circuit-breaker used, there may be a reduction in output The technical data may vary for UL applications

Product features

Number of poles:	3-pole
Dimensions:	Width: 90 mm Height: 160 mm Depth: 45 mm
Rated current max.:	160 A
Rated operating voltage:	690 V (AC), 3~ 600 V (DC), 3~
Cable outlet:	Top/bottom

Mounting distance:	25 mm
To fit manufacturer (model):	ABB (XT1) Allen Bradley (140G-G) Siemens (3VA10, 3VA11, 3VA51)
Packs of:	1 pc(s).
Copper weight (kg per piece):	0
EAN:	4028177951877
Customs tariff number:	85369095
ETIM 7.0:	EC001531
ETIM 6.0:	EC001531
eCl@ss 8.0/8.1:	27370304
eCl@ss 6.0/6.1:	27370304
Product description:	SV CB component adaptor160 A, 690 V (AC), 600 V (DC), 3-pole WH: 90 x 160 mm, mounting distance 25 mm
Approvals	
Approvals:	UL + C-UL