



Telecom Grounding Busbar – TGBA12L06P



- Meets TIA-607-C and conforms to BICSI® recommendations
- Complies with NEMA® standards
- Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)
- Telecom grounding busbar splice kits are available to extend the length of the busbar



Part Number	TGBA12L06P
Material	Copper
Tin Plating	No
Width (W)	2"
Thickness (T)	1/4"
Length 1 (L1)	12"
Length 2 (L2)	9"
Hole Size 1 (HS1)	5/16"
Hole Size 1 Number of Pairs	6
Hole Size 2 (HS2)	7/16"
Hole Size 2 Number of Pairs	3
A	1"
B	1 1/8"
C	5/8"
Certifications	cULus
Standard Packaging Quantity	1 pc
UPC	78285668652
EAN-13	0782856686521

BICSI is a registered service mark of Building Industry Consulting Service International, Inc. NEMA is a registered service mark of National Electrical Manufacturers Association. UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2020 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.