


Ground Rod Clamp, U-Bolt, Tinned, One Conductor – GC064



- Tinned finish provides a theft-deterrent appearance
- Accepts conductors in both parallel and perpendicular orientations



Part Number	GC064
Material	Bronze Stainless Steel 304 (EN 1.4301)
Finish	Tinned
Ground Rod Diameter, Nominal	5/8" – 3/4"
Conductor Size, UL	#4 Sol - 2/0 Str 16 mm ² Str - 50 mm ² Str
Certifications	cULus
Standard Packaging Quantity	1 pc
UPC	78285661711
EAN-13	8711893125375

Conductor Orientation (Parallel or Perpendicular)						
GC064	Conductor Size					
Nominal Ground Rod Diameter	#4 Sol	#4 Str	#2 Sol	#2 Str	1/0 Sol	1/0 Str-3/0 Sol
5/8" copper-bonded ground rod	Par.	Par.	Par.	Par.	Both	Perp.
5/8" galvanized/stainless steel ground rod	Par.	Par.	Par.	-	Perp.	Perp.
3/4" copper-bonded ground rod	Par.	-	-	-	Perp.	Perp.
3/4" galvanized/stainless steel ground rod	-	-	-	-	Perp.	-

Conductor Orientation (Parallel or Perpendicular)				
GC065	Conductor Size			
Nominal Ground Rod Diameter	#4 Sol-#4 Str	#2 Sol-4/0 Sol	4/0 Str	250 kcmil Str
5/8" copper-bonded ground rod	Par.	Both	Both	Par.
5/8" galvanized/stainless steel ground rod	Par.	Both	Both	Par.
3/4" copper-bonded ground rod	Par.	Both	Both	-
3/4" galvanized/stainless steel ground rod	Par.	Both	-	-

UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2020 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.