



16A model :	Circuit Protection
MiniBoot-4C13-16A / 230V	16A resettable fuse x 1

Input Rating : 16Amp, 230V
Outlet : C13 #1-4
Inlet : 16A IEC320 C20
Protection : 16A resettable fuse x 1
Circuit : Output 16A max.

13A model :	Circuit Protection
MiniBoot-4C13-13A / 230V	13A resettable fuse x 1

Input Rating : 13Amp, 230V
Outlet : C13 #1-4
Inlet : 16A IEC320 C20
Protection : 13A resettable fuse x 1
Circuit : Output 13A max.

10A model :	Circuit Protection
MiniBoot-4C13-10A / 230V	10A resettable fuse x 1

Input Rating : 10Amp, 230V
Outlet : C13 #1-4
Inlet : 16A IEC320 C20
Protection : 10A resettable fuse x 1
Circuit : Output 10A max.



Meter Features (MiniBoot PDU)

- Local Display : 3-digit LED ammeter for input current
- Measurement : Current (Amp)
- Alarm threshold support : Overload, temp, humidity & auto-ping
- Remote management : Telnet or SNMP v2 / v3
- Outlet : ON / OFF / Reboot over network
- IP security : LDAPv3 / LDAPS, AD, RADIUS, local credential database
- Protocol : HTTP(S), SSH Command Line Interface, Telnet, SMTP, IPv6/IPv4
- 1 x IP port : 10 / 100 / 1000 Base T, RJ45
- 1 x serial port : for CLI command access
- 2 x sensor port : Support Temp. / Temp. + Humid. / Smoke sensor / Door switch
- 1 x USB port : for Wifi Kit (option)

Chassis Material : Steel
Chassis Color : White

Net weight : 0.9 kg
Gross wieht : 1.5 kg

Product Dimension : 180 (W) x 140 (D) x 44.5 (H) mm
Packing dimension : 300 (W) x 196 (D) x 81 (H) mm

EMC Compliance : CE / EMC
Safety Compliance : CE / LVD
Environment Compliance : RoHS3, Reach & WEEE

Operating Temperature : -5 to 60 °C
Storage Temperature : -25 to 65 °C
Operating Altitude : 0 to 2,000 m
Storage Altitude : 0 to 15,000 m
Humidity : 8 to 95% RH, non-condensing