

---

## Slim Line II Wi-Fi Doorbell Camera (ADC-VDB105x/106x) - Data Sheet

### Overview

The Slim Line II Wi-Fi Doorbell Camera makes it easy to deliver front door awareness to even more customers! The Slim Line II delivers an engaging customer experience with Two-Way Audio, live and recorded video, and notifications. The Slim Line II has an integrated camera, PIR motion sensor, and digital microphone and speaker, that enables homeowners to answer the door and speak right from their app. Customers can also record doorbell triggered clips, set motion triggered automation rules, and receive realtime alerts.

### Features

- 720p live video
- Doorbell with integrated camera
- PIR-triggered motion sensitivity (low, medium, and high settings)
- Digital microphone and speaker
- Doorbell-triggered clips
- Motion-triggered automation rules
- Real-time alerts
- Battery heater for improved cold weather performance

### Included accessories

- Wall mounting bracket
- Wall screws
- Masonry anchors





## Specifications

### Power

Operational range is 10-30 VAC, 10 VA or 12 VDC 0.5 to 1.0 A wired to an in-home mechanical or digital doorbell chime. Digital doorbell chime compatibility requires SkyBell Digital Doorbell Adapter - not included.

Alarm.com recommends a minimum of 12 VAC for consistent functionality, but the recommended range for best results is 16-24 VAC.

### Wi-Fi

Compatible with Wi-Fi 802.11 b/g/n/ ac, 2.4 and 5 GHz

### Minimum Bandwidth Requirement

2 Mbps

### Video Camera

1.3 MP, full-color

### Lens / angle of view

170° horizontal, 110° vertical

### Resolution

Live: 720p (adjustable to lower resolution if required)  
Recorded: 720p

### Night vision

Infrared

### Microphone

Omni-directional

### Motion Sensor

Detects motion up to 8 ft range

### Dimensions (width x depth x weight)

1.4 x 4.8 x 1.1" (3.65 x 12.2 x 2.86 cm); 3.1 oz (87.9 g)

### Weather Rating

IPX4 rated

### Operating Temperature

-40°F to 122°F (-40°C to 50°C)

### Operating Humidity

Operating Humidity (RH): 10% to 80%

