

Full-Motion TV Wall Mount with Fully Articulating Arm for 23" to 55" Flat-Screen Displays

MODEL NUMBER: DWM2355S



Mounts your 23 to 55 in. television to the wall of your home theater, office, restaurant or boardroom to provide optimal viewing angles.

Features

Mounts Your TV or Monitor to the WallFits most flat-panel televisions, monitors and other displays from 23 to 55 in. Ideal for home theaters, offices, classrooms, boardrooms, hotels, bars and restaurants Full-motion articulating arm adjusts independently for angle and height Mounting hardware included Mounts on wood or concrete block

Convenient One-Touch Adjustment180° swivel and -15° to 15° tilt capability provides comfortable viewing from multiple angles

Durable Metal ConstructionSupports up to 51 lbs (23.1 kgs) Soft rubber-feel finish tolerates frequent handling and blends with any décor Display cables tuck inside articulating arm to prevent clutter

VESA ComplianceConforms with VESA-compliant universal mounting hole patterns

Highlights

- TV wall mount with articulating gas-spring arm adjusts easily with just a single touch
- -15° to +5° tilt and -90° to +90° swivel helps you find the perfect angle to avoid glare
- Durable steel construction blends into any décor and supports up to 51 lbs (23.1 kgs)
- Display cables attach to arm to reduce clutter and keep cords organized
- VESA compliance ensures compatibility with most popular mounting hole patterns

Applications

- Mounting a flat-screen television or monitor in an office lobby, conference room, bar, restaurant, airport or anywhere else digital signage is desired
- Installing a TV in your home theater that can be easily adjusted to accommodate the comfort levels of the audience

System Requirements

- Flat-screen television or monitor from 23 to 55 in.

Package Includes

- Wall plate with articulating arm
- VESA plate
- (4) VESA adapter brackets
- (2) Wall plate end caps
- (4) Nuts
- (4) Bolts
- Wrench



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Hex key, 4 mm
- Hex key, 6 mm
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 30 screws
- (4) M8 x 50 screws
- (4) D5 washers
- (4) D8 washers
- (8) Small spacers
- (8) Large spacers
- (3) Anchor bolts
- (3) Concrete anchors
- (3) Washers
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332258779
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
VESA Pattern (mm)	75x75; 100x100; 200x100; 200x200; 300x300; 400x200; 400x300; 400x400
Degrees of Motion	-15/+15 Tilt; 180 Swivel
Distance from Wall (in.)	12.7
Distance from Wall (cm)	32
Distance from Wall (mm)	323
Material of Construction	Steel
Maximum Screen Size (cm)	139.7
Maximum Screen Size (in.)	55
Maximum Weight Capacity (kg)	23
Maximum Weight Capacity (lbs.)	51
Min/Max Arm Extension (cm)	71.9 to 46.6
Min/Max Arm Extension (in.)	2.83 to 18.34"



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Minimum Screen Size (in.)	23
Minimum Screen Size (cm)	58.4
Motion	Full
Mounting Location	Wall
Number of Displays	1
Shipping Dimensions (hwd / cm)	43.94 x 34.80 x 8.38
Shipping Dimensions (hwd / in.)	17.30 x 13.70 x 3.30
Shipping Weight (kg)	4.04
Shipping Weight (lbs.)	8.90
Unit Dimensions (hwd / cm)	16.69 x 6.88 x 63.19
Unit Dimensions (hwd / in.)	6.57 x 2.71 x 24.88
Unit Weight (kg)	3.22
Unit Weight (lbs.)	7.1
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
SPECIAL FEATURES	
Cord Management	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Approvals	RoHS3, REACH and CE
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>