

ITW Performance Polymers

SAFETY DATA SHEET MA300 ADHESIVE.

Commission Regulation (EU) No 2015/830 of 28 May 2015.

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name MA300 ADHESIVE.
UFI UFI: 5T10-G09V-0004-QXC1
REACH registration notes CAS 80-62-6: 01-2119452498-28-XXXX CAS 79-41-4: 01-2119463884-26-XXXX

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Adhesive.

1.3. Details of the supplier of the safety data sheet

Supplier ITW Performance Polymers
Bay 150
Shannon Industrial Estate
Co. Clare
Ireland
V14 DF82
353(61)771500
353(61)471285
customerservice.shannon@itwpp.com

1.4. Emergency telephone number

Emergency telephone +44(0)1235 239 670 (24h)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards Flam. Liq. 2 - H225
Health hazards Skin Irrit. 2 - H315 Skin Sens. 1 - H317 STOT SE 3 - H335
Environmental hazards Not Classified

2.2. Label elements

Hazard pictograms



Signal word Danger

Hazard statements H225 Highly flammable liquid and vapour.
H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H335 May cause respiratory irritation.

MA300 ADHESIVE.

Precautionary statements	<p>P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.</p> <p>P271 Use only outdoors or in a well-ventilated area.</p> <p>P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.</p> <p>P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower.</p> <p>P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.</p> <p>P333+P313 If skin irritation or rash occurs: Get medical advice/ attention.</p>
Contains	methyl methacrylate, methacrylic acid, bis[4-(2,3-EPOXYPROPOXY)PHENYL]PROPANE, 1,4-dihydroxybenzene
Supplementary precautionary statements	<p>P240 Ground and bond container and receiving equipment.</p> <p>P241 Use explosion-proof electrical equipment.</p> <p>P242 Use non-sparking tools.</p> <p>P243 Take action to prevent static discharges.</p> <p>P261 Avoid breathing vapour/ spray.</p> <p>P264 Wash contaminated skin thoroughly after handling.</p> <p>P272 Contaminated work clothing should not be allowed out of the workplace.</p> <p>P302+P352 IF ON SKIN: Wash with plenty of water.</p> <p>P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.</p> <p>P310 Immediately call a POISON CENTER/ doctor.</p> <p>P312 Call a POISON CENTRE/doctor if you feel unwell.</p> <p>P321 Specific treatment (see medical advice on this label).</p> <p>P332+P313 If skin irritation occurs: Get medical advice/ attention.</p> <p>P362+P364 Take off contaminated clothing and wash it before reuse.</p> <p>P370+P378 In case of fire: Use foam, carbon dioxide, dry powder or water fog to extinguish.</p> <p>P403+P233 Store in a well-ventilated place. Keep container tightly closed.</p> <p>P403+P235 Store in a well-ventilated place. Keep cool.</p> <p>P405 Store locked up.</p> <p>P501 Dispose of contents/ container in accordance with national regulations.</p>

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

methyl methacrylate		50-60%
CAS number: 80-62-6	EC number: 201-297-1	REACH registration number: 01-2119452498-28-0000
Classification		
Flam. Liq. 2 - H225		
Skin Irrit. 2 - H315		
Skin Sens. 1 - H317		
STOT SE 3 - H335		

MA300 ADHESIVE.

methacrylic acid 5-10%		
CAS number: 79-41-4	EC number: 201-204-4	REACH registration number: 01-2119463884-26-0000
Classification		
Acute Tox. 4 - H302		
Acute Tox. 4 - H312		
Skin Corr. 1A - H314		
Eye Dam. 1 - H318		
STOT SE 3 - H335		
bis-[4-(2,3-epoxipropoxy)phenyl]propane <1%		
CAS number: 1675-54-3	EC number: 216-823-5	REACH registration number: 01-2119456619-26-0000
Classification		
Skin Irrit. 2 - H315		
Eye Irrit. 2 - H319		
Skin Sens. 1 - H317		
Aquatic Chronic 2 - H411		
2,6-DITERTIARYBUTYL-PARA-CRESOL <1%		
CAS number: 128-37-0		
M factor (Chronic) = 1		
Classification		
Aquatic Chronic 1 - H410		
α,α-dimethylbenzyl hydroperoxide <1%		
CAS number: 80-15-9		
EC number: 201-254-7		
Classification		
Org. Perox. E - H242		
Acute Tox. 4 - H302		
Acute Tox. 4 - H312		
Acute Tox. 3 - H331		
Skin Corr. 1B - H314		
Eye Dam. 1 - H318		
STOT SE 3 - H335		
STOT RE 2 - H373		
Aquatic Chronic 2 - H411		

MA300 ADHESIVE.

1,4-dihydroxybenzene	<1%
CAS number: 123-31-9	EC number: 204-617-8
M factor (Acute) = 10	M factor (Chronic) = 1
Classification Acute Tox. 4 - H302 Eye Dam. 1 - H318 Skin Sens. 1 - H317 Muta. 2 - H341 Carc. 2 - H351 Aquatic Acute 1 - H400 Aquatic Chronic 1 - H410	

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures**4.1. Description of first aid measures**

General information	Avoid contact with skin and eyes. Do not breathe vapour/spray. In case of accident or if you feel unwell, seek medical advice immediately (show the label where possible).
Inhalation	Move affected person to fresh air at once. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Get medical attention if any discomfort continues.
Ingestion	Do not induce vomiting. Give plenty of water to drink. Get medical attention.
Skin contact	Remove affected person from source of contamination. Wash skin thoroughly with soap and water. Get medical attention if irritation persists after washing.
Eye contact	Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes and get medical attention. Get medical attention if irritation persists after washing.

4.2. Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
----------------------------	---

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	No specific recommendations. If in doubt, get medical attention promptly.
-----------------------------	---

SECTION 5: Firefighting measures**5.1. Extinguishing media**

Suitable extinguishing media	Extinguish with foam, carbon dioxide or dry powder.
-------------------------------------	---

5.2. Special hazards arising from the substance or mixture

Specific hazards	Highly flammable. Avoid breathing fire gases or vapours. Vapours are heavier than air and may spread near ground and travel a considerable distance to a source of ignition and flash back. Polymerises easily with evolution of heat.
-------------------------	--

5.3. Advice for firefighters

Protective actions during firefighting	Keep up-wind to avoid fumes. Do not use water jet as an extinguisher, as this will spread the fire. Cool containers exposed to flames with water until well after the fire is out. Control run-off water by containing and keeping it out of sewers and watercourses.
---	---

MA300 ADHESIVE.

Special protective equipment for firefighters Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Highly flammable Warn everybody of potential hazards and evacuate if necessary. No smoking, sparks, flames or other sources of ignition near spillage. Provide adequate ventilation. Avoid contact with skin and eyes. Avoid inhalation of spray mist and contact with skin and eyes. Wear protective clothing as described in Section 8 of this safety data sheet.

6.2. Environmental precautions

Environmental precautions Avoid the spillage or runoff entering drains, sewers or watercourses. Spillages or uncontrolled discharges into watercourses must be reported immediately to the Environmental Agency or other appropriate regulatory body.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Absorb spillage with non-combustible, absorbent material. Collect and place in suitable waste disposal containers and seal securely. Containers with collected spillage must be properly labelled with correct contents and hazard symbol.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8. For waste disposal, see section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Provide adequate general and local exhaust ventilation. Observe any occupational exposure limits for the product or ingredients. Avoid contact with skin and eyes. Take precautionary measures against static discharges. Storage tanks and other containers must be earthed. No smoking, sparks, flames or other sources of ignition near spillage. Good personal hygiene procedures should be implemented.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Store in tightly-closed, original container in a dry, cool and well-ventilated place. Store away from incompatible materials (see Section 10).

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Occupational exposure limits

methyl methacrylate

Long-term exposure limit (8-hour TWA): WEL 50 ppm 208 mg/m³

Short-term exposure limit (15-minute): WEL 100 ppm 416 mg/m³

methacrylic acid

Long-term exposure limit (8-hour TWA): WEL 20 ppm 72 mg/m³

Short-term exposure limit (15-minute): WEL 40 ppm 143 mg/m³

2,6-DITERTIARYBUTYL-PARA-CRESOL

Long-term exposure limit (8-hour TWA): WEL 10 mg/m³

1,4-dihydroxybenzene

Long-term exposure limit (8-hour TWA): WEL 0.5 mg/m³

MA300 ADHESIVE.

WEL = Workplace Exposure Limit.

Ingredient comments WEL = Workplace Exposure Limits

8.2. Exposure controls

Protective equipment



Appropriate engineering controls

Provide adequate general and local exhaust ventilation.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. The following protection should be worn: Chemical splash goggles. Personal protective equipment for eye and face protection should comply with European Standard EN166.

Hand protection

Wear protective gloves made of the following material: Rubber or plastic. To protect hands from chemicals, gloves should comply with European Standard EN374. The selected gloves should have a breakthrough time of at least 8 hours.

Other skin and body protection

Wear apron or protective clothing in case of contact.

Hygiene measures

Provide eyewash station and safety shower. Keep away from food, drink and animal feeding stuffs. Good personal hygiene procedures should be implemented. Wash hands and any other contaminated areas of the body with soap and water before leaving the work site. Do not eat, drink or smoke when using the product. Change work clothing daily before leaving workplace.

Respiratory protection

If ventilation is inadequate, suitable respiratory protection must be worn. Respirator selection must be based on exposure levels, the hazards of the product and the safe working limits of the selected respirator. Check that the respirator fits tightly and the filter is changed regularly. Wear a respirator fitted with the following cartridge: Organic vapour filter. Gas filter, type A2. Half mask and quarter mask respirators with replaceable filter cartridges should comply with European Standard EN140.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Paste.
Colour	White/off-white.
Odour	Slight pungent.
pH	pH (diluted solution): 3.5 - 5%
Initial boiling point and range	101°C @
Flash point	10°C Tag closed cup.
Evaporation rate	3 (butyl acetate =1)
Upper/lower flammability or explosive limits	Upper flammable/explosive limit: 12.5 Lower flammable/explosive limit: 2.1
Vapour pressure	28 mmHg @ °C
Vapour density	>1

MA300 ADHESIVE.

Relative density	1.03 @ 20 °C°C
Viscosity	40,000-60,000 cP @ 25°C

9.2. Other information

Other information	Not available.
--------------------------	----------------

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity	The following materials may react with the product: Strong oxidising agents. Strong reducing agents.
-------------------	--

10.2. Chemical stability

Stability	Stable at normal ambient temperatures and when used as recommended. May polymerise.
------------------	---

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	May polymerise.
---	-----------------

10.4. Conditions to avoid

Conditions to avoid	Avoid heat, flames and other sources of ignition. Avoid excessive heat for prolonged periods of time. Avoid exposure to high temperatures or direct sunlight. Heating may generate flammable vapours. Vapours may form explosive mixtures with air.
----------------------------	---

10.5. Incompatible materials

Materials to avoid	Avoid contact with the following materials: Oxidising agents. Reducing agents. Alkalis - inorganic. Alkalis - organic.
---------------------------	--

10.6. Hazardous decomposition products

Hazardous decomposition products	Oxides of carbon. Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.
---	--

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral

ATE oral (mg/kg)	5,882.35
-------------------------	----------

Acute toxicity - dermal

ATE dermal (mg/kg)	12,941.18
---------------------------	-----------

Acute toxicity - inhalation

ATE inhalation (gases ppm)	106,060.61
-----------------------------------	------------

ATE inhalation (vapours mg/l)	454.55
--------------------------------------	--------

ATE inhalation (dusts/mists mg/l)	75.76
--	-------

Inhalation	Vapours in high concentrations are narcotic. Symptoms following overexposure may include the following: Headache. Fatigue. Dizziness. Nausea, vomiting. Vapours in high concentrations are anaesthetic. Symptoms following overexposure may include the following: Headache. Fatigue. Dizziness. Central nervous system depression.
-------------------	---

Ingestion	Irritating. Symptoms following overexposure may include the following: Nausea, vomiting. Stomach pain.
------------------	--

MA300 ADHESIVE.

Skin contact	May be absorbed through the skin. Irritating to skin. Prolonged or repeated exposure may cause severe irritation. May cause sensitisation by skin contact. May cause sensitisation or allergic reactions in sensitive individuals.
Eye contact	Irritating to eyes. A single exposure may cause the following adverse effects: Corneal damage.
Target organs	Prolonged or repeated exposure may cause the following adverse effects: May cause damage to the liver and kidneys. Central nervous system Respiratory system, lungs

Toxicological information on ingredients.

methyl methacrylate

Carcinogenicity

IARC carcinogenicity IARC Group 3 Not classifiable as to its carcinogenicity to humans.

methacrylic acid

Acute toxicity - oral

ATE oral (mg/kg) 500.0

Acute toxicity - dermal

ATE dermal (mg/kg) 1,100.0

bis-[4-(2,3-epoxipropoxy)phenyl]propane

Carcinogenicity

IARC carcinogenicity IARC Group 3 Not classifiable as to its carcinogenicity to humans.

1,4-dihydroxybenzene

Acute toxicity - oral

ATE oral (mg/kg) 500.0

Carcinogenicity

IARC carcinogenicity IARC Group 3 Not classifiable as to its carcinogenicity to humans.

SECTION 12: Ecological information

Ecotoxicity Avoid release to the environment.

12.1. Toxicity

Toxicity Not considered toxic to fish.

12.2. Persistence and degradability

Persistence and degradability Methyl methacrylate monomer : Biochemical oxygen demand within 5 days (BOD5) = .14 g/g - 0.9 g/g.

12.3. Bioaccumulative potential

Bioaccumulative potential Methyl methacrylate monomer: LC50/96h/fathead minnows = 150 ppm, LC50/96h/bluegill sunfish = 232ppm. Methyl methacrylate monomer: LC50/96h/rainbow trout = >79mg/l

12.4. Mobility in soil

Mobility Do not discharge into drains or watercourses or onto the ground.

12.5. Results of PBT and vPvB assessment

MA300 ADHESIVE.

Results of PBT and vPvB assessment This product does not contain any substances classified as PBT or vPvB.

12.6. Other adverse effects

Other adverse effects Not available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information Waste is classified as hazardous waste. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority. When handling waste, the safety precautions applying to handling of the product should be considered.

Disposal methods Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

Waste class 08 04 09

SECTION 14: Transport information

General No other information known.

14.1. UN number

UN No. (ADR/RID) 1133

UN No. (IMDG) 1133

UN No. (ICAO) 1133

14.2. UN proper shipping name

Proper shipping name (ADR/RID) ADHESIVES

Proper shipping name (IMDG) ADHESIVES

Proper shipping name (ICAO) ADHESIVES

Proper shipping name (ADN) ADHESIVES

14.3. Transport hazard class(es)

ADR/RID class 3

ADR/RID label 3

IMDG class 3

ICAO class/division 3

Transport labels



14.4. Packing group

ADR/RID packing group II

IMDG packing group II

ICAO packing group II

14.5. Environmental hazards

MA300 ADHESIVE.**Environmentally hazardous substance/marine pollutant**

No.

14.6. Special precautions for user**EmS** F-E, S-D**Emergency Action Code** •3YE**Hazard Identification Number (ADR/RID)** 33**Tunnel restriction code** (D/E)**14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code****Transport in bulk according to** No information required.**Annex II of MARPOL 73/78 and the IBC Code****SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU legislation** Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).**15.2. Chemical safety assessment**

No chemical safety assessment has been carried out.

SECTION 16: Other information**Revision comments** Revised classification.**Revision date** 09/02/2021**Revision** 32**Supersedes date** 05/04/2018

Hazard statements in full

H225 Highly flammable liquid and vapour.
H242 Heating may cause a fire.
H302 Harmful if swallowed.
H312 Harmful in contact with skin.
H314 Causes severe skin burns and eye damage.
H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H318 Causes serious eye damage.
H319 Causes serious eye irritation.
H331 Toxic if inhaled.
H335 May cause respiratory irritation.
H341 Suspected of causing genetic defects.
H351 Suspected of causing cancer.
H373 May cause damage to organs through prolonged or repeated exposure.
H400 Very toxic to aquatic life.
H410 Very toxic to aquatic life with long lasting effects.
H411 Toxic to aquatic life with long lasting effects.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.