

WWT-P-7401 Series

Wisenet WAVE Client Workstation



The WWT-P-7401W series client workstation is an easily deployable solution that can be used on-site or remotely to access your Wisenet WAVE video recorder running Windows 10 IoT / Ubuntu Linux 18.04 LTS.

WWT-P-7401W / WWT-P-7401L

SYSTEM		
Video Management Software	Wisenet WAVE	
OS Drive Bays	1 x 256GB SSD (internally mounted)	
Network Interface	1 x RJ-45, Gigabit Ethernet	
Processor	1 x Intel® Core™ i7 10th Gen, 3.0Ghz to 4.7Ghz (8 Cores, 8 Threads, 12MB)	
Memory	16GB DDR4	
Operating System	Windows 10 IoT / Ubuntu Linux 18.04 LTS	
Video Outputs	Nvidia Quadro P620 GPU 4x Mini DisplayPort with 4x HDMI adapters	
USB Ports	Rear: (2) USB 3.1 Gen 1, (2) USB 2.0; Front: (2) USB 3.1 Gen 1, (2) USB 2.0	
Other Ports	3.5mm audio output	
Keyboard & Mouse	Included	
MECHANICAL / ELECTRICAL / ENVIRONMENTAL		
Mechanical	Form Factor	Small Form Factor Workstation
	Color / Material	Black / Metal & Plastic
	Dimensions (WxDxH)	3.7" x 11.5" x 11.4" (97mm x 292mm x 290mm)
	Weight	11.52 lbs (5.26 kg)
Electrical	Power Supply	1 x 200W 80 Plus Bronze
	Power Input	100 ~ 240V AC
	Power Consumption	Maximum 200W
Environmental	Operating Temperature	41°F ~ 95°F (5°C ~ 35°C)
	Storage Temperature	-40°F ~ 149°F (-40°C ~ 65°C)
	Operating Humidity	20% to 80% relative humidity (non-condensing)
Certification	UL, cUL, CB, FCC, 80 Plus Bronze	

* The latest product information / specification can be found at www.hanwhasecurity.com
 * Bandwidth performance figures based on performance testing by Hanwha Techwin using Wisenet WAVE

Key Features

- Preloaded and configured with Wisenet WAVE video management system client & tools
- Includes USB mouse and keyboard
- 5-Year, On-site, Next Business Day, Keep Your Hard Drive Warranty
- Nvidia Quadro P620 GPU, 4 x Mini DisplayPort video outputs with HDMI adapters

