

Rittal – The System.

Faster – better – everywhere.

Signal pillar 3-way LED – SG 2372.102

Date : Dec 17, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Signal pillar 3-way LED – SG 2372.102

created: 17.12.2020 on www.rittal.com/com-en



Product description

Design:	for wall/base mounting
Benefits:	Complete, ready-to-connect solution Extremely long service life of the LEDs (max. 100,000 hours, therefore maintenance-free) Minimal assembly work and warehousing costs
Technical specifications:	3-stage, red, yellow, green Transmission angle: 3 x 120° Flashing function: Controllable via PLC
Protection category IP to IEC 60 529:	IP 65

Product features

Dimensions:	Height: 343 mm
Rated operating voltage:	24 V
Min. cable diameter:	3 mm
Max. cable diameter:	6.5 mm
Operating temperature:	Operation (environment): -20 °C...+50 °C
Type of electrical connection:	Screwless spring terminals
Equipment (electrical):	Light: LEDs

Cable entry:	Metric diameter: M12 x 1.5 Number x metric diameter: M12 x 1.5
Packs of:	1 pc(s).
Copper weight (kg per piece):	0
EAN:	4028177953765
Customs tariff number:	85318070
ETIM 7.0:	EC001042
ETIM 6.0:	EC001042
eCl@ss 8.0/8.1:	27371230
eCl@ss 6.0/6.1:	27371230
Product description:	SG signal pillar, LED compact for wall mounting
Approvals	
Approvals:	UL + C-UL